

Uni-Dicht-Verschraubung Pg21, 14-18mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5093
Specification	Uni-Dicht-Verschraubung Pg21, 14-18mm
HARTING eCatalogue	https://b2b.harting.com/09000005093

Identification

Category	Accessories
Type of accessory	Cable gland

Technical characteristics

Tightening torque	≤15 Nm (depending on the cable and the seal insert used)
Wrench size	30
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	Pg 21
Clamping range	14 ... 18 mm

Material properties

Material (cable glands)	Metal
Colour (accessories)	Blue
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes



Pushing Performance

Material properties

California Proposition 65 substances	Nickel
	Lead

Commercial data

Packaging size	10
Net weight	63.82 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09000005093](#)