

NEW



- Extremely high light intensity up to 70 cd
- Wear-free thanks to the absence of any moving mechanical components
- Intensive rotating signal effect with low power consumption
- Life duration up to 50,000 hrs
- Shock proof and resistant against vibration
- High impact resistance to 20 Joules

i TECHNICAL SPECIFICATIONS:

Dimensions (Diameter x Height):	142 mm x 220 mm
Housing:	PC/ABS-Blend, black
Dome:	PC, transparent
Fixing:	Base mounting, bracket mounting, tube mounting (accessory)
Connection:	Screwable connection with wire protection max. 0.5 - 2.5 mm ² Contact protection according to VDE
Cable entry:	Cable diameter 5-7 mm
Starting current:	< 500 mA at 24 V ⁼⁼
Rotation rate:	c. 180 r.p.m.
Life duration:	up to 50,000 hrs
Duty cycle:	100 %

Life duration up to 50,000 hrs



🛒 ORDER SPECIFICATIONS:

Voltage	24 V ⁼⁼	115 - 230 V [~]
Current consumption	150 mA	140 mA
red	280 120 55	280 120 68
yellow	280 320 55	280 320 68

🏠 ACCESSORIES:

Plastic bracket for wall mounting	975 883 06
Flange for tube mounting max. 25.3 mm	975 883 02
Wire guard	975 883 08

📏 TECHNICAL DIAGRAMS:

see page 240



Generates a high signal effect thanks to the LEDs programmed to create a rotating light.



High impact resistance to 20 Joules



Plastic bracket, flange for tube mounting and wire guard (accessories)

