



**CUSTOMER DRAWING**

- NOTES:  
 1. IP67 RATED WHEN PROPERLY ASSEMBLED.  
 2. PANEL THICKNESS MAX OF 0.169 [4.30].  
 3. ALL PARTS SHIPPED ASSEMBLED.  
 4. MATERIALS;  
 HOUSING AND PANEL NUT - NYLON, BLACK  
 GASKET- EPDM RUBBER, BLACK  
 5. THIS PRODUCT IS RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
A	28311	08/24/20	PC	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED  
 1. ALL DIMENSIONS IN INCHES [mm]  
 - TWO PLACE DECIMALS ±0.02 [0.5]  
 - THREE PLACE DECIMALS ±0.005 [0.13]

**DO NOT SCALE DRAWING**

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE	WIDTH	MULT	LBS/M	TEMPER					
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON					SCALE 2:1				
DATE DRAWN	BY	CHKD	APVD						
6/23/20	FM	FM	TJK						
			6/23/20						
NAME RJ45 CAT6 PANEL MOUNT, UNSHIELDED JACK, PC TERMINAL					PART No. ENDP6PC				
					REV A				