






PC BOARD VERSIONS

PRODUCTNR:	PCB THICKNESS	DIM "A"
89036-X01LF	1.6	2.90
89036-X11LF	2.4	3.53



89036-XY1LF



RECOMMENDED HOLE PATTERN, COMPONENT SIDE.






NOTES:

- MATERIAL : BODY : LCP UL94-V0
: CONTACT : COPPER ALLOY.
- FOR PLATING PERFORMANCE REFER DRAWING # 101594.08 \triangle
- INDICATED HOLES ARE UNPLATED.
- DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47- 0004.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- A \triangle SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

mat'l. code		surface	tolerance	projection	product family	
		ISO 1302 <input checked="" type="checkbox"/>	ISO 406 ISO 1101		METRAL	
tolerances unless otherwise specified				title		
ltr	ecn no	dr	date	angles	RA FEMALE SIGNAL	
M	DG08-0171	TER	2008-08-26	linear	24 mm PRES PEG	
N	DG09-0068	CENH	2009-06-06	0°±2°	scale -	
P	ELX-I-38913	MINI	2020-10-23		dwg no sheet 1 of 3 size	
				dr	H. BOUWKENG	1993-02-02
				enr	ARUN	2020-10-23
				chr	ALEX BABU	2020-10-23
				appd	SANOJ	2020-10-23
sheet index		revision	P	P	Amphenol FCI	
		sheet	1	2	89036 A3	
			3		type Product Customer Drawing	


PC BOARD VERSIONS

PRODUCTNR:	PCB THICKNESS	DIM "A"
89036-X02LF	1.6	2.90
89036-X12LF	2.4	3.53



PC BOARD THICKNESS ±0.20
SEE TABLE

PRODUCT AFTER PC BOARD APPLICATION.



REFER NOTE-2

89036-XYLFF

RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

NOTES:

- MATERIAL : BODY : LCP UL94-V0 ; CONTACT : COPPER ALLOY.
- FOR PLATING PERFORMANCE REFER DRAWING # 101594.08
- INDICATED HOLES ARE UNPLATED.
- SET BACK FOR PRESS BLOCK.
- DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
- TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47- 0004.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.






mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection		product family METRAL	
ltr				ecn no		dr		date		title	
M	DG08-0171	TER	2008-08-26	tolerances unless otherwise specified		.X±0.3		mm		RA FEMALE SIGNAL	
N	DG09-0068	CENH	2009-06-06	angles linear		.XX±0.13		mm		24 mm PRES PEG	
P	ELX-I-38913	MINI	2020-10-23	0°±2°		.XXX±0.050		scale -		dwg no sheet 2 of 3 size	
				dr		H. BOUWKENG		1993-02-02		89036	
				enr		ARUN		2020-10-23		A3	
				chr		ALEX BABU		2020-10-23		type Product Customer Drawing	
				appd		SANUJ		2020-10-23			
sheet index		revision sheet		P P		P					
				1 2		3					

Amphenol FCI

2016 AFCl

PC BOARD VERSIONS

PRODUCTNR:	PCB THICKNESS	DIM "A"
89036-X03LF	1.6	2.90
89036-X13LF	2.4	3.53



REFER NOTE-2
89036-XYYLF

RECOMMENDED HOLE PATTERN, COMPONENT SIDE.

NOTES:

- MATERIAL : BODY : LCP UL94-V0
: CONTACT : COPPER ALLOY.
- FOR PLATING PERFORMANCE REFER DRAWING # 10159408 \triangle
- INDICATED HOLES ARE UNPLATED.
- DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47- 0004.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- A \triangle SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406	ISO 1101	METRAL		
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title		
M	DG08-0171	TER	2008-08-26	angles	.X±0.3		RA FEMALE SIGNAL		
N	DG09-0068	CENH	2009-06-06	linear	.XX±0.13		24 mm PRES PEG		
P	ELX-I-38913	MINI	2020-10-23	0°±2°	.XXX±0.050	scale			
				dr	H. BOUWKENG	1993-02-02	dwg no		
				enr	ARUN	2020-10-23	sheet 3 of 3		
				chr	ALEX BABU	2020-10-23	size		
				appd	SANOJ	2020-10-23	A3		
sheet index		revision	P	P	P	type			
		sheet	1	2	3	Product Customer Drawing			

Amphenol FCI

© 2016 AFCl