


**SPAX®**

BN 20183 - Hexalobular (6 Lobe) socket flat countersunk head chipboard screws T-STAR plus, fully threaded with 4CUT point



Manufacturer



Product description

Other documentation: [www.spax.com](http://www.spax.com)

Additional information

The WIROX® coating is an alternative chromium free (VI) surface coating with considerably higher corrosion protection compared to yellow electrogalvanizing.

Headform

Countersunk

Drive

Hexalobular socket

Thread

fully threaded

Brand

SPAX®

Material

Steel

Material execution

case-hardened

Surface

WIROX® added lubricant

Version

with 4CUT point

Certificates



Warnings

ISO 4042

Quenched and tempered fasteners  $\geq 360$  HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!

Further notice to residual risks can be found in the introduction section.

Article no	p	d1	L	d2	k max	Hexalobular socket	b~
3336938	200	3	12	6	1.8	T10	10
3373525	1000	3	12	6	1.8	T10	10

Article no	p	d1	L	d2	k max	Hexalobular socket	b~
3336939	200	3	16	6	1.8	T10	14
3336897	1000	3	16	6	1.8	T10	14
3336940	200	3	20	6	1.8	T10	17
3336898	1000	3	20	6	1.8	T10	17
3336941	200	3	25	6	1.8	T10	21
3336899	1000	3	25	6	1.8	T10	21
3336942	200	3	30	6	1.8	T10	26
3336900	1000	3	30	6	1.8	T10	26
3702540	1000	3.5	12	7	2.1	T20	10
3620427	1000	3.5	15	7	2.1	T20	11
3336943	200	3.5	16	7	2.1	T20	13
3336901	1000	3.5	16	7	2.1	T20	13
3336945	200	3.5	20	7	2.1	T20	16
3336902	1000	3.5	20	7	2.1	T20	16
3336946	200	3.5	25	7	2.1	T20	21
3336903	1000	3.5	25	7	2.1	T20	21
3336947	200	3.5	30	7	2.1	T20	25
3336904	1000	3.5	30	7	2.1	T20	25
3336948	200	3.5	35	7	2.1	T20	30
3336905	1000	3.5	35	7	2.1	T20	30
3336949	200	3.5	40	7	2.1	T20	35
3336906	1000	3.5	40	7	2.1	T20	35
3336950	200	3.5	45	7	2.1	T20	40
3336907	1000	3.5	45	7	2.1	T20	40
3336908	1000	4	15	8	2.4	T20	11
3510222	200	4	16	8	2.4	T20	13
3336909	1000	4	16	8	2.4	T20	13
3336911	1000	4	20	8	2.4	T20	16
3336951	200	4	25	8	2.4	T20	21
3336913	1000	4	25	8	2.4	T20	21
3336952	200	4	30	8	2.4	T20	25
3336915	1000	4	30	8	2.4	T20	25
3336953	200	4	35	8	2.4	T20	30
3336916	1000	4	35	8	2.4	T20	30
3336954	200	4	40	8	2.4	T20	35
3336917	1000	4	40	8	2.4	T20	35
3336955	200	4	45	8	2.4	T20	40
3336918	500	4	45	8	2.4	T20	40
3336956	200	4	50	8	2.4	T20	45
3336919	500	4	50	8	2.4	T20	45
3543606	1000	4.5	16	8.8	2.7	T20	13
3373526	1000	4.5	20	8.8	2.7	T20	15
3373527	1000	4.5	25	8.8	2.7	T20	20
3373528	1000	4.5	30	8.8	2.7	T20	25
3336957	200	4.5	35	8.8	2.7	T20	30
3336920	500	4.5	35	8.8	2.7	T20	30
3336958	200	4.5	40	8.8	2.7	T20	34
3336921	500	4.5	40	8.8	2.7	T20	34
3336959	200	4.5	45	8.8	2.7	T20	39
3336922	500	4.5	45	8.8	2.7	T20	39

Article no	p	d1	L	d2	k max	Hexalobular socket	b~
3336960	200	4.5	50	8.8	2.7	T20	44
3336923	500	4.5	50	8.8	2.7	T20	44
3336962	100	4.5	60	8.8	2.7	T20	54
3336924	500	4.5	60	8.8	2.7	T20	54
3336963	100	4.5	70	8.8	2.7	T20	59
3336925	500	4.5	70	8.8	2.7	T20	59
3373529	1000	5	20	9.7	2.9	T20	15
3373530	1000	5	25	9.7	2.9	T20	20
3373531	500	5	30	9.7	2.9	T20	25
3373532	500	5	35	9.7	2.9	T20	30
3336965	200	5	40	9.7	2.9	T20	35
3336926	500	5	40	9.7	2.9	T20	35
3336966	200	5	45	9.7	2.9	T20	39
3336927	500	5	45	9.7	2.9	T20	39
3336967	200	5	50	9.7	2.9	T20	44
3336928	500	5	50	9.7	2.9	T20	44
3336968	100	5	60	9.7	2.9	T20	54
3336929	500	5	60	9.7	2.9	T20	54
3336969	100	5	70	9.7	2.9	T20	61
3336930	200	5	70	9.7	2.9	T20	61
3336970	100	5	80	9.7	2.9	T20	61
3336931	200	5	80	9.7	2.9	T20	61
3336971	100	6	50	11.6	3.4	T30	43
3336932	200	6	50	11.6	3.4	T30	43
3336973	100	6	60	11.6	3.4	T30	53
3336934	200	6	60	11.6	3.4	T30	53
3336975	100	6	70	11.6	3.4	T30	61
3336935	200	6	70	11.6	3.4	T30	61
3336976	100	6	80	11.6	3.4	T30	61
3336936	200	6	80	11.6	3.4	T30	61