





### **Accelerometers**

Murata is the global market leader in low-g acceleration sensors for automotive applications. The extensive accelerometer product range includes high performance analog and digital accelerometers for both safety critical automotive and industrial applications.

Murata accelerometers are based on the company's proprietary 3D MEMS technology and offer a number of excellent product features for the most demanding applications. The sensing element and the measuring ASIC are assembled in dual flat lead plastic package with pins for the surface mount and reflow soldering. They are environmentally protected with silicone gel, resulting in excellent performance and reliability in humid environments and at temperature cycling. In addition, the robust sensing element design with over damped frequency response enables excellent performance even in harsh and vibrating environments.

Series	No. of axes	Range	Supply voltage	Temperature range	Sensitivity	Signal bandwidth	Output type	Typical applications
SCA800	1	±2 g	3.3 V	-40 +125 °C	900 LSB/g	50 Hz	Digital/SPI	
SCA2100	2	±2 g	3.3 V	-40 +125 °C	900 LSB/g	45 Hz	Digital/SPI	Automotive safety critical applications, IMU, Industrial
SCA3100	3	±2 g ±6 g	3.3 V	-40 +125 °C	900 LSB/g 650 LSB/g	45 Hz	Digital/SPI	applications
SCA3300	3	±3 g ±6 g ±1.5 g	3.3 V	-40 +125 °C	2700 LSB/g 1350 LSB/g 5400 LSB/g	70 Hz 70 Hz 70 Hz/10Hz*	Digital/SPI	

<sup>\*</sup> user selectable via SPI bus



## Inclinometers

Murata inclination sensors are an optimum choice for high accuracy leveling and inclination measurement instruments. Highest accuracy 3-axis inclination measurement is available with Murata's SCL3300. This sensor also features direct inclination angle output making it a perfect choice for variety of different use cases and applications.

With the best shock durability available on the MEMS market, Murata inclinometers provide trouble-free measurements in moving machines, vehicles, airplanes, construction machines and handheld devices.

Series	No. of axes	Range	Supply voltage	Temperature range	Sensitivity	Signal bandwidth	Output type	Typical applications
SCA830	1	±90°, ±1 g	3.3 V	-40 +125 °C	32000 LSB/g	6.25 Hz	Digital/SPI	Levelling, Tilt sensing, Machine control, Structural health
SCL3300	3	±1.8g/±90° ±3.6g/±90° - /±10°	3.3 V	-40 +125 °C	6000 LSB/g/*182 LSB/° 3000 LSB/g/*182 LSB/° 12000 LSB/g/*182 LSB/°	40 Hz 70 Hz 10 Hz	Digital/SPI	monitoring, Inertial measurement units (IMUs), Robotics, Positioning and guidance systems

<sup>\*</sup> Inclination output

Murata Electronics Oy's product range also includes inclination modules and sub-assemblies. For more information, please refer to the product datasheets available online at **www.murata.com** 





# Gyroscopes

Murata develops and manufactures gyroscope components based on the company's proven 3D MEMS technology and highly integrated electronics.

Industrial gyros offer a performance level that typically has been available only for expensive module products. The sensing elements and measuring circuitry are assembled into a premolded plastic dual-in-line (DIL) package, protected with silicon gel and covered with a stainless steel lid. All products are RoHS compatible and suitable for lead-free reflow soldering.

Series	No. of axes	Range	Supply voltage	Temperature range	Sensitivity	Signal bandwidth	Output type	Typical applications
SCC1300	07	±100°/s, ±2 g ±300°/s, ±6 g	5 V analog 3.3 V digital	-40 +125 °C	50 LSB/(°/s), 1800 LSB/g, 18 LSB/(°/s), 650 LSB/g	50 Hz	Digital/SPI	Platform
SCR1100	X-axis gyro	±100 °/s ±300 °/s	5 V analog 3.3 V digital	-40 +125 °C	50 LSB/(°/s) 18 LSB/(°/s)	50 Hz	Digital/SPI	stabilization, Motion analysis
SCC2130	X-axis gyro 3-axis accelerometer	±125°/s, ±6 g	3.3 V	-40 +125 °C	50 LSB/(°/s) 1962 LSB/g	60 Hz/10 Hz*	Digital/SPI	and control, Guidance and
SCR2100	X-axis gyro	±125 °/s	3.3 V	-40 +125 °C	50 LSB/g	60 Hz/10 Hz*	Digital/SPI	navigation systems
SCC2230	0,	±125°/s, ±6 g ±125°/s, ±2 g	3.3 V	-40 +125 °C	50 LSB/(°/s) 1962 LSB/g (6 g) 5886 LSB/g (2 g)	60 Hz/10 Hz*	Digital/SPI	3,3,5,6,1113

<sup>\*</sup> User selectable via SPI bus



# Pressure Sensing Elements

Murata SCB10H capacitive absolute pressure sensing elements have been designed for applications that require a small size and ultra low power consumption. The SCB10H pressure sensing elements are ideal for implantable medical devices thanks to their inherent accuracy, reliability, small size and enabled low power consumption.

The SCB10H pressure sensing element allows the possibility for volume OEM customers to integrate pressure measurement functions in an optimal way into their products.

					Typical
Parameter	Unit	B012	B080	B250	applications
Measuring range	kPa	30-120	100-800	100-2500	
Capacitance at min. pressure	pF	7.8	7.5	7.3	Medical devices.
Capacitance at max. pressure	рF	11.8	13.4	13.9	Flow meters,
Capacitance dynamics	рF	4.0	5.9	6.6	Barometers, Altimeters
Sensitivity	fF/kPa	55 (@100 kPa)	6.2 (@350 kPa)	1.3 (@100 kPa) 6.5 (@2500 kPa)	, terriocord

For more information, please refer to the product datasheets available online at www.murata.com



# Global Locations

For details please visit www.murata.com



#### **⚠** Note

### 1 Export Control

#### For customers outside Japan:

No Murata products should be used or sold, through any channels, for use in the design, development, production, utilization, maintenance or operation of, or otherwise contribution to (1) any weapons (Weapons of Mass Destruction [nuclear, chemical or biological weapons or missiles] or conventional weapons) or (2) goods or systems specially designed or intended for military end-use or utilization by military end-users.

### For customers in Japan:

For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.

- 2 Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.
  - Aircraft equipment
  - Aerospace equipment
  - 3 Undersea equipment
  - Power plant equipment
  - Medical equipment
  - (6) Transportation equipment (vehicles, trains, ships, etc.)
  - (7) Traffic signal equipment
  - (3) Disaster prevention / crime prevention equipment
  - Data-processing equipment
  - Application of similar complexity and/or reliability requirements to the applications listed above

- 3 Product specifications in this catalog are as of December 2018. They are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.
- 4 Please read rating and \(\Delta\)CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
- This catalog has only typical specifications.
  Therefore, please approve our product
  specifications or transact the approval sheet
  for product specifications before ordering.
- Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.
- 7 No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.

Murata Manufacturing Co., Ltd.

www.murata.com



## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Murata:

SCA61T-FAHH1G-1 SCA61T-FA1H1G-1 SCA830-D07-1 SCA100T-D01-1 SCA100T-D02-1 SCA610-E23H1A-1 SCA620-EF1V1B-1 SCA820-D04-1 SCA830-D06-1 SCA100T-D07-1 SCA3060-D01-1 SCA3100-D04-1 SCA3100-D07-1 SCC1300-D02-05 SCC1300-D04-05 SCA3100-D04 PWB SCA3100-D04 DEMO SCA1020-D02-1 SCA1020-D02-6 SCA2100-D02-1 SCA100T-D02-6 SCA1000-D01-1 SCA100T-D01-6 SCA2100-D02-10 SCA610-E23H1A-6 SCA100T-D07-6 SCC1300-D02-6 SCA620-EF1V1B-6 SCA820-D04-10 SCA830-D06-10 SCA830-D07-10 SCR1100-D04-05 SCC1300-D02-EMO SCC1300-D04 PWB SCC1300-D04-6 SCC1300-D04-EMO SCL1700-D01 SCR1100-D02-05 SCR1100-D02-6 SCA3060-D01 DEMO SCR1100-D04-6 SCC1300-D02 PWB SCA61T-FAHH1G-6 SCA3060-D02-10 SCA3060-D02-1 SCA3060-D01-10 SCA3060-D01 PWB SCA3100-D04-10 SCA61T-FAHH1G-6 SCA610-CAHH1G-1 SCA610-CA1H1G-1 SCA610-C23H1A-6 SCA610-C23H1A-1 SCA610-CA1H1G-6 SCA610-CAHH1G-6 SCA3100-D07-10 SCA1000-N1000070-6 SCA1000-N1000070-1 SCA2120-D06-1 SCA2120-D06-10 SCA620-EF8H1A-1 SCA610-E28H1A-1 SCA610-E28H1A-6 SCA620-EF8H1A-6 SCA720-D01-1 SCA720-D01-10 SCA2100-D02-PCB SCA330-D06-PCB SCA1100-D04-PCB SCA300-D07-PCB SCA300-D07-PCB SCA3100-D04-PCB SCA3100-D04-PCB SCA330-D07-PCB SCA3100-D04-PCB SCA330-D07-PCB SCA330-D07-PCB SCA330-D07-PCB SCA330-D07-PCB SCA330-D07-PCB SCA330-D04-PCB SCA330-D07-PCB SCA330-D07-PCB