

EMILY-WWW

 ${\sim}60^\circ$ wide beam. 13.43 mm high lens. Modified version to fit CREE XM-L LEDs.

TECHNICAL SPECIFICATIONS:

Dimensions	Ø 26.0 mm
Height	13.4 mm
Fastening	tape
Colour	clear
Box size	480 x 280 x 300 mm
Box weight	8.9 kg
Quantity in Box	1690 pcs
ROHS compliant	yes 🛈




MATERIAL SPECIFICATIONS:

Component EMILY-WWW SPUTNIK-TAPE **Type** Single lens Tape Material PMMA PU tape Colour

black






LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.



PHOTOMETRIC DATA (MEASURED):





PHOTOMETRIC DATA (MEASURED):

CREE LED FWHM Efficiency Peak intensity LEDs/each optic Light colour Required compor	XP-L HD 66.0° 83 % 0.710 cd/lm 1 White	30°
CREE LED FWHM Efficiency Peak intensity LEDs/each optic Light colour Required compor	XP-L HI 67.0° 88 % 0.760 cd/lm 1 White	
ED FWHM Efficiency Peak intensity LEDs/each optic Light colour Required compor	NVSW219F 71.0° 91 % 0.680 cd/lm 1 White	
SEQUI SEMICONDUCTOR LED FWHM Efficiency Peak intensity LEDs/each optic Light colour Required compor	White	200 90' 90' 90' 90' 90' 90' 90' 9



PHOTOMETRIC DATA (SIMULATED):

LED XP-L2 FWHM 74.0° Efficiency 94 % Peak intensity 0.710 cd/lm LEDs/each optic 1 Light colour White Required components: 1	90°
LUMILEDS LED LUXEON MZ FWHM 64.0° Efficiency 96 % Peak intensity 0.959 cd/lm LEDs/each optic 1 Light colour White Required components: 1	
LED NV4WB35AM FWHM 66.0° Efficiency 96 % Peak intensity 0.935 cd/lm LEDs/each optic 1 Light colour White Required components:	



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Local sales and technical support www.ledil.com/ where_to_buy

Shipping locations Salo, Finland Hong Kong, China

Distribution Partners www.ledil.com/ where_to_buy