


# Datasheet

## Stainless Steel Toggle Latch, 250kgf Op. Tension

RS Stock number [206-4573](#)



### Description:

This design is particularly recommended for equipment liable to vibration. A sprung catch fitted to the inside wall locks the toggle arm down making accidental release difficult. A wedged blade such as a small screw driver should be used to open the spring safety lock.

Suitable for screw fixing using 4 M5 screws

Holes provided for tamper sealing

### Features:

- Dimensions 86 x 40 x 22mm
- Length 86mm
- Material Stainless Steel
- Operating Tension 250kgf
- Spring Loaded Yes

