



THIRD ANGLE PROJECTION

ITEM CODE	RATED VOLTAGE	CAP. μF (*)	DIMENSIONS					MARKING STYLE	FORMING TYPE
			L	T	H	S	d		
ECQE4103 () FW	400VDC	0.01 (103)	10.3	4.3	7.4	7.5	0.6	1	N
" 4123 () FW	"	0.012 (123)	"	4.4	7.5	"	"	"	"
" 4153 () FW	"	0.015 (153)	"	"	"	"	"	"	"
" 4183 () FW	"	0.018 (183)	"	"	"	"	"	"	"
" 4223 () FW	"	0.022 (223)	"	4.8	7.9	"	"	"	"
" 4273 () FW	"	0.027 (273)	"	5.5	8.0	"	"	"	"
" 4333 () FW	"	0.033 (333)	"	6.0	9.0	"	"	"	"
" 4393 () FW	"	0.039 (393)	12.0	4.9	8.0	10.0	"	"	"
" 4473 () FW	"	0.047 (473)	"	5.0	8.3	"	"	"	"
" 4563 () FW	"	0.056 (563)	"	"	10.0	"	"	"	"
" 4683 () FW	"	0.068 (683)	"	5.4	10.5	"	"	"	"
" 4823 () FW	"	0.082 (823)	"	5.8	11.0	"	"	"	"
" 4104 () FW	"	0.1 (104)	"	6.3	12.0	"	"	"	"
" 4124 () FW	"	0.12 (124)	18.5	5.0	10.0	"	"	2	T
" 4154 () FW	"	0.15 (154)	"	"	12.4	"	"	"	"
" 4184 () FW	"	0.18 (184)	"	5.4	12.5	"	"	"	"
" 4224 () FW	"	0.22 (224)	"	5.9	13.0	"	"	"	"
" 4274 () FW	"	0.27 (274)	"	6.5	14.3	"	0.8	"	"
" 4334 () FW	"	0.33 (334)	"	7.0	14.9	"	"	"	"
" 4394 () FW	"	0.39 (394)	"	7.5	15.4	"	"	"	"
" 4474 () FW	"	0.47 (474)	"	7.8	17.0	"	"	"	"
" 4564 () FW	"	0.56 (564)	26.0	6.5	16.0	15.0	"	"	"
" 4684 () FW	"	0.68 (684)	"	7.0	16.5	"	"	"	"
" 4824 () FW	"	0.82 (824)	"	7.9	17.3	"	"	"	"
" 4105 () FW	"	1.0 (105)	"	8.5	18.0	"	"	"	"
" 4125 () FW	"	1.2 (125)	"	9.5	18.9	"	"	"	"
" 4155 () FW	"	1.5 (155)	31.0	"	19.0	22.5	"	"	"
" 4185 () FW	"	1.8 (185)	"	11.0	20.5	"	"	"	"
" 4225 () FW	"	2.2 (225)	"	"	22.0	"	"	"	"

TOL. SYMBOL (J or K)



ITEM CODE NUMBER STRUCTURE



CONSTRUCTION

The capacitor is of non-inductive construction, wound with metallized polyester film dielectric.

The capacitor is enclosed in non-combustible epoxy resin and has two leads.

MARKING

Marking comprises capacitance, capacitance tolerance, rated voltage, manufacturer's trademark (STYLE 2 only) and date code.

PROPERTIES

- Capacitance : See table at 1kHz
- Capacitance tolerance : ±5% (J), ±10% (K) at 1kHz
- Rated voltage : 400VDC Δ (Derating of rated voltage by 1.25%/°C at more than 85°C)
- Withstand voltage : 400VDC x 150% for 60s
- Insulation resistance : $\geq 9000\Omega$ ($C \leq 0.33\mu F$) at 100VDC, 20°C for 60s
 $\geq 3000\Omega \cdot \mu F$ ($C > 0.33\mu F$) at 100VDC, 20°C for 60s
- Dissipation factor : $\leq 1.0\%$ at 1kHz, 20°C
- Category temperature range : Δ From -40°C to +105°C (including temperature rise on unit surface)


DO NOT SCALE DRAWING REVISIONS INDICATED BY Δ ALL DIMENSIONS ARE IN MILLIMETERS

ALTERATION		
ISSUE	DESCRIPTION	DATE
Δ 2	Modification	Jun. 20 2002
Δ 3	Company name changed	Oct. 1 2004
Δ 4	Company name changed	Apr. 1 2005
Δ 5	Company name changed	Apr. 1 2006
Δ 6	Correction: category temperature range (-40°C~+85°C~-40°C~+105°C) Addition: rated voltage (Derating of rated voltage by 1.25%/°C at more than 85°C)	Jan. 22 2008
Δ 7	Company name changed Error correction	Apr. 1 2008
Δ 8	Company name changed	Apr. 1 2012
Δ 9	Company name changed	Apr. 1 2013
Δ 10	Company name changed	Apr. 1 2015

SPECIFICATIONS No.
TE72031Y

Reference

MARKING EXAMPLE



DESIGN	<i>M. Nakagawa</i>
CHECKED	<i>K. Oshiki</i>
APPROVAL	<i>J. Takata</i>
ESTABLISHMENT	Jan. 25. 1994
TYPE NAME	ECQE4*** () FW
NAME	Metallized Polyester Film Capacitor
DRAWING NAME	PRODUCT DRAWING
DRAWING No.	CT-H-401E (1/1)

Toyama Matsue Plant
Device Solutions Business Division
Panasonic Corporation

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[ECQ-E1225JFW](#) [ECQ-E1225KFW](#) [ECQ-E1275JFW](#) [ECQ-E1275KFW](#) [ECQ-E1335JFW](#) [ECQ-E1335KFW](#) [ECQ-](#)
[E1395JFW](#) [ECQ-E1395KFW](#) [ECQ-E1475JFW](#) [ECQ-E1475KFW](#) [ECQ-E1564JFW](#) [ECQ-E1564KFW](#) [ECQ-](#)
[E1565JFW](#) [ECQ-E1565KFW](#) [ECQ-E1684JFW](#) [ECQ-E1684KFW](#) [ECQ-E1685JFW](#) [ECQ-E1685KFW](#) [ECQ-](#)
[E1824JFW](#) [ECQ-E1824KFW](#) [ECQ-E1825JFW](#) [ECQ-E1825KFW](#) [ECQ-E2103JFW](#) [ECQ-E2103KFW](#) [ECQ-](#)
[E2104JFW](#) [ECQ-E2104KFW](#) [ECQ-E2105JFW](#) [ECQ-E2105KFW](#) [ECQ-E2106JFW](#) [ECQ-E2106KFW](#) [ECQ-](#)
[E2123JFW](#) [ECQ-E2123KFW](#) [ECQ-E2124JFW](#) [ECQ-E2124KFW](#) [ECQ-E2125JFW](#) [ECQ-E2125KFW](#) [ECQ-](#)
[E2153JFW](#) [ECQ-E2153KFW](#) [ECQ-E2154JFW](#) [ECQ-E2154KFW](#) [ECQ-E2155JFW](#) [ECQ-E2155KFW](#) [ECQ-](#)
[E2183JFW](#) [ECQ-E2183KFW](#) [ECQ-E2184JFW](#) [ECQ-E2184KFW](#) [ECQ-E2185JFW](#) [ECQ-E2185KFW](#) [ECQ-](#)
[E2223JFW](#) [ECQ-E2223KFW](#) [ECQ-E2224JFW](#) [ECQ-E2224KFW](#) [ECQ-E2225JFW](#) [ECQ-E2225KFW](#) [ECQ-](#)
[E2273JFW](#) [ECQ-E2273KFW](#) [ECQ-E2274JFW](#) [ECQ-E2274KFW](#) [ECQ-E2275JFW](#) [ECQ-E2275KFW](#) [ECQ-](#)
[E2333JFW](#) [ECQ-E2333KFW](#) [ECQ-E2334JFW](#) [ECQ-E2334KFW](#) [ECQ-E2335JFW](#) [ECQ-E2335KFW](#) [ECQ-](#)
[E2393JFW](#) [ECQ-E2393KFW](#) [ECQ-E2394JFW](#) [ECQ-E2394KFW](#) [ECQ-E2395JFW](#) [ECQ-E2395KFW](#) [ECQ-](#)
[E2473JFW](#) [ECQ-E2473KFW](#) [ECQ-E2474JFW](#) [ECQ-E2474KFW](#) [ECQ-E2475JFW](#) [ECQ-E2475KFW](#) [ECQ-](#)
[E2563JFW](#) [ECQ-E2563KFW](#) [ECQ-E2564JFW](#) [ECQ-E2564KFW](#) [ECQ-E2565JFW](#) [ECQ-E2565KFW](#) [ECQ-](#)
[E2683JFW](#) [ECQ-E2683KFW](#) [ECQ-E2684JFW](#) [ECQ-E2684KFW](#) [ECQ-E2685JFW](#) [ECQ-E2685KFW](#) [ECQ-](#)
[E2823JFW](#) [ECQ-E2823KFW](#) [ECQ-E2824JFW](#) [ECQ-E2824KFW](#) [ECQ-E2825JFW](#) [ECQ-E2825KFW](#) [ECQ-](#)
[E4103JFW](#) [ECQ-E4103KFW](#) [ECQ-E4104JFW](#) [ECQ-E4104KFW](#)