

## SAIL-M8BG-3-5.0U

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

### General ordering data

|            |  |
|------------|--|
| Type       | SAIL-M8BG-3-5.0U   |
| Order No.  | <a href="#">9457450500</a>   |
| Version    | Sensor/actuator line, One end without connector, M8, Number of poles : 3, 5 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| GTIN (EAN) | 4032248228263  |
| Qty.       | 1 pc(s).   |

**SAIL-M8BG-3-5.0U****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 108 g

**Temperatures**

Operating temperature, max. 80 °C Operating temperature, min. -25 °C

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Technical specifications for cable**

|                                      |                                  |  |   |
|--------------------------------------|----------------------------------|--|---|
| Number of poles                      | 3                                | Core cross-section                             | 0.25 mm <sup>2</sup>  |
| Outside diameter                     | 4.1 mm ± 0.2 mm                  | Cable length                                   | 5 m   |
| Shielded                             | No                               | Insulation                                     | PP  |
| Colour coding                        | brown, blue, black               | Sheath material                                | PUR   |
| Sheathing colour                     | black                            | Halogen  | No  |
| Temperature range, moving            | -25...80 °C                      | Temperature range, stationary                  | -40...80 °C   |
| Core in accordance with UL AWM style | 10493 (80 °C / 300 V)            | Outer cladding in accordance with UL AWM style | 20233/21198 (80 °C / 300 V)   |
| Suitable for cable carriers          | Yes                              | Torsion resistance                             | 360 °/m   |
| Bending radius, min., stationary     | 5 x cable diameter               | Bending radius, min., moving                   | 10 x cable diameter   |
| Acceleration                         | 5 m/s <sup>2</sup>               | Speed  | 5 m/s   |
| Bending cycles                       | 2 Mio                            | Resistant to welding beads                     | No  |
| Configurable cable length            | No                               | Hydrolysis and microbe resistant               | Yes   |
| Resistance to oils                   |                                  | Resistance to spread of flame                  | In accordance with UL1581 UL/ CUL FT1, in accordance with IEC 60332-1-2, in accordance with IEC 60332-1-3, in accordance with IEC 60332-2-2 |
|                                      | in accordance with IEC 60811:404 |  |   |

**General technical data**

|                              |   |                       |                         |
|------------------------------|---|-----------------------|-------------------------|
| AF size                      | 12 mm                                   | Version               | Female socket, straight |
| Connection thread            | M8                                      | Housing main material | PUR                     |
| Threaded ring material       | Brass, nickel-plated                    | Coding                | none                    |
| Protection degree            | IP65, IP66, IP67, IP68, when screwed in | Contact surface       | Gold-plated             |
| LED                          | No                                      | Rated voltage         | 60 V                    |
| Rated current                | 4 A                                     | Insulation strength   | 10 <sup>8</sup> Ω       |
| Temperature range of housing | -25...+80 °C                            | Tightening torque     | M8: 0.5 - 0.6 Nm        |
| Plugging cycles jumpered     | ≥ 100                                   | Pollution severity    | 3                       |
|                              | No                                      |                       |                         |

**Standards**

Connector standard IEC 61076-2-104 Certificate no. (cULus) E307231

**Classifications**

|             |             |            |             |
|-------------|-------------|------------|-------------|
| ETIM 6.0    | EC001855    | ETIM 7.0   | EC001855    |
| eClass 9.0  | 27-06-03-11 | eClass 9.1 | 27-06-03-11 |
| eClass 10.0 | 27-06-03-11 | UNSPSC     | 26-12-16-13 |

Creation date February 24, 2020 11:11:24 AM CET

Catalogue status 21.02.2020 / We reserve the right to make technical changes.

**Data sheet****SAIL-M8BG-3-5.0U**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Brochure/Catalogue

[CAT 8 SAI 15/16 EN](#)  
[FL FIELDWIRING EN](#)

Engineering Data

[EPLAN, WSCAD, Zuken E3.S](#)


**Data sheet**

**SAIL-M8BG-3-5.0U**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com


**Drawings**

**Dimensioned drawing**



Straight socket

**Pole scheme**



Socket

**Wiring diagram**



**The ideal tool: Screwty® with torque function**



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F