

We measure it.



# Humidity/temperature/pressure measuring instrument

testo 622 – Fast and precise ambient climate monitoring

---

Precise measurement of temperature, humidity and pressure

---

All important values directly at a glance

---

Large, easily legible display

---

Adjustable calibration reminder function (optional)

---



In addition to temperature and humidity, the testo 622 also measures pressure, making it ideal for indoor climate monitoring. It shows the current measurement values as well as date and time in a large, clear display. It thus provides all important values at a glance. Especially in laboratories, the testo 622 is suitable for monitoring ambient conditions during calibrations or when setting up experiments.

Thanks to the long-term stable sensor, the measuring instrument provides reliable and correct measurement results even after years. The hanging and standing bracket allows flexible positioning of the instrument on a table or wall.

Particularly time-saving and user friendly: The calibration and adjustment of the measuring instrument is possible directly on site with the help of the optional calibration and adjustment software.

[www.testo.co.uk](http://www.testo.co.uk)

## Technical data / Accessories

### testo 622

testo 622 hygrometer with pressure display, incl. calibration protocol, batteries and attachment material

Part no. 0560 6220



### General technical data

Measuring rate	10 s
Storage temp.	-20 to +60 °C
Oper. temp.	-10 to +60 °C
Battery life	12 months
Weight	240 g (without batteries)
Dimensions	185 x 105 x 36 mm

### Sensor types

	NTC	Testo humid. sensor, cap.	Piezoresistive pressure sensor
Meas. range	-10 to +60 °C	0 to 100 %RH	300 to 1200 hPa
Accuracy ±1 digit	±0.4 °C	±2 %RH at +25 °C (10 to 90 %RH) ±3 %RH (remaining range)	±3 hPa
Resolution	0.1 °C	0.1 %RH	0.1 hPa

### Accessories

### Part no.

#### Accessories for measuring instrument

	Part no.
Calibration and adjustment software with USB cable for testo 622/623	0554 6230
ISO calibration certificate humidity	0520 0006
DAkkS calibration certificate/humidity	0520 0206