UBA2014

600 V driver IC for HF fluorescent lamps

Rev. 04 — 16 October 2008

Product data sheet

1. General description

The IC is a monolithic integrated circuit for driving electronically ballasted fluorescent lamps, with mains voltages up to 277 V (RMS) (nominal value).

The circuit is made in a 650 V Bipolar CMOS DMOS (BCD) power-logic process. It provides the drive function for the two discrete power MOSFETs.

Besides the drive function, the IC also includes the level-shift circuit, the oscillator function, a lamp voltage monitor, a current control function, a timer function and protections.

2. Features

- Adjustable preheat time
- Adjustable preheat current
- Current controlled operating
- Single ignition attempt
- Adaptive non-overlap time control
- Integrated high-voltage level-shift function
- Power-down function
- Protection against lamp failures or lamp removal
- Capacitive mode protection

3. Applications

■ The circuit topology enables a broad range of ballast applications at different mains voltages for driving lamp types from T8, T5, PLC, T10, T12, PLL and PLT, for example.



600 V driver IV for HF fluorescent lamps

4. Quick reference data

Table 1. Quick reference data

 V_{DD} = 13 V; V_{FVDD} – V_{SH} = 13 V; T_{amb} = 25 °C; all voltages are referenced to GND; see test circuit of <u>Figure 8</u>; unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Start-up state	е					
V _{DD(stop)}	oscillator stop supply voltage		8.6	9.1	9.6	V
V _{DD(start)}	oscillator start supply voltage		12.4	13.0	13.6	V
I _{DD(start)}	oscillator start-up supply current	$V_{DD} < V_{DD(start)}$	-	170	200	μΑ
High-voltage	supply					
V_{HS}	high-side supply voltage	I _{HS} < 30 μA	-	-	570	V
Reference vo	oltage					
V_{VREF}	reference voltage	$I_L = 10 \mu A$	2.86	2.95	3.04	V
Voltage cont	rolled oscillator					
f_{max}	maximum bridge frequency		90	100	110	kHz
f_{min}	minimum bridge frequency		38.9	40.5	42.1	kHz
High-side ou	tput driver					
I _{o(source)}	output source current	$V_{GH} - V_{SH} = 0 V$	135	180	235	mA
I _{o(sink)}	output sink current	$V_{GH} - V_{SH} = 13 \text{ V}$	265	330	415	mA
Preheat curre	ent sensor					
V_{ph}	preheat voltage		0.57	0.60	0.63	V
Lamp voltage	e sensor					
$V_{lamp(fail)}$	lamp fail voltage		0.77	0.81	0.85	V
$V_{lamp(max)}$	maximum lamp voltage		1.44	1.49	1.54	V
Average curr	ent sensor					
V _{offset}	offset voltage	$V_{CSP} = V_{CSN} = 0 \text{ V to } 2.5 \text{ V}$	-2	0	+2	mV
g _m	transconductance	f = 1 kHz	1900	3800	5700	μA/mV
Preheat time	r					
t_{ph}	preheat time	C_{CT} = 330 nF; R_{IREF} = 33 k Ω	1.6	1.8	2.0	S
V_{OL}	LOW-level output voltage		-	1.4	-	V
V _{OH}	HIGH-level output voltage		-	3.6	-	V

5. Ordering information


Table 2. Ordering information

Type number	Package	Package							
	Name	Description	Version						
UBA2014T	SO16	plastic small outline package; 16 leads; body width 3.9 mm	SOT109-1						
UBA2014P	DIP16	plastic dual in-line package; 16 leads (300 mil); long body	SOT38-1						

UBA2014_4 © NXP B.V. 2008. All rights reserved.

600 V driver IV for HF fluorescent lamps

3 of 19



UBA2014_4 © NXP B.V. 2008. All rights reserved. Rev. 04 — 16 October 2008


Block diagram

6.

600 V driver IV for HF fluorescent lamps

Pinning information

7.1 Pinning



7.2 Pin description

Table 3. Pin description

Symbol	Pin	Description
CT	1	preheat timer output
CSW	2	input of voltage controlled oscillator
CF	3	voltage controlled oscillator output
IREF	4	internal reference current input
GND	5	ground
GL	6	gate output for the low-side switch
V_{DD}	7	low-voltage supply
PCS	8	preheat current sensor input
FV_{DD}	9	floating supply voltage; supply for high-side switch
GH	10	gate output for the high-side switch
SH	11	source for the high-side switch
ACM	12	capacitive mode input
LVS	13	lamp voltage sensor input
VREF	14	reference voltage output
CSP	15	positive input for the average current sensor
CSN	16	negative input for the average current sensor
-		

Product data sheet

4 of 19

600 V driver IV for HF fluorescent lamps

Functional description 8.

8.1 Start-up state

Initial start-up can be achieved by charging the low-voltage supply capacitor C7 (see Figure 8) via an external start-up resistor. Start-up of the circuit is achieved under the condition that both half bridge transistors TR1 and TR2 are non-conductive. The circuit will be reset in the start-up state. If the low-voltage supply (V_{DD}) reaches the value of V_{DD(start)} the circuit will start oscillating. A DC reset circuit is incorporated in the High-Side (HS) driver. Below the lockout voltage at the FV_{DD} pin the output voltage (V_{GH} – V_{SH}) is zero. The voltages at pins CF and CT are zero during the start-up state.

8.2 Oscillation

The internal oscillator is a Voltage Controlled Oscillator (VCO) circuit which generates a sawtooth waveform between the V_{CF(high)} level and 0 V. The frequency of the sawtooth is determined by capacitor CCF, resistor RIREF, and the voltage at pin CSW. The minimum and maximum switching frequencies are determined by RIRFF and CCF; their ratio is internally fixed. The sawtooth frequency is twice the half bridge frequency. The UBA2014 brings the transistors TR1 and TR2 into conduction alternately with a duty cycle of approximately 50 %. An overview of the oscillator signal and driver signals is illustrated in Figure 4. The oscillator starts oscillating at f_{max}. During the first switching cycle the Low-Side (LS) transistor is switched on. The first conducting time is made extra long to enable the bootstrap capacitor to charge.

8.3 Adaptive non-overlap

The non-overlap time is realized with an Adaptive Non-overlap circuiT (ANT). By using an adaptive non-overlap circuit, the application can determine the duration of the non-overlap time and make it optimum for each frequency; see Figure 4. The non-overlap time is determined by the slope of the half bridge voltage, and is detected by the signal across resistor R16 which is connected directly to pin ACM. The minimum non-overlap time is internally fixed. The maximum non-overlap time is internally fixed at approximately 25 % of the bridge period time. An internal filter of 30 ns is included at the ACM pin to increase the noise immunity.

8.4 Timing circuit

A timing circuit is included to determine the preheat time and the ignition time. The circuit consists of a clock generator and a counter.

The preheat time is defined by C_{CT} and R_{IREF} and consists of 7 pulses at C_{CT}; the maximum ignition time is 1 pulse at C_{CT}. The timing circuit starts operating after the start-up state, as soon as the low supply voltage (V_{DD}) has reached V_{DD(start)} or when a critical value of the lamp voltage (V_{lamp(fail)}) is exceeded. When the timer is not operating C_{CT} is discharged to 0 V at 1 mA.

UBA2014 4 Rev. 04 — 16 October 2008

Product data sheet

5 of 19

600 V driver IV for HF fluorescent lamps

8.5 Preheat state

After starting at f_{max} , the frequency decreases until the momentary value of the voltage across sense resistor R14 reaches the internally fixed preheat voltage level (pin PCS). At crossing the preheat voltage level, the output current of the Preheat Current Sensor (PCS) circuit discharges the capacitor C_{CSW} , thus raising the frequency. The preheat time begins at the moment that the circuit starts oscillating. During the preheat time the Average Current Sensor (ACS) circuit is disabled. An internal filter of 30 ns is included at pin PCS to increase the noise immunity.

8.6 Ignition state

After the preheat time the ignition state is entered and the frequency will sweep down due to charging of the capacitor at pin CSW with an internally fixed current; see <u>Figure 5</u>. During this continuous decrease in frequency, the circuit approaches the resonant frequency of the load. This will cause a high voltage across the load, which normally ignites the lamp. The ignition voltage of a lamp is designed above the $V_{lamp(fail)}$ level. If the lamp voltage exceeds the $V_{lamp(fail)}$ level the ignition timer is started.

8.7 Burn state

If the lamp voltage does not exceed the $V_{lamp(max)}$ level the voltage at pin CSW will continue to increase until the clamp level at pin CSW is reached; see <u>Figure 5</u>. As a consequence the frequency will decrease until the minimum frequency is reached.

When the frequency reaches its minimum level it is assumed that the lamp has ignited and the circuit will enter the burn state. The ACS circuit will be enabled. As soon as the averaged voltage across sense resistor R14, measured at pin CSN, reaches the reference level at pin CSP, the average current sensor circuit will take over the control of the lamp current. The average current through R14 is transferred to a voltage at the voltage controlled oscillator and regulates the frequency and, as a result, the lamp current.

8.8 Lamp failure mode

8.8.1 During ignition state

If the lamp does not ignite, the voltage level increases. When the lamp voltage exceeds the $V_{lamp(max)}$ level, the voltage will be regulated at the $V_{lamp(max)}$ level; see <u>Figure 6</u>. When the $V_{lamp(fail)}$ level is crossed the ignition timer has already started. If the voltage at pin LVS is above the $V_{lamp(fail)}$ level at the end of the ignition time the circuit stops oscillating and is forced into the Power-down mode. The circuit will be reset only when the supply voltage is powered down.

8.8.2 During burn state

If the lamp fails during normal operation, the voltage across the lamp will increase and the lamp voltage will exceed the $V_{lamp(fail)}$ level; see <u>Figure 7</u>. At that moment the ignition timer is started. If the lamp voltage increases further it will reach the $V_{lamp(max)}$ level. This forces the circuit to reenter the ignition state and results in an attempt to re-ignite the lamp. If during restart the lamp still fails, the voltage remains high until the end of the ignition time. At the end of the ignition time the circuit stops oscillating and the circuit will enter the Power-down mode.

UBA2014_4 © NXP B.V. 2008. All rights reserved

600 V driver IV for HF fluorescent lamps

8.9 Power-down mode

The Power-down mode will be entered if, at the end of the ignition time, the voltage at pin LVS is above V_{lamp(fail)}. In the Power-down mode the oscillator will be stopped and both TR1 and TR2 will be non-conductive. The V_{DD} supply is internally clamped. The circuit is released from the Power-down mode by lowering the low-voltage supply below V_{DD(reset)}.

8.10 Capacitive mode protection

The signal across R16 also gives information about the switching behavior of the half bridge. If, after the preheat state, the voltage across the ACM resistor (R16) does not exceed the V_{CMD} level during the non-overlap time, the Capacitive Mode Detection (CMD) circuit assumes that the circuit is in the capacitive mode of operation. As a consequence the frequency will directly be increased to f_{max}. The frequency behavior is decoupled from the voltage at pin CSW until C_{CSW} has been discharged to zero.

8.11 Charge coupling

Due to parasitic capacitive coupling to the high voltage circuitry all pins are burdened with a repetitive charge injection. Given the typical application the pins IREF and CF are sensitive to this charge injection. For charge coupling of approximately 8 pC, a safe functional operation of the IC is guaranteed, independent of the current level.

Charge coupling at current levels below 50 µA will not interfere with the accuracy of the V_{CS} , V_{PCS} and V_{ACM} levels.

Charge coupling at current levels below 20 µA will not interfere with the accuracy of any parameter.

8.12 Design equations

The following design equations are used to calculate the desired preheat time, the maximum ignition time, and the minimum and the maximum switching frequency.

$$t_{ph} = 1.8 \times \frac{C_{CT}}{330 \times 10^{-9}} \times \frac{R_{IREF}}{33 \times 10^{3}} \tag{1}$$

$$t_{ign} = 0.26 \times \frac{C_{CT}}{330 \times 10^{-9}} \times \frac{R_{IREF}}{33 \times 10^{3}}$$
 (2)


$$f_{min} = 40.5 \times 10^3 \times \frac{100 \times 10^{-12}}{C_{CF}} \times \frac{33 \times 10^3}{R_{IREF}}$$
 (3)


$$f_{max} = 2.5 \times f_{min} \tag{4}$$

Start of ignition is defined as the moment at which the measured lamp voltage crosses the V_{lamp(fail)} level; see Section 8.8.

UBA2014 4

600 V driver IV for HF fluorescent lamps







Product data sheet

Downloaded from Arrow.com.

600 V driver IV for HF fluorescent lamps





600 V driver IV for HF fluorescent lamps

9. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). All voltages referenced to GND.

Symbol	Parameter	Conditions	Min	Max	Unit
V_{HS}	high-side supply voltage	I_{HS} < 30 μ A; t < 1 s	-	600	V
		I _{HS} < 30 μA	-	570	V
V_{VDD}	voltage at pin V _{DD}		-	14	V
V_{ACM}	voltage at pin ACM		– 5	+5	V
V_{PCS}	voltage at pin PCS		– 5	+5	V
V _{LVS}	voltage at pin LVS		0	5	V
V_{CSP}	voltage at pin CSP		0	5	V
V_{CSN}	voltage at pin CSN		-0.3	+5	V
V_{CSW}	voltage at pin CSW		0	5	V
T _{amb}	ambient temperature		-25	+80	°C
Tj	junction temperature		-25	+150	°C
T _{stg}	storage temperature		– 55	+150	°C
V _{esd}	electrostatic discharge voltage				
	pins FV _{DD} , GH and SH		<u>[1]</u> –1000	+1000	V
	pins CT, CSW, CF, IREF, GL, V _{DD} , PCS, CSN, CSP, VREF, LVS and ACM		<u>[1]</u> –2500	+2500	V

^[1] In accordance with the human body model, i.e. equivalent to discharging a 100 pF capacitor through a 1.5 $k\Omega$ series resistor.

10. Thermal characteristics

Table 5. Thermal characteristics

Symbol	Parameter	Conditions	Тур	Unit
$R_{th(j-a)}$	thermal resistance from junction to ambient	in free air		
	SO16		100	K/W
	DIP16		60	K/W
R _{th(j-pin)}	thermal resistance from junction to pin	in free air		
	SO16		50	K/W
	DIP16		30	K/W

UBA2014_4 © NXP B.V. 2008. All rights reserved.

600 V driver IV for HF fluorescent lamps

11. Characteristics

Table 6. Characteristics

 V_{DD} = 13 V; V_{FVDD} – V_{SH} = 13 V; T_{amb} = 25 °C; all voltages referenced to GND; see test circuit of <u>Figure 8</u>; unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Start-up st	ate: pin V _{DD}					
V_{DD}	supply voltage	TR1 = off; TR2 = off	-	-	6	V
V _{DD(reset)}	reset supply voltage	TR1 = off; TR2 = off	4.5	5.5	7.0	V
V _{DD(stop)}	oscillator stop supply voltage		8.6	9.1	9.6	V
V _{DD(start)}	oscillator start supply voltage		12.4	13.0	13.6	V
$V_{\rm DD(hys)}$	start-stop hysteresis supply voltage		3.5	3.9	4.4	V
V _{DD(clamp)}	clamp supply voltage	Power-down mode	10	11	12	V
I _{DD(start)}	start-up supply current	$V_{DD} < V_{DD(start)}$	-	170	200	μΑ
I _{DD(pd)}	power-down supply current	$V_{DD} = 9 V$	-	170	200	μΑ
I _{DD}	supply current	f _{bridge} = 40 kHz without gate drive	-	1.5	2.2	mA
High-volta	ge supply: pins GH, SH and FV _{DD}					
IL	latching current	600 V at high-voltage pins	-	-	30	μΑ
Reference	voltage: pin VREF					
V _{ref}	reference voltage	$I_L = 10 \mu A$	2.86	2.95	3.04	V
ΔV_{VREF}	reference voltage stability	I _L = 10 μA; T _{amb} = 25 °C to 150 °C	-	-0.64	-	%
I _{source}	source current		1	-	-	mA
I _{sink}	sink current		1	-	-	mA
Z _o	output impedance	I _L = 1 mA source	-	3.0	-	Ω
Current su	pply: pin IREF					
VI	input voltage		-	2.5	-	V
l _l	input current		65	-	95	μΑ
Voltage co	ntrolled oscillator					
Output: pin	CSW					
Vo	output control voltage		2.7	3.0	3.3	V
V _{clamp}	clamp voltage	burn state	2.8	3.1	3.4	V
	trolled oscillator output: pin CF					
f _{max}	maximum frequency		90	100	110	kHz
f _{min}	minimum frequency		38.9	40.5	42.1	kHz
Δf_{stab}	frequency stability	$T_{amb} = -20 ^{\circ}\text{C} \text{ to } +80 ^{\circ}\text{C}$	-	1.3	-	%
t _{start}	first output oscillator stroke time		-	50	-	μs
t _{no(min)}	minimum non-overlap time	GH to GL	0.68	0.90	1.13	μs
` '		GL to GH	0.75	1.00	1.25	μs
t _{no(max)}	maximum non-overlap time	f _{bridge} = 40 kHz	[1] _	7.5	-	μs
V _{CF(high)}	high-level oscillator output voltage	$f = f_{min}$	-	2.5	-	V

 UBA2014_4
 © NXP B.V. 2008. All rights reserved.

 Product data sheet
 Rev. 04 — 16 October 2008
 11 of 19

600 V driver IV for HF fluorescent lamps

12 of 19

Characteristics ... continued

 V_{DD} = 13 V; V_{FVDD} – V_{SH} = 13 V; T_{amb} = 25 °C; all voltages referenced to GND; see test circuit of Figure 8; unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
I _{o(start)}	oscillator output start current	V _{CF} = 1.5 V	3.8	4.5	5.2	μΑ
I _{o(min)}	minimum oscillator output current	V _{CF} = 1.5 V	-	21	-	μΑ
I _{o(max)}	maximum oscillator output current	V _{CF} = 1.5 V	-	54	-	μΑ
Output driv	ers					
High-side dr	iver output: pin GH					
V _{OH}	HIGH-level output voltage	I _o = 10 mA	12.5	-	-	V
V _{OL}	LOW-level output voltage	I _o = 10 mA	-	-	0.5	V
I _{o(source)}	output source current	$V_{GH} - V_{SH} = 0 V$	135	180	235	mA
I _{o(sink)}	output sink current	$V_{GH} - V_{SH} = 13 \text{ V}$	265	330	415	mA
R _{on}	on resistance	I _o = 10 mA	32	39	45	Ω
R _{off}	off resistance	I _o = 10 mA	16	21	26	Ω
Low-side dri	ver output: pin GL					
V _{OH}	HIGH-level output voltage	I _o = 10 mA	12.5	-	-	V
V_{OL}	LOW-level output voltage	I _o = 10 mA	-	-	0.5	V
I _{o(source)}	output source current	$V_{GL} = 0$	135	200	235	mA
I _{o(sink)}	output sink current	V _{GL} = 13 V	265	330	415	mA
R _{on}	on resistance	I _o = 10 mA	32	39	45	Ω
R _{off}	off resistance	$I_0 = 10 \text{ mA}$	16	21	26	Ω
Floating sup	ply voltage: pin FV _{DD}					
V_{FVDD}	lockout voltage		2.8	3.5	4.2	V
I _{FVDD}	floating well supply current	DC level at $V_{GH} - V_{SH} = 13 \text{ V}$	-	35	-	μΑ
Bootstrap die	ode					
V _{boot}	bootstrap diode forward drop voltage	I = 5 mA	1.3	1.7	2.1	V
Preheat cur	rent sensor					
Input: pin PC	CS					
li	input current	$V_{PCS} = 0.6 V$	-	-	1	μΑ
V_{ph}	preheat voltage		0.57	0.60	0.63	V
Output: pin (CSW					
I _{o(source)}	output source current	$V_{CSW} = 2.0 \text{ V}$	9.0	10	11	μΑ
I _{o(sink)}	output sink current	V _{CSW} = 2.0 V	-	10	-	μΑ
Adaptive no	on-overlap and capacitive mode d	etection; pin ACM				
li	input current	$V_{ACM} = 0.6 V$	-	-	1	μΑ
V _{CMDP}	positive capacitive mode detection voltage		80	100	120	mV
V_{CMDN}	negative capacitive mode detection voltage		-68	-85	-102	mV

UBA2014_4 © NXP B.V. 2008. All rights reserved. Rev. 04 — 16 October 2008

600 V driver IV for HF fluorescent lamps

 Table 6.
 Characteristics ...continued

 V_{DD} = 13 V; V_{FVDD} – V_{SH} = 13 V; T_{amb} = 25 °C; all voltages referenced to GND; see test circuit of <u>Figure 8</u>; unless otherwise specified.


Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Lamp voltage	ge sensor					
Input: pin LV	'S					
l _i	input current	$V_{LVS} = 0.81 \text{ V}$	-	-	1	μΑ
V _{lamp(fail)}	lamp fail voltage		0.77	0.81	0.85	V
V _{lamp(fail)(hys)}	lamp fail hysteresis voltage		119	144	169	mV
$V_{lamp(max)}$	maximum lamp voltage		1.44	1.49	1.54	V
Output: pin (СТ					
I _{o(sink)}	output sink current	$V_{CSW} = 2.0 \text{ V}$	27	30	33	μΑ
I _{o(source)}	ignition output source current	$V_{CSW} = 2.0 \text{ V}$	9.0	10	11	μΑ
Average cu	rrent sensor					
Input: pins C	CSP and CSN					
l _i	input current	V _{CS} = 0 V	-	-	1	μΑ
V _{offset}	offset voltage	$V_{CSP} = V_{CSN} = 0 \text{ V to } 2.5 \text{ V}$	-2	0	+2	mV
g _m	transconductance	f = 1 kHz	1900	3800	5700	μΑ/mV
Output: pin (CSW					
lo	output current	source and sink; $V_{CSW} = 2 V$	85	95	105	μΑ
Preheat tim	er; pin CT					
t _{ph}	preheat time	C_{CT} = 330 nF; R_{IREF} = 33 k Ω	1.6	1.8	2.0	S
t _{ign}	ignition time	C_{CT} = 330 nF; R_{IREF} = 33 k Ω	-	0.32	-	S
Io	output current	$V_{CT} = 2.5 \text{ V}$	5.5	5.9	6.3	μΑ
V _{OL}	LOW-level output voltage		-	1.4	-	V
V _{OH}	HIGH-level output voltage		-	3.6	-	V
V _{hys}	hysteresis voltage		2.05	2.20	2.35	V

^[1] The maximum non-overlap time is determined by the level of the CF signal. If this signal exceeds a level of 1.25 V, the non-overlap will end, resulting in a maximum non-overlap time of 7.5 μs at a bridge frequency of 40 kHz.

UBA2014_4 © NXP B.V. 2008. All rights reserved.

600 V driver IV for HF fluorescent lamps

14 of 19



UBA2014_4 © NXP B.V. 2008. All rights reserved. Rev. 04 — 16 October 2008

Product data sheet


12. Application information

600 V driver IV for HF fluorescent lamps

13. Package outline

SO16: plastic small outline package; 16 leads; body width 3.9 mm

SOT109-1



UNIT	A max.	A ₁	A ₂	A ₃	bp	С	D ⁽¹⁾	E ⁽¹⁾	е	HE	L	Lp	Q	v	w	у	Z ⁽¹⁾	θ
mm	1.75	0.25 0.10	1.45 1.25	0.25	0.49 0.36	0.25 0.19	10.0 9.8	4.0 3.8	1.27	6.2 5.8	1.05	1.0 0.4	0.7 0.6	0.25	0.25	0.1	0.7 0.3	8°
inches	0.069	0.010 0.004	0.057 0.049	0.01	l	0.0100 0.0075	0.39 0.38	0.16 0.15	0.05	0.244 0.228	0.041	0.039 0.016	0.028 0.020	0.01	0.01	0.004	0.028 0.012	0°

Note

1. Plastic or metal protrusions of 0.15 mm (0.006 inch) maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT109-1	076E07	MS-012				99-12-27 03-02-19

Package outline SOT109-1 (SO16) Fig 9.


UBA2014_4 © NXP B.V. 2008. All rights reserved.

600 V driver IV for HF fluorescent lamps

DIP16: plastic dual in-line package; 16 leads (300 mil); long body

SOT38-1

16 of 19



UNIT	A max.	A ₁ min.	A ₂ max.	b	b ₁	С	D ⁽¹⁾	E ⁽¹⁾	е	e ₁	L	ME	Мн	w	Z ⁽¹⁾ max.
mm	4.7	0.51	3.7	1.40 1.14	0.53 0.38	0.32 0.23	21.8 21.4	6.48 6.20	2.54	7.62	3.9 3.4	8.25 7.80	9.5 8.3	0.254	2.2
inches	0.19	0.02	0.15	0.055 0.045	0.021 0.015	0.013 0.009	0.86 0.84	0.26 0.24	0.1	0.3	0.15 0.13	0.32 0.31	0.37 0.33	0.01	0.087

Note

Product data sheet

1. Plastic or metal protrusions of 0.25 mm (0.01 inch) maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT38-1	050G09	MO-001	SC-503-16			99-12-27 03-02-13

Fig 10. Package outline SOT38-1 (DIP16)

UBA2014_4 © NXP B.V. 2008. All rights reserved. Rev. 04 — 16 October 2008

600 V driver IV for HF fluorescent lamps

14. Revision history

Table 7. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
UBA2014_4	20081016	Product data sheet	-	UBA2014_3
Modifications:		r V _{HS} in <u>Table 1</u> updated. r VHS in <u>Table 4</u> updated.		
UBA2014_3	20080815	Product data sheet	-	UBA2014_2
UBA2014_2	20050912	Product data sheet	-	UBA2014_1
UBA2014_1	20020516	Product specification	-	-

600 V driver IV for HF fluorescent lamps

15. Legal information

15.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

15.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

15.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental

damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

16. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

UBA2014_4 © NXP B.V. 2008. All rights reserved.

600 V driver IV for HF fluorescent lamps

17. Contents

General description
Features
Applications
Quick reference data 2
Ordering information 2
Block diagram 3
Pinning information 4
Pinning
Pin description 4
Functional description 5
Start-up state 5
Oscillation
Adaptive non-overlap 5
Timing circuit
Preheat state 6
Ignition state 6
Burn state 6
Lamp failure mode 6
During ignition state 6
During burn state 6
Power-down mode
Capacitive mode protection
Charge coupling
Design equations
Limiting values 10
Thermal characteristics
Characteristics11
Application information 14
Package outline 15
Revision history
Legal information
Data sheet status
Definitions
Disclaimers
Trademarks
Contact information
Contents

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.



All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 16 October 2008 Document identifier: UBA2014_4

