ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and Onsemi. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

2-Kb Microwire Serial CMOS EEPROM

CAT93C57 Not Recommended for New Designs: Replace with CAT93C56

Description

The CAT93C56/57 is a 2–kb CMOS Serial EEPROM device which is organized as either 128 registers of 16 bits (ORG pin at $V_{\rm CC}$) or 256 registers of 8 bits (ORG pin at GND). Each register can be written (or read) serially by using the DI (or DO) pin. The CAT93C56/57 features sequential read and self–timed internal write with auto–clear. On–chip Power–On Reset circuitry protects the internal logic against powering up in the wrong state.

Features

- High Speed Operation: 2 MHz
- 1.8 V to 5.5 V Supply Voltage Range
- Selectable x8 or x16 Memory Organization
- Sequential Read
- Software Write Protection
- Power-up Inadvertent Write Protection
- Low Power CMOS Technology
- 1,000,000 Program/Erase Cycles
- 100 Year Data Retention
- Industrial and Extended Temperature Ranges
- 8-pin PDIP, SOIC, TSSOP and 8-pad TDFN Packages
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant




Figure 1. Functional Symbol

NOTE: When the ORG pin is connected to $V_{\rm CC}$, the x16 organization is selected. When it is connected to ground, the x8 pin is selected. If the ORG pin is left unconnected, then an internal pullup device will select the x16 organization.



ON Semiconductor®

http://onsemi.com







V or W SUFFIX CASE 751BD SOIC-8 EIAJ X SUFFIX CASE 751BE TDFN-8 VP2 SUFFIX CASE 511AK





L SUFFIX CASE 646AA TSSOP-8 Y SUFFIX CASE 948AL

PIN CONFIGURATIONS

cs		8	V _{CC}	NC	1	8	ORG
SK	2	7	NC	V _{CC} CS	2	7	GND
DI	3	6	ORG		3	6	DO
DO	4	5	GND	SK	4	5	DI
BBIB (I.) 8818 (I.) 10					2010	(1.4.44)	

PDIP (L), SOIC (V, X), TSSOP (Y), TDFN (VP2) SOIC (W*)

PIN FUNCTION

Pin Name	Function			
CS	Chip Select			
SK	Clock Input			
DI	Serial Data Input			
DO	Serial Data Output			
V _{CC}	Power Supply			
GND	Ground			
ORG	Memory Organization			
NC	No Connection			

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 15 of this data sheet.

^{*} SOIC (W) rotated pin-out package not recommended for new designs

Table 1. ABSOLUTE MAXIMUM RATINGS

Parameters	Ratings	Units
Storage Temperature	-65 to +150	°C
Voltage on Any Pin with Respect to Ground (Note 1)	-0.5 to +6.5	V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

Table 2. RELIABILITY CHARACTERISTICS (Note 2)

Symbol	Parameter	Min	Units
N _{END} (Note 3)	Endurance	1,000,000	Program / Erase Cycles
T _{DR}	Data Retention	100	Years

These parameters are tested initially and after a design or process change that affects the parameter according to appropriate AEC-Q100 and JEDEC test methods.

Table 3. D.C. OPERATING CHARACTERISTICS, CAT93C56

 $(V_{CC} = +1.8 \text{ V to } +5.5 \text{ V}, T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C unless otherwise specified.})$

Symbol	Parameter	Test Cond	Min	Max	Units	
I _{CC1}	Power Supply Current (Write)	f _{SK} = 1 MHz, V _{CC} = 5.0 V			1	mA
I _{CC2}	Power Supply Current (Read)	f _{SK} = 1 MHz, V _{CC} = 5.0 V			500	μΑ
I _{SB1}	Power Supply	$V_{IN} = GND \text{ or } V_{CC},$	$T_A = -40^{\circ}C \text{ to } +85^{\circ}C$		2	μΑ
	Current (Standby) (x8 Mode)	CS = GND ORG = GND	$T_A = -40^{\circ}\text{C} \text{ to } +125^{\circ}\text{C}$		4	
I _{SB2}	Power Supply	$V_{IN} = GND \text{ or } V_{CC}, CS =$	$T_A = -40^{\circ}C$ to $+85^{\circ}C$		1	μΑ
	Current (Standby) (x16 Mode)	GND ORG = Float or V _{CC}	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$		2	
ILI	Input Leakage				1	μΑ
	Current		$T_A = -40^{\circ}C \text{ to } +125^{\circ}C$		2	
I _{LO} Output Leakage					1	μΑ
	Current	CS = GND	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$		2	
V_{IL1}	Input Low Voltage	$4.5 \text{ V} \leq \text{V}_{CC} < 5.5 \text{ V}$		-0.1	0.8	V
V _{IH1}	Input High Voltage	$4.5 \text{ V} \leq \text{V}_{CC} < 5.5 \text{ V}$		2	V _{CC} + 1	V
V_{IL2}	Input Low Voltage	$1.8 \text{ V} \leq \text{V}_{CC} < 4.5 \text{ V}$		0	V _{CC} x 0.2	V
V _{IH2}	Input High Voltage	$1.8 \text{ V} \leq \text{V}_{CC} < 4.5 \text{ V}$		V _{CC} x 0.7	V _{CC} + 1	V
V _{OL1}	Output Low Voltage	$4.5 \text{ V} \leq \text{V}_{CC} < 5.5 \text{ V},$ $\text{I}_{OL} = 2.1 \text{ mA}$			0.4	V
V _{OH1}	Output High Voltage	$4.5 \text{ V} \leq \text{V}_{CC} < 5.5 \text{ V},$ $I_{OH} = -400 \mu\text{A}$		2.4		V
V _{OL2}	Output Low Voltage	$1.8 \text{ V} \le \text{V}_{CC} < 4.5 \text{ V},$ $\text{I}_{OL} = 1 \text{ mA}$			0.2	V
V _{OH2}	Output High Voltage	$1.8 \text{ V} \le \text{V}_{CC} < 4.5 \text{ V},$ $\text{I}_{OH} = -100 \mu\text{A}$		V _{CC} – 0.2		V

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

^{1.} The DC input voltage on any pin should not be lower than -0.5 V or higher than $V_{CC} + 0.5$ V. During transitions, the voltage on any pin may undershoot to no less than -1.5 V or overshoot to no more than $V_{CC} + 1.5$ V, for periods of less than 20 ns.

^{3.} Block Mode, V_{CC} = 5 V, 25°C

Table 4. D.C. OPERATING CHARACTERISTICS, CAT93C57, Die Rev. E – Mature Product (NOT RECOMMENDED FOR NEW DESIGNS) (V_{CC} = +1.8 V to +5.5 V, T_A =-40°C to +125°C unless otherwise specified.)

Symbol	Parameter	Test Conditions	Min	Max	Units
I _{CC1}	Power Supply Current (Write)	f _{SK} = 1 MHz, V _{CC} = 5.0 V		3	mA
I _{CC2}	Power Supply Current (Read)	f _{SK} = 1 MHz, V _{CC} = 5.0 V		500	μΑ
I _{SB1}	Power Supply Current (Standby) (x8 Mode)	V_{IN} = GND or V_{CC} , CS = GND ORG = GND		10	μΑ
I _{SB2}	Power Supply Current (Standby) (x16 Mode)	V_{IN} = GND or V_{CC} , CS = GND ORG = Float or V_{CC}		10	μΑ
I _{LI}	Input Leakage Current	V_{IN} = GND to V_{CC}		1	μΑ
I _{LO}	Output Leakage Current	$V_{OUT} = GND$ to V_{CC} , $CS = GND$		1	μΑ
V _{IL1}	Input Low Voltage	$4.5 \text{ V} \le \text{V}_{CC} < 5.5 \text{ V}$	-0.1	0.8	V
V _{IH1}	Input High Voltage	$4.5 \text{ V} \le \text{V}_{CC} < 5.5 \text{ V}$	2	V _{CC} + 1	V
V_{IL2}	Input Low Voltage	$1.8 \text{ V} \leq \text{V}_{CC} < 4.5 \text{ V}$	0	V _{CC} x 0.2	V
V _{IH2}	Input High Voltage	$1.8 \text{ V} \le \text{V}_{CC} < 4.5 \text{ V}$	V _{CC} x 0.7	V _{CC} + 1	V
V _{OL1}	Output Low Voltage	$4.5 \text{ V} \le \text{V}_{CC} < 5.5 \text{ V}, \text{I}_{OL} = 2.1 \text{ mA}$		0.4	V
V _{OH1}	Output High Voltage	$4.5 \text{ V} \leq \text{V}_{CC} < 5.5 \text{ V}, \text{I}_{OH} = -400 \mu\text{A}$	2.4		V
V _{OL2}	Output Low Voltage	$1.8 \text{ V} \leq \text{ V}_{CC} < 4.5 \text{ V}, \text{ I}_{OL} = 1 \text{ mA}$		0.2	V
V _{OH2}	Output High Voltage	$1.8 \text{ V} \leq \text{V}_{CC} < 4.5 \text{ V}, \text{I}_{OH} = -100 \mu\text{A}$	V _{CC} - 0.2		V

Table 5. PIN CAPACITANCE ($T_A = 25^{\circ}C$, f = 1 MHz, $V_{CC} = 5$ V)

Symbol	Test	Conditions	Min	Тур	Max	Units
C _{OUT} (Note 4)	Output Capacitance (DO)	V _{OUT} = 0 V			5	pF
C _{IN} (Note 4)	Input Capacitance (CS, SK, DI, ORG)	$V_{IN} = 0 V$			5	pF

^{4.} These parameters are tested initially and after a design or process change that affects the parameter according to appropriate AEC-Q100 and JEDEC test methods.

Table 6. A.C. CHARACTERISTICS (Note 5), CAT93C56

(V_{CC} = +1.8V to +5.5V, T_A = -40°C to +125°C, unless otherwise specified.)

		Lim	Limits			
Symbol	Parameter	Min	Max	Units		
tcss	CS Setup Time	50		ns		
t _{CSH}	CS Hold Time	0		ns		
t _{DIS}	DI Setup Time	100		ns		
t _{DIH}	DI Hold Time	100		ns		
t _{PD1}	Output Delay to 1		0.25	μS		
t _{PD0}	Output Delay to 0		0.25	μs		
t _{HZ} (Note 6)	Output Delay to High-Z		100	ns		
t _{EW}	Program/Erase Pulse Width		5	ms		
t _{CSMIN}	Minimum CS Low Time	0.25		μs		
t _{SKHI}	Minimum SK High Time	0.25		μS		
t _{SKLOW}	Minimum SK Low Time	0.25		μs		
t _{SV}	Output Delay to Status Valid		0.25	μs		
SK _{MAX}	Maximum Clock Frequency	DC	2000	kHz		

Table 7. A.C. CHARACTERISTICS (Note 5), CAT93C57, Die Rev. E – Mature Product (NOT RECOMMENDED FOR NEW DESIGNS)

	Limits							
		V _{CC} = 1.8 V - 5.5 V		V _{CC} = 2.5 V - 5.5 V		V _{CC} = 4.5 V - 5.5 V		1
Symbol	Parameter	Min	Max	Min	Max	Min	Max	Units
t _{CSS}	CS Setup Time	200		100		50		ns
t _{CSH}	CS Hold Time	0		0		0		ns
t _{DIS}	DI Setup Time	400		200		100		ns
t _{DIH}	DI Hold Time	400		200		100		ns
t _{PD1}	Output Delay to 1		1		0.5		0.25	μS
t _{PD0}	Output Delay to 0		1		0.5		0.25	μS
t _{HZ} (Note 6)	Output Delay to High–Z		400		200		100	ns
t _{EW}	Program/Erase Pulse Width		10		10		10	ms
t _{CSMIN}	Minimum CS Low Time	1		0.5		0.25		μS
t _{SKHI}	Minimum SK High Time	1		0.5		0.25		μS
t _{SKLOW}	Minimum SK Low Time	1		0.5		0.25		μS
t _{SV}	Output Delay to Status Valid		1		0.5		0.25	μS
SK _{MAX}	Maximum Clock Frequency	DC	250	DC	500	DC	1000	kHz

Table 8. POWER-UP TIMING (Notes 6 and 7)

Symbol	Parameter	Max	Units
t _{PUR}	Power-up to Read Operation	1	ms
t _{PUW}	Power-up to Write Operation	1	ms

^{5.} Test conditions according to "A.C. Test Conditions" table.

^{6.} These parameters are tested initially and after a design or process change that affects the parameter according to appropriate AEC-Q100 and JEDEC test methods.

^{7.} t_{PUR} and t_{PUW} are the delays required from the time V_{CC} is stable until the specified operation can be initiated.

Table 9. A.C. TEST CONDITIONS

Input Rise and Fall Times	≤ 50 ns			
Input Pulse Voltages	0.4 V to 2.4 V	$4.5 \text{ V} \leq \text{V}_{\text{CC}} \leq 5.5 \text{ V}$		
Timing Reference Voltages	0.8 V, 2.0 V	$4.5 \text{ V} \leq \text{V}_{\text{CC}} \leq 5.5 \text{ V}$		
Input Pulse Voltages	0.2 V _{CC} to 0.7 V _{CC}	$1.8 \text{ V} \leq \text{V}_{\text{CC}} \leq 4.5 \text{ V}$		
Timing Reference Voltages	0.5 V _{CC}	$1.8 \text{ V} \leq \text{V}_{\text{CC}} \leq 4.5 \text{ V}$		
Output Load	Current Source I _{OLmax} /I _{OHmax} ; CL=100 pF			

Device Operation

The CAT93C56/57 is a 2048-bit nonvolatile memory intended for use with industry standard microprocessors. The CAT93C56/57 can be organized as either registers of 16 bits or 8 bits. When organized as X16, seven 10-bit instructions for 93C57 or seven 11-bit instructions for 93C56 control the reading, writing and erase operations of the device. When organized as X8, seven 11-bit instructions for 93C57 or seven 12-bit instructions for 93C56 control the reading, writing and erase operations of the device. The CAT93C56/57 operates on a single power supply and will generate on chip, the high voltage required during any write operation.

Instructions, addresses, and write data are clocked into the DI pin on the rising edge of the clock (SK). The DO pin is normally in a high impedance state except when reading data

from the device, or when checking the ready/busy status after a write operation. The serial communication protocol follows the timing shown in Figure 2.

The ready/busy status can be determined after the start of internal write cycle by selecting the device (CS high) and polling the DO pin; DO low indicates that the write operation is not completed, while DO high indicates that the device is ready for the next instruction. If necessary, the DO pin may be placed back into a high impedance state during chip select by shifting a dummy "1" into the DI pin. The DO pin will enter the high impedance state on the rising edge of the clock (SK). Placing the DO pin into the high impedance state is recommended in applications where the DI pin and the DO pin are to be tied together to form a common DI/O pin.




Figure 2. Synchronous Data Timing

The format for all instructions sent to the device is a logical "1" start bit, a 2-bit (or 4-bit) opcode, 7-bit address (CAT93C57) / 8-bit address (CAT93C56) (an additional bit

when organized X8) and for write operations a 16-bit data field (8-bit for X8 organizations). The instruction format is shown in Instruction Set table.

Table 10. INSTRUCTION SET

		Start		Add	ress	D	ata	
Instruction	Device Type	Bit	Opcode	х8	x16	х8	x16	Comments
READ	93C56 (Note 8)	1	10	A8-A0	A7-A0			Read Address
	93C57	1	10	A7-A0	A6-A0			AN–A0
ERASE	93C56 (Note 8)	1	11	A8-A0	A7-A0			Clear Address
	93C57	1	11	A7-A0	A6-A0			AN–A0
WRITE	93C56 (Note 8)	1	01	A8-A0	A7-A0	D7-D0	D15-D0	Write Address
	93C57	1	01	A7-A0	A6-A0	D7-D0	D15-D0	AN–A0
EWEN	93C56 (Note 8)	1	00	11XXXXXXX	11XXXXXX			Write Enable
	93C57	1	00	11XXXXXX	11XXXXX			
EWDS	93C56 (Note 8)	1	00	00XXXXXXX	00XXXXXX			Write Disable
	93C57	1	00	00XXXXXX	00XXXXX			
ERAL	93C56 (Note 8)	1	00	10XXXXXXX	10XXXXXX			Clear All
	93C57	1	00	10XXXXXX	10XXXXX			Addresses
WRAL	93C56 (Note 8)	1	00	01XXXXXXX	01XXXXXX	D7-D0	D15-D0	Write All
	93C57	1	00	01XXXXXX	01XXXXX	D7-D0	D15-D0	Addresses

^{8.} Address bit A8 for 256x8 organization and A7 for 128x16 organization are "Don't Care" bits, but must be kept at either a "1" or "0" for READ, WRITE and ERASE commands.

Read

Upon receiving a READ command and an address (clocked into the DI pin), the DO pin of the CAT93C56/57 will come out of the high impedance state and, after sending an initial dummy zero bit, will begin shifting out the data addressed (MSB first). The output data bits will toggle on the rising edge of the SK clock and are stable after the specified time delay (t_{PD0} or t_{PD1}).

For the CAT93C56/57, after the initial data word has been shifted out and CS remains asserted with the SK clock continuing to toggle, the device will automatically increment to the next address and shift out the next data word in a sequential READ mode. As long as CS is continuously asserted and SK continues to toggle, the device will keep incrementing to the next address automatically until it reaches to the end of the address space, then loops back to address 0. In the sequential READ mode, only the initial

data word is preceded by a dummy zero bit. All subsequent data words will follow without a dummy zero bit. The READ instruction timing is illustrated in Figure 3.

Erase/Write Enable and Disable

The CAT93C56/57 powers up in the write disable state. Any writing after power—up or after an EWDS (erase/write disable) instruction must first be preceded by the EWEN (erase/write enable) instruction. Once the write instruction is enabled, it will remain enabled until power to the device is removed, or the EWDS instruction is sent. The EWDS instruction can be used to disable all CAT93C56/57 write and erase instructions, and will prevent any accidental writing or clearing of the device. Data can be read normally from the device regardless of the write enable/disable status. The EWEN and EWDS instructions timing is shown in Figure 4.




Figure 3. READ Instruction Timing




Figure 4. EWEN/EWDS Instruction Timing

Write

After receiving a WRITE command (Figure 5), address and the data, the CS (Chip Select) pin must be deselected for a minimum of t_{CSMIN}. The falling edge of CS will start the self clocking clear and data store cycle of the memory location specified in the instruction. The clocking of the SK pin is not necessary after the device has entered the self clocking mode. The ready/busy status of the CAT93C56/57 can be determined by selecting the device and polling the DO pin. Since this device features Auto—Clear before write, it is NOT necessary to erase a memory location before it is written into.

Erase

Upon receiving an ERASE command and address, the CS (Chip Select) pin must be deasserted for a minimum of t_{CSMIN} (Figure 6). The falling edge of CS will start the self clocking clear cycle of the selected memory location. The clocking of the SaK pin is not necessary after the device has entered the self clocking mode. The ready/busy status of the CAT93C56/57 can be determined by selecting the device and polling the DO pin. Once cleared, the content of a cleared location returns to a logical "1" state.




Figure 5. Write Instruction Timing




Figure 6. Erase Instruction Timing

Erase All

Upon receiving an ERAL command (Figure 7), the CS (Chip Select) pin must be deselected for a minimum of t_{CSMIN}. The falling edge of CS will start the self clocking clear cycle of all memory locations in the device. The clocking of the SK pin is not necessary after the device has entered the self clocking mode. The ready/busy status of the CAT93C56/57 can be determined by selecting the device and polling the DO pin. Once cleared, the contents of all memory bits return to a logical "1" state.

Write All

Upon receiving a WRAL command and data, the CS (Chip Select) pin must be deselected for a minimum of t_{CSMIN} (Figure 8). The falling edge of CS will start the self clocking data write to all memory locations in the device. The clocking of the SK pin is not necessary after the device has entered the self clocking mode. The ready/busy status of the CAT93C56/57 can be determined by selecting the device and polling the DO pin. It is not necessary for all memory locations to be cleared before the WRAL command is executed.




Figure 7. ERAL Instruction Timing





Figure 8. WRAL Instruction Timing


PACKAGE DIMENSIONS


PDIP-8, 300 mils CASE 646AA-01 ISSUE A



SYMBOL	MIN	MAX	
Α			5.33
A1	0.38		
A2	2.92	3.30	4.95
b	0.36	0.46	0.56
b2	1.14	1.52	1.78
С	0.20	0.25	0.36
D	9.02	9.27	10.16
Е	7.62	7.87	8.25
E1	6.10 6.35		7.11
е	2.54 BSC		
eB	7.87		10.92
L	2.92	3.30	3.80

TOP VIEW






END VIEW

Notes:

- (1) All dimensions are in millimeters.
- (2) Complies with JEDEC MS-001.


PACKAGE DIMENSIONS

SOIC 8, 150 mils CASE 751BD-01 ISSUE O




SYMBOL	MIN	NOM	MAX
А	1.35		1.75
A1	0.10		0.25
b	0.33		0.51
С	0.19		0.25
D	4.80		5.00
E	5.80		6.20
E1	3.80		4.00
е	1.27 BSC		
h	0.25		0.50
L	0.40		1.27
θ	0°		8°

TOP VIEW



SIDE VIEW




END VIEW

Notes:

- (1) All dimensions are in millimeters. Angles in degrees.(2) Complies with JEDEC MS-012.


PACKAGE DIMENSIONS


SOIC-8, 208 mils CASE 751BE-01 ISSUE O



SYMBOL	MIN	NOM	MAX
А			2.03
A1	0.05		0.25
b	0.36		0.48
С	0.19		0.25
D	5.13		5.33
E	7.75		8.26
E1	5.13		5.38
е	1.27 BSC		
L	0.51		0.76
θ	0°		8°

TOP VIEW






END VIEW

- (1) All dimensions are in millimeters. Angles in degrees.(2) Complies with EIAJ EDR-7320.


PACKAGE DIMENSIONS

TSSOP8, 4.4x3 CASE 948AL-01 ISSUE O




SYMBOL	MIN	NOM	MAX		
А			1.20		
A1	0.05		0.15		
A2	0.80	0.90	1.05		
b	0.19 0.30				
С	0.09		0.20		
D	2.90	3.00	3.10		
E	6.30	6.40	6.50		
E1	4.30 4.40 4.50				
е	0.65 BSC				
L	1.00 REF				
L1	0.50 0.60 0.75				
θ	0°		8°		

TOP VIEW



SIDE VIEW




Notes:

- (1) All dimensions are in millimeters. Angles in degrees.(2) Complies with JEDEC MO-153.


PACKAGE DIMENSIONS

TDFN8, 2x3 CASE 511AK-01 ISSUE A



SIDE VIEW

SYMBOL	MIN NOM		MAX	
А	0.70	0.70 0.75		
A1	0.00	0.02	0.05	
A2	0.45	0.55 0.69		
А3	0.20 REF			
b	0.20	0.25	0.30	
D	1.90	2.00	2.10	
D2	1.30	1.40	1.50	
Е	2.90	3.00	3.10	
E2	1.20	1.30 1.40		
е	0.50 TYP			
L	0.20	0.20 0.30 0.40		



BOTTOM VIEW

FRONT VIEW

Notes:

- (1) All dimensions are in millimeters.(2) Complies with JEDEC MO-229.

TOP VIEW

Example of Ordering Information

OPN	Specific Device Marking	Pkg Type	Temperature Range	Lead Fin- ish	Shipping
CAT93C56LI-G	CSI*4G / 93C56LI	PDIP-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tube, 50 Units / Tube
CAT93C56VE-G	CSI*4G / 93C56LE	SOIC-8, JEDEC	E = Extended (-40°C to +125°C)	NiPdAu	Tube, 100 Units / Tube
CAT93C56VE-GT3	CSI*4G / 93C56VE	SOIC-8, JEDEC	E = Extended (-40°C to +125°C)	NiPdAu	Tape & Reel, 3000 Units / Reel
CAT93C56VI-G	CSI*4G / 93C56VI	SOIC-8, JEDEC	I = Industrial (-40°C to +85°C)	NiPdAu	Tube, 100 Units / Tube
CAT93C56VI-GT3	CSI*4G / 93C56VI	SOIC-8, JEDEC	I = Industrial (-40°C to +85°C)	NiPdAu	Tape & Reel, 3000 Units / Reel
CAT93C56VP2I-GT3	НВ	TDFN-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tape & Reel, 3000 Units / Reel
CAT93C56WI-G	CSI*4G / 93C56WI	SOIC-8, JEDEC	I = Industrial (-40°C to +85°C)	NiPdAu	Tube, 100 Units / Tube
CAT93C56WI-GT3	93C56W	SOIC-8, JEDEC	I = Industrial (-40°C to +85°C)	NiPdAu	Tape & Reel, 3000 Units / Reel
CAT93C56XI	CSI*3G / 93C56XI	SOIC-8, EIAJ	I = Industrial (-40°C to +85°C)	Matte-Tin	Tube, 94 Units / Tube
CAT93C56XI-T2	CSI*3G / 93C56XI	SOIC-8, EIAJ	I = Industrial (-40°C to +85°C)	Matte-Tin	Tape & Reel, 2000 Units / Reel
CAT93C56YI-G	M56	TSSOP-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tube, 100 Units / Tube
CAT93C56YI-GT3	M56	TSSOP-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tape & Reel, 3000 Units / Reel
CAT93C57LI-G	CSI*4E/ 93C57LI	PDIP-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tube, 50 Units / Tube
CAT93C57VI-G	CSI*4E / 93C57VI	SOIC-8, JEDEC	I = Industrial (-40°C to +85°C)	NiPdAu	Tube, 100 Units / Tube
CAT93C57VI-GT3	CSI*4E / 93C57VI	SOIC-8, JEDEC	I = Industrial (-40°C to +85°C)	NiPdAu	Tape & Reel, 3000 Units / Reel
CAT93C57XI	CSI*3E / 93C57X	SOIC-8, EIAJ	I = Industrial (-40°C to +85°C)	Matte-Tin	Tube, 94 Units / Tube
CAT93C57XI-T2	CSI*3E / 93C57X	SOIC-8, EIAJ	I = Industrial (-40°C to +85°C)	Matte-Tin	Tape & Reel, 2000 Units / Reel
CAT93C57YI-GT3	M57	TSSOP-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tape & Reel, 3000 Units / Reel

All packages are RoHS-compliant (Lead-free, Halogen-free).
 The standard lead finish is NiPdAu.
 CAT93C57 NOT recommended for new designs.
 For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

ON Semiconductor and the registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subscilaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunit

N. American Technical Support: 800-282-9855 Toll Free

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada
Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

2217 USA
-3860 Toll Free USA/Canada
67 Toll Free USA/Canada
67 Toll Free USA/Canada
68 Toll Free USA/Canada
69 Toll Free USA/Canada
60 Toll Free USA/Canada
61 Toll Free USA/Canada
62 Toll Free USA/Canada
63 Toll Free USA/Canada
64 Toll Free USA/Canada
65 Toll Free USA/Canada
66 Toll Free USA/Canada

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

CAT93C56/D