


Silicon Photodiode, RoHS Compliant



94 8482


RoHS
COMPLIANT

FEATURES

- Package type: leaded
- Package form: TO-5
- Dimensions (in mm): \varnothing 8.13
- Radiant sensitive area (in mm²): 7.5
- High photo sensitivity
- High radiant sensitivity
- Suitable for visible and near infrared radiation
- Angle of half sensitivity: $\varphi = \pm 50^\circ$
- Hermetically sealed package
- Cathode connected to package
- Flat glass window
- UV enhanced
- Low dark current
- High shunt resistance
- High linearity
- Compliant to RoHS Directive 2002/95/EC and in accordance with WEEE 2002/96/EC

DESCRIPTION

BPW20RF is a planar Silicon PN photodiode in a hermetically sealed short TO-5 case, especially designed for high precision linear applications.

Due to its extremely high dark resistance, the short circuit photocurrent is linear over seven decades of illumination level.

On the other hand, there is a strictly logarithmic correlation between open circuit voltage and illumination over the same range.

Equipped with a clear, flat glass window, the spectral responsivity reaches from blue to near infrared.

APPLICATIONS

- Sensor for light measuring techniques in cameras, photometers, color analyzers, exposure meters (e.g. solariums) and other medical and industrial measuring and control applications.

PRODUCT SUMMARY

| COMPONENT | I_{ra} (μ A) | φ (deg) | $\lambda_{0.1}$ (nm) |
|-----------|---------------------|-----------------|----------------------|
| BPW20RF | 60 | ± 50 | 400 to 1100 |

Note

- Test condition see table "Basic Characteristics"

ORDERING INFORMATION

| ORDERING CODE | PACKAGING | REMARKS | PACKAGE FORM |
|---------------|-----------|----------------------------|--------------|
| BPW20RF | Bulk | MOQ: 500 pcs, 500 pcs/bulk | TO-5 |

Note

- MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25^\circ\text{C}$, unless otherwise specified)

| PARAMETER | TEST CONDITION | SYMBOL | VALUE | UNIT |
|-------------------------------------|--|------------|---------------|------------------|
| Reverse voltage | | V_R | 10 | V |
| Power dissipation | $T_{amb} \leq 50^\circ\text{C}$ | P_V | 300 | mW |
| Junction temperature | | T_j | 125 | $^\circ\text{C}$ |
| Operating temperature range | | T_{amb} | - 40 to + 125 | $^\circ\text{C}$ |
| Storage temperature range | | T_{stg} | - 40 to + 125 | $^\circ\text{C}$ |
| Soldering temperature | $t \leq 5$ s | T_{sd} | 260 | $^\circ\text{C}$ |
| Thermal resistance junction/ambient | Connected with Cu wire, 0.14 mm ² | R_{thJA} | 250 | K/W |

| BASIC CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified) | | | | | | |
|---|--|-------------------|------|----------|------|------------------|
| PARAMETER | TEST CONDITION | SYMBOL | MIN. | TYP. | MAX. | UNIT |
| Forward voltage | $I_F = 50\text{ mA}$ | V_F | | 1.0 | 1.3 | V |
| Breakdown voltage | $I_R = 20\text{ }\mu\text{A}$, $E = 0$ | $V_{(BR)}$ | 10 | | | V |
| Reverse dark current | $V_R = 5\text{ V}$, $E = 0$ | I_{ro} | | 2 | 30 | nA |
| Diode capacitance | $V_R = 0\text{ V}$, $f = 1\text{ MHz}$, $E = 0$ | C_D | | 1.2 | | nF |
| | $V_R = 5\text{ V}$, $f = 1\text{ MHz}$, $E = 0$ | C_D | | 400 | | pF |
| Dark resistance | $V_R = 10\text{ mV}$ | R_D | | 38 | | $\text{G}\Omega$ |
| Open circuit voltage | $E_A = 1\text{ klx}$ | V_o | 330 | 500 | | mV |
| Temperature coefficient of V_o | $E_A = 1\text{ klx}$ | TK_{V_o} | | -2 | | mV/K |
| Short circuit current | $E_A = 1\text{ klx}$ | I_k | 20 | 60 | | μA |
| Temperature coefficient of I_k | $E_A = 1\text{ klx}$ | TK_{I_k} | | 0.1 | | %/K |
| Reverse light current | $E_A = 1\text{ klx}$, $V_R = 5\text{ V}$ | I_{ra} | 20 | 60 | | μA |
| | $E_e = 1\text{ mW/cm}^2$, $\lambda = 950\text{ nm}$, $V_R = 5\text{ V}$ | I_{ra} | | 42 | | μA |
| Angle of half sensitivity | | φ | | ± 50 | | deg |
| Wavelength of peak sensitivity | | λ_p | | 920 | | nm |
| Range of spectral bandwidth | | $\lambda_{0.1}$ | 400 | | 1100 | nm |
| Rise time | $V_R = 0\text{ V}$, $R_L = 1\text{ k}\Omega$, $\lambda = 820\text{ nm}$ | t_r | | 3.4 | | μs |
| Fall time | $V_R = 0\text{ V}$, $R_L = 1\text{ k}\Omega$, $\lambda = 820\text{ nm}$ | t_f | | 3.7 | | μs |


BASIC CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)


Fig. 1 - Reverse Dark Current vs. Ambient Temperature







Fig. 2 - Relative Reverse Light Current vs. Ambient Temperature




18959
Fig. 3 - Short Circuit Current vs. Illuminance




94 8473
Fig. 6 - Diode Capacitance vs. Reverse Voltage




94 8471
Fig. 4 - Reverse Light Current vs. Irradiance



94 8474
Fig. 7 - Relative Spectral Sensitivity vs. Wavelength




94 8472
Fig. 5 - Reverse Light Current vs. Reverse Voltage



94 8475
Fig. 8 - Relative Radiant Sensitivity vs. Angular Displacement



PACKAGE DIMENSIONS in millimeters



Drawing-No.: 6.511-5002.01-4
Issue:1; 01.07.96
96 12181



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.