



Part No. A1001013 Automotive Wi-Fi / BT SMD On Ground / Off Ground Antenna

2400 - 2485 MHz

Supports: Wi-Fi applications, Bluetooth, Zigbee, WLAN, Automotive, Healthcare, Agriculture, Industrial Applications



Automotive FR4 Wi-Fi / **Bluetooth Antenna**

2400 - 2485 MHz

KEY BENEFITS Stay-in-Tune

IMD antenna technology provides superior RF field containment, resulting in less interaction with surrounding components. **Quicker Time-to-Market**

By optimizing antenna size, performance and emissions, customer and regulatory specifications are more easily met. Reliability

Products are the latest RoHS version compliant.

APPLICATIONS

- Automotive Healthcare M2M,
- Infotainment •
- Embedded design
- Telematics Smart Grid
- Tracking
- OBD-II

Industrial

devices

KYOCERA AVX A-Series automotive antennas deliver on the key needs of device designers for higher functionality.

KYOCERA AVX has completed rigorous testing to qualify the A-series antennas for automotive applications. Although the AEC-Q200 standard does not include antenna products, all testing has been done following applicable AEC-Q200 requirements and procedures as closely as possible. Customers must provide additional quality requirements, if any, to drive additional compliance testing.

Electrical Specifications

Typical Characteristics, on 50 x 70 mm PCB

Frequency	2400 – 2485 MHz		
Mounting	Off Ground	On Ground (Over Metal)	
VSWR Match	1.5:1 max	1.8:1 max	
Average Efficiency	76%	48%	
Peak Gain	2.6 dBi	0.7 dBi	
Feed Point Impedance	50 ohms u	nbalanced	
Polarization	Linear		
Power Handling	0.5 Watt CW		
Mechanical Specifications & Ordering Part Number			
Ordering Part Number	A1001013		
Size (mm)	15.0 x 3.2 x 3.3		
Mounting	SMT (P&P)		
Weight (grams)	0.2		
Packaging	Tape & Reel		
Demo Board	1001013-02		
Temperature Range	-50/+125 °C		
Temperature Cycle	IEC 60068-2-14:2009		
Temperature Exposure	Mil-STD-202 Method 108		
High Temperature & High Humidity	MIL-STD-202		
Mechanical Shock	IEC 60068-2-27:2008		
Vibration	IEC 60068-2-6:2007		
IMDS and PPAP available			



Antenna Dimensions

Typical antenna dimensions (mm)



© 2022 KYOCERA AVX

TDS-ANT-0093 | Rev 0



VSWR and Efficiency Plots (Off-Ground)

Typical performance on 50 x 70 mm PCB



Antenna Radiation Patterns (Off-Ground)

Typical performance on 50 x 70 mm PCB





© 2022 KYOCERA AVX

TDS-ANT-0093 | Rev 0





* VIAS: Diam. 0.2mm, (no vias on transmission lines). Via holes must be covered by solder mask

Pin Descriptions

Pin#	Description
1	Feed
2	Dummy Pad
3	Dummy Pad

Matching Pi Network (Demo Board)

Component	Value	Tolerance	
P1	DNI	N/A	
S1	0Ω	N/A	
P2	0.4pF	±0.25pF	
P3	0Ω	N/A	

*Actual matching values depend on customer design





TDS-ANT-0093 | Rev 0



VSWR and Efficiency Plots (On-Ground)

Typical performance on 50 x 70 mm PCB







TDS-ANT-0093 | Rev 0





* VIAS: Diam. 0.2mm, (no vias on transmission lines). Via holes must be covered by solder mask

Pin Descriptions

Pin#	Description
1	Feed
2	Dummy Pad
3	Dummy Pad

Matching Pi Network (Demo Board)

Component	Value	Tolerance	
P1	DNI	N/A	
S1	0Ω	N/A	
P2	DNI	N/A	
P3	0Ω	N/A	

*Actual matching values depend on customer design







BOTTOM METAL

© 2022 KYOCERA AVX

TDS-ANT-0093 | Rev 0



Antenna Demo Board 1001013-02 Off-Ground

Part Number	A (mm)	B (mm)	C (mm)
1001013-02	70.0	50.0	15.0



TDS-ANT-0093 | Rev 0