

Coaxial Cable Connector 11_BNT-50-2-1/103_N

Description

Straight cable plug

Interface standards
SUHNER-BNT



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 3 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | soldered |
| Outer contact | clamped |
| Weight | 0.0256 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -50 °C to 125 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|-----------------------|-----------------------------------|
| Centre contact | Brass | Gold Plating (Nickel underplated) |
| Outer contact | Brass | Silver Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |
| Coupling nut | Brass | SUCOPLATE (R) Plating |
| Gasket | VMQ (Silicone rubber) | |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00048065 |
| Catalogue drawing | DOU-00007643 |
| Assembly instruction | DOC-0000179264 |

Ordering Information

| | |
|----------------|----------------------|
| Single package | 11_BNT-50-2-1/103_NE |
|----------------|----------------------|

Additional Information

| | |
|-----------------|---------|
| Suitable cables | G_02332 |
|-----------------|---------|

Remarks

Triaxial Connector

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_BNT-50-2-1/103_NE](#)