

LED flush-mounted dimmer T46.03 complete device

Item-no.: 4660x0300















Suitable for dimmable LED-lamps, dimmable LED-driver, incandescent-, HV- and LV-halogen lamps
Electronic, transistor operated dimmer without inductor
EHMANN Silent Technology - Operates absolutely silent
Optimization possibility for flicker-free dimming of LED-lamps
No stand-by consumption because of a real on/off switch
Electronically controlled short-circuit, overload and over-temperature protection with automatic reactivation
Single cover with rotary knob / Colour: white (similar to RAL 9010)
Dimmer compatible with common switch ranges from GIRA, Busch Jäger, Berker, Jung etc.
EHMANN Advantage - 100 % quality assurance, 5 years warranty, German manufacturer
EHMANN Service - Adapter inclusive, LED lamp recommendation



LED flush-mounted dimmer T46.03 - complete device

Technical data

<p>3 - 50 W LED rated power</p>	<p>15 - 150 W/VA Rated power</p>	<p>230 V ~ (+/- 10%) / 50 Hz Rated voltage</p>
<p>Suitable for dimmable LED-lamps, dimmable LED-driver, incandescent-, HV- and LV-halogen lamps with electronic transformer</p>		
<p>Operating principle: trailing edge Function: rotation dimmer with pressure two-way switch Shaft: metal shaft Ø 4 mm with fine raster (Ø 6 mm with shaft adapter) Connection: screw terminals up to 2 x 2.5 mm² (rigid) Temperature protection: resettable thermal switch Overload/short-circuit protection: electronic</p>		        
<p>Red adapter Allows the use of common covers e.g. Gira, Busch-Jäger, Jung, Berker</p> 	<p>LED Lamp recommendation „Which LED lamp works ideal with this dimmer“</p> 	<p>Optimization possibility for flicker-free dimming of LED-lamps In case of flickering during dimming the LED lamp, you can try to adjust in the lowest and highest dimming range the minimum and maximum brightness to optimize the dimming behavior.</p> 
<p>Item-no. 4660x0300 EAN 401209600678 7 PU 10</p>		<p>84 x 84 x 54 mm Dimension (L x W x H)</p>