



DEWALT 2300W 355mm Abrasive Metal Cutting Chop Saw (240V)

D28730



- Horizontal D handle for superior ergonomics and less user fatigue
- Quick release clamp results in less time in changing the work piece
- Spindle lock for quick and easy wheel change
- High power abrasion protected motor delivers high overload capabilities for greater durability
- Adjustable spark guard allows user to control the direction of the sparks coming from the machine
- Includes hex key

Description:

The DEWALT 240V 355mm Abrasive Metal Cutting Chop Saw has been constructed with a powerful motor which delivers 2300W of power, enabling solid sections of up to 130mm to be cut with ease. The heavy duty motor has an overload protection feature which helps increase performance and durability. The ergonomic D handle design provides improved comfort and reduces hand fatigue during application. The quick release vice lock allows for fast clamping of different sizes and the 45-degree pivoting fence allows for fast and accurate angle cuts. The spindle lock provides quick and easy wheel change. The spark guard is adjustable and allows the users to direct sparks away from the work area. Ideal for metal fabrication, general contractors and dry wall installers.

Specifications	
Power Source	Corded
Wheel Diameter	355 mm
Wheel Bore	25.4 mm
No Load Speed	4000 rpm
Max. Cutting Capacity at 90° [Square Profile]	115 x 115 mm
Max. Cutting Capacity at 90° [Rectangular]	115 x 130 mm

Profile]	
Max. Cutting Capacity at 90° [L-Shape Profile]	120 x 120 mm
Max. Cutting Capacity at 90° [Rounded Profile]	125 mm
Max. Cutting Capacity at 45° [Square Profile]	98 x 98 mm
Max. Cutting Capacity at 45° [Rectangular Profile]	95 x 105 mm
Max. Cutting Capacity at 45° [L-Shape Profile]	105 x 105 mm
Max. Cutting Capacity at 45° [Rounded Profile]	115 mm
Weight	17.5 kg