

**Part Number: 9223**

Special Audio, Low Noise, RG58, 22 AWG



**Product Description**

Low noise, RG-58/U Type, 22 AWG stranded (7x30) .029" TC conductor, conductive layer on conductor, polyethylene insulation, Duobond® II + TC braid shield (95% coverage), PVC jacket.

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor (Not Riser or Plenum)
----------------------	------------------------------

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	Nominal Diameter	No. of Coax
22	Stranded	TC - Tinned Copper	0.029 in	1

Conductor Count:	1
Conductor Size:	22 AWG

**Insulation**

Layer	Material	Nominal Diameter
1	C-PE - Conductive Polyethylene	0.036 in
2	PE - Polyethylene	0.112 in

**Outer Shield Material**

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum/Polyester/Aluminum	Bonded Duofoil®	100 %
Braid	2	TC - Tinned Copper		95 %

**Outer Jacket Material**

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.195 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
10.8 Ohm/1000ft	10.8 Ohm/1000ft		4.1 Ohm/1000ft	4.1 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Shield
37 pF/ft

**Impedance**

Nominal Characteristic Impedance
50 Ohm

**Delay**

Nominal Delay	Nominal Velocity of Propagation (VP) [%]

1.8 ns/ft	56 %
-----------	------

#### Voltage

##### Voltage Rating [V]

300 V RMS

Electrical Characteristics Notes: NBS Low Noise Test (Modified), MIL-C-17 Paragraph 4.8.14, 8 mV Peak to Peak Max

#### Temperature Range

Non-UL Temp Rating:	80°C
Operating Temp Range:	-40°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight:	24 lbs/1000ft
Max Recommended Pulling Tension:	8.85 lbs
Min Bend Radius/Minor Axis:	2 in

#### Standards

CPR Euroclass:	Eca
RG Type:	58/U Type

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

#### Part Number

##### Variants

Item #	Color	Footnote
9223 010100	Black	
9223 0101000	Black	C
9223 010500	Black	C

Footnote: C - CRATE REEL PUT-UP.

#### Product Notes

Notes: Not recommended for RF use

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.