




The innovative connector (accessory) enables traffic light combinations to be created in a matter of seconds



The way in which the brain processes visual stimuli formed the basis for the development of the EVS technology



- LED EVS Beacon in attractive quadratic form
- Attention-grabbing flickering light
- Extremely powerful signal effect
- Innovative connector to create traffic light combinations
- Easy assembly due to quick-release screws
- Thread/membrane combination keeps cabling requirements to a minimum



Housing: PP-GF, black Lens: PC, transparent

Connection: Screw terminal with wire protection, max. 1.5 mm<sup>2</sup>

Cable diameter max. 8 mm, Cable entry:

optional Cable gland M 20 (accessory)

Wall, base and ceiling mounting Fixing:

**Current consumption:** Max. 200 mA at 24 V

Equipment: Eight self-sealing membranes for cable entry

without tools

Eight integrated M 20 threads, no nuts required

Optional use of a cable gland,

thread length of cable gland  $\leq 9$  mm (accessory)

Incl. snap-on fixing bracket Assembly:

(optional use, see page 136)

## **ORDER SPECIFICATIONS:**

Voltage	12 V	24 V ==	115-230 V~	
red	853 120 54	853 120 55	853 120 60	
green	853 220 54	853 220 55	853 220 60	
yellow	853 320 54	853 320 55	853 320 60	
clear	853 420 54	853 420 55	853 420 60	
blue	853 520 54	853 520 55	853 520 60	

Available: 1st Quarter 2011.

## **ACCESSORIES:**

Connector for traffic light combinations	975 853 01
(For further information see page 119)	
Cable gland M 20 x 1.5 mm	975 853 02
8 mm thread length, required for protection rating IP 67	

## ADDITIONAL INFORMATION:

\* EVS = Enhanced Visibility System or Enhanced Visibility System.

Further informationen can be found in the chapter "Tech-Talk" beginning on page 326.



see page 287



The "EVS" light signal ensures a maximum attention-grabbing effect













