



## Data sheet: BV EI 304 2081

Size 4 a: height 27.0 mm

2,1 VA

ta 70/F

BV EI 304 ...

Several hundreds of typen provide high electrical safety and long service-life for printed circuit boards, household appliances, leisure electronics, heating and control technology as well as in assembly techniques. Transformers for special requirements with lower open-circuit (no-load) loss capacity are also available in the range.

absolutely short-circuit-proof

**minimal size**

test certifications to ENEC 10-, VDE, UL- and CSA-regulations

**vaccum encapsulated, bobbin with dual chamber windings**

temperature class ta 40°C/F and ta 70°C/F

**high electrical safety and long service-life properties**


individually tested with certificate

**excellent temperature fluctuation resistance properties**



self-extinguishing cast housing and sealing material



| Article no. BV | Output ta 40°C/F | prim.V | Connecting pins | Operating point<br>sec. ± 5% | Connecting pins | No-load voltage<br>V ± 5% |
|----------------|------------------|--------|-----------------|------------------------------|-----------------|---------------------------|
| BV EI 304 2081 | 2,1              | 230    | 1-5             | 10 V 210 mA                  | 7-9             | 15,8                      |



Ansicht auf die Stifte



Maße ohne Toleranzangabe ± 0,3 mm.  
Ausführungsänderungen vorbehalten

Dimensions with no indication of tolerances ± 0,3mm.