

Specification Sheet

Part Number: 553-50029

Flexible, flame retardant, heat shrinkable polyolefin tubing meets all military specification.

3:1 shrink ratio enables a wide range of wire sizes to be covered.

Standard colors - yellow, white and black.

Larger pack options result in less box changes.


Center slit and multiple slit versions reduce or eliminate hand cutting.

Nonslip printable liner allows additional marker data to be printed on the reverse side for records and placement instructions.

Use HellermannTyton's Durattach ribbon system for the highest print performance on the market.

Custom box opening allows markers to dispense directly into HellermannTyton thermal transfer printers.

Dispense markers faster and easier with waxed core dispenser.



ShrinkTrak Labels, 1-Sided, Unslit, .5" (12.7mm), PO-X, White, 250/box

| | |
|-----------------------|------------|
| Article Number | 553-50029 |
| Type | HST12-4WH |
| Color | White (WH) |
| Quantity Per | box |

| | |
|---------------------------------------|--|
| Product Description | HellermannTyton's ShrinkTrak™ heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production. |
| Short Description | ShrinkTrak Labels, 1-Sided, Unslit, .5" (12.7mm), PO-X, White, 250/box |
| Global Part Name | HST12-4WH-PO-X-WH |
| Variant | Thin-Wall |
| Width W (Imperial) | 1.9 |
| Width W (Metric) | 48.26 |
| Thickness T (Imperial) | .003 |
| Thickness T (Metric) | .0762 |
| Height H (Imperial) | 0.77 |
| Height H (Metric) | 19.55 |
| Width of Liner (Metric) | 76.2 |
| Width of Liner (Imperial) | 3.0 |
| Outside Diameter OD (Imperial) | 0.5 |

| | |
|--|--|
| Outside Diameter OD (Metric) | 12.7 |
| Outside Diameter Max (Imperial) | 0.5 |
| Outside Diameter Max (Metric) | 12.7 |
| Wall Thickness WT (Imperial) | 0.033 |
| Wall Thickness WT (Metric) | 0.84 |
| Material | Polyolefin, cross-linked (PO-X) |
| Material Shortcut | PO-X |
| US MIL SPEC | SAE-AS81531 SAE-AMS-DTL-23053/5 Class 1 and 3 MIL-STD-202G Method 215K |
| Flammability | UL 224 VW-1 |
| Halogen Free | No |
| Operating Temperature | -67°F to +275°F (-55°C to +135°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Certification/Specification | UL 224 125 °C 600V VW-1 SAE - AMS - DTL-23053/5 Class 1 and 3 SAE - AS81531 |

| | |
|------------------------------------|------------|
| Package Quantity (Imperial) | 250 |
| Package Quantity (Metric) | 250 |
| Customs Number | 3917320000 |
| Labels per Column | 1 |
| Labels per Row | 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-50029](#)