




Data sheet | Item number: 2201-1204



2-conductor through terminal block; with push-button; 1.5 mm<sup>2</sup>; with test port; suitable for Ex i applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 1,50 mm<sup>2</sup>; blue

[www.wago.com/2201-1204](http://www.wago.com/2201-1204)



Data  
Electrical data



### Ratings per IEC/EN 60664-1

|                                 |       |
|---------------------------------|-------|
| Rated voltage (III / 3)         | 800 V |
| Rated impulse voltage (III / 3) | 8 kV  |
| Rated current                   | 18 A  |
| Rated current (2)               | 24 A  |

### Approvals per UL 1059

|                                |       |
|--------------------------------|-------|
| Rated voltage UL (Use Group B) | 600 V |
| Rated current UL (Use Group B) | 15 A  |
| Rated voltage UL (Use Group C) | 600 V |
| Rated current UL (Use Group C) | 15 A  |

### Connection data

|                                      |   |
|--------------------------------------|---|
| Connection technology                | Push-in CAGE CLAMP®   |
| Actuation type                       | Push-in<br>Push-button  |
| Connectable conductor materials      | Copper  |
| Nominal cross section                | 1.5 mm <sup>2</sup>   |
| Solid conductor                      | 0.25 ... 2.5 mm <sup>2</sup> / 22 ... 14 AWG  |
| Solid conductor, push-in termination | 0.75 ... 2.5 mm <sup>2</sup> / 18 ... 14 AWG  |
| Fine-stranded conductor              | 0.25 ... 2.5 mm <sup>2</sup> / 22 ... 14 AWG  |
| Strip length                         | 9 ... 11 mm / 0.35 ... 0.43 inch  |
| Note (conductor cross-section)       | Depending on the conductor characteristic, a conductor with a smaller cross section can also be inserted via push-in termination. |
| Total number of connection points    | 2   |
| Total number of potentials           | 1   |
| Number of levels                     | 1   |
| Type of wiring                       | Front-entry wiring  |
| Number of jumper slots               | 2   |

### Geometrical Data

|                                       |                      |
|---------------------------------------|----------------------|
| Width                                 | 4.2 mm / 0.165 inch  |
| Height from upper-edge of DIN-35 rail | 32.9 mm / 1.295 inch |
| Depth                                 | 48.5 mm / 1.909 inch |

### Mechanical data

|                  |                     |
|------------------|---------------------|
| Design           | horizontal          |
| Type of mounting | DIN-35 rail         |
| Marking level    | Center/side marking |

## Material Data

|                     |                      |
|---------------------|----------------------|
| Color               | blue                 |
| Insulating material | Polyamide 66 (PA 66) |
| Fire load           | 0.089 MJ             |
| Weight              | 4.145 g              |

## Commercial data




|                    |               |
|--------------------|---------------|
| Country of origin  | DE            |
| GTIN               | 4055143694667 |
| Customs Tariff No. | 85369010000   |

## Approvals / Certificates

### Ex-Approvals




| Logo   | Approval                                       | Additional Approval Text | Certificate name   |
|--|--|--------------------------|--|
|    | ATEX<br>Physikalisch Technische Bundesanstalt  | IEC 60079-0              | PTB 18<br>ATEX<br>1004 U (II<br>2 G Ex eb<br>IIC Gb<br>bzw. I M 2<br>Ex eb I Mb) |
|  | IECEX<br>Physikalisch Technische Bundesanstalt | IEC 60079-0              | IECEX PTB<br>18.0011U<br>(Ex eb IIC<br>Gb and Ex<br>eb I Mb)                     |

### Country specific Approvals


| Logo   | Approval                              | Additional Approval Text | Certificate name |
|--|---------------------------------------|--------------------------|------------------|
|  | CCA<br>DEKRA Certification B.V.       | EN 60947                 | NTR NL<br>7664   |
|  | CSA<br>DEKRA Certification B.V.       | C22.2                    | 70173738         |
|  | KEMA/KEUR<br>DEKRA Certification B.V. | EN 60947                 | 71-<br>102875    |

### Ship Approvals

Certificate




| Logo  | Approval  | Additional Approval Text | name                     |
|---|---|--------------------------|--------------------------|
|   | <b>ABS</b><br>American Bureau of Shipping               | -                        | 19-<br>HG1866350-<br>PDA |
|   | <b>DNV GL</b><br>Det Norske Veritas, Germanischer Lloyd | -                        | TAE00003JT               |
|  | <b>LR</b><br>Lloyds Register                            | -                        | 19/20050                 |

#### UL-Approvals


| Logo   | Approval                                       | Additional Approval Text | Certificate name |
|--|--|--------------------------|------------------|
|  | <b>cURus</b><br>Underwriters Laboratories Inc. | UL 1059                  | 4788308064       |

#### Compatible products

##### tools




















|  |  |  |
|--|--|--|
|  | <b>Item no.: 210-647</b><br>Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft              | <a href="http://www.wago.com/210-647">www.wago.com/210-647</a> |
|  | <b>Item no.: 210-648</b><br>Operating tool with partially insulated shaft; Blade (2.5 x 0.4) mm; short; angled | <a href="http://www.wago.com/210-648">www.wago.com/210-648</a> |
|  | <b>Item no.: 210-719</b><br>Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft              | <a href="http://www.wago.com/210-719">www.wago.com/210-719</a> |


















##### plug
















|  |   |  |
|--|---|--|
|  | <b>Item no.: 2002-880</b><br>Empty component plug housing; 10.4 mm wide; 2-pole; Type 4; gray | <a href="http://www.wago.com/2002-880">www.wago.com/2002-880</a> |
|--|---|--|



















##### End plate

|  |  |  |
|--|--|--|
|  | <b>Item no.: 2002-1291</b><br>End and intermediate plate; 0.8 mm thick; gray | <a href="http://www.wago.com/2002-1291">www.wago.com/2002-1291</a> |
|--|--|--|






|  |  |  |
|--|--|--|
|    | <b>Item no.: 2002-1292</b><br>End and intermediate plate; 0.8 mm thick; orange                                       | <a href="http://www.wago.com/2002-1292">www.wago.com/2002-1292</a>               |
|    | <b>Item no.: 2002-1293</b><br>Separator plate; 2 mm thick; oversized; gray   | <a href="http://www.wago.com/2002-1293">www.wago.com/2002-1293</a>               |
|    | <b>Item no.: 2002-1294</b><br>Separator plate; 2 mm thick; oversized; orange   | <a href="http://www.wago.com/2002-1294">www.wago.com/2002-1294</a>               |
| <b>Jumper</b>  |  |  |
|    | <b>Item no.: 2001-402</b><br>Push-in type jumper bar; insulated; 2-way; Nominal current 18 A; light gray             | <a href="http://www.wago.com/2001-402">www.wago.com/2001-402</a>                 |
|    | <b>Item no.: 2001-403</b><br>Push-in type jumper bar; insulated; 3-way; Nominal current 18 A; light gray             | <a href="http://www.wago.com/2001-403">www.wago.com/2001-403</a>                 |
|    | <b>Item no.: 2001-404</b><br>Push-in type jumper bar; insulated; 4-way; Nominal current 18 A; light gray             | <a href="http://www.wago.com/2001-404">www.wago.com/2001-404</a>                 |
|    | <b>Item no.: 2001-405</b><br>Push-in type jumper bar; insulated; 5-way; Nominal current 18 A; light gray             | <a href="http://www.wago.com/2001-405">www.wago.com/2001-405</a>                 |
|    | <b>Item no.: 2001-405/011-000</b><br>Star point jumper; insulated; 3-way (1-3-5); IN = IN terminal block; light gray | <a href="http://www.wago.com/2001-405/011-000">www.wago.com/2001-405/011-000</a> |
|   | <b>Item no.: 2001-406</b><br>Push-in type jumper bar; insulated; 6-way; Nominal current 18 A; light gray             | <a href="http://www.wago.com/2001-406">www.wago.com/2001-406</a>                 |
|  | <b>Item no.: 2001-406/020-000</b><br>Delta jumper; insulated; 1-2 3-4 5-6; IN = IN terminal block; light gray        | <a href="http://www.wago.com/2001-406/020-000">www.wago.com/2001-406/020-000</a> |
|  | <b>Item no.: 2001-407</b><br>Push-in type jumper bar; insulated; 7-way; Nominal current 18 A; light gray             | <a href="http://www.wago.com/2001-407">www.wago.com/2001-407</a>                 |
|  | <b>Item no.: 2001-408</b><br>Push-in type jumper bar; insulated; 8-way; Nominal current 18 A; light gray             | <a href="http://www.wago.com/2001-408">www.wago.com/2001-408</a>                 |
|  | <b>Item no.: 2001-409</b><br>Push-in type jumper bar; insulated; 9-way; Nominal current 18 A; light gray             | <a href="http://www.wago.com/2001-409">www.wago.com/2001-409</a>                 |
|  | <b>Item no.: 2001-410</b><br>Push-in type jumper bar; insulated; 10-way; Nominal current 18 A; light gray            | <a href="http://www.wago.com/2001-410">www.wago.com/2001-410</a>                 |
|  | <b>Item no.: 2001-433</b><br>Push-in type jumper bar; insulated; from 1 to 3; Nominal current 18 A; light gray       | <a href="http://www.wago.com/2001-433">www.wago.com/2001-433</a>                 |
|  | <b>Item no.: 2001-434</b><br>Push-in type jumper bar; insulated; from 1 to 4; Nominal current 18 A; light gray       | <a href="http://www.wago.com/2001-434">www.wago.com/2001-434</a>                 |
|  | <b>Item no.: 2001-435</b><br>Push-in type jumper bar; insulated; from 1 to 5; Nominal current 18 A; light gray       | <a href="http://www.wago.com/2001-435">www.wago.com/2001-435</a>                 |
|  | <b>Item no.: 2001-436</b><br>Push-in type jumper bar; insulated; from 1 to 6; Nominal current 18 A; light gray       | <a href="http://www.wago.com/2001-436">www.wago.com/2001-436</a>                 |
|  | <b>Item no.: 2001-437</b><br>Push-in type jumper bar; insulated; from 1 to 7; Nominal current 18 A; light gray       | <a href="http://www.wago.com/2001-437">www.wago.com/2001-437</a>                 |

|  |  |  |
|--|--|--|
|    | <b>Item no.: 2001-438</b><br>Push-in type jumper bar; insulated; from 1 to 8; Nominal current 18 A; light gray   | <a href="http://www.wago.com/2001-438">www.wago.com/2001-438</a>                 |
|    | <b>Item no.: 2001-439</b><br>Push-in type jumper bar; insulated; from 1 to 9; Nominal current 18 A; light gray   | <a href="http://www.wago.com/2001-439">www.wago.com/2001-439</a>                 |
|    | <b>Item no.: 2001-440</b><br>Push-in type jumper bar; insulated; from 1 to 10; Nominal current 18 A; light gray  | <a href="http://www.wago.com/2001-440">www.wago.com/2001-440</a>                 |
|    | <b>Item no.: 2006-499</b><br>Step-down jumper; insulated; from 6/4 mm <sup>2</sup> to 4/2.5/1.5 mm <sup>2</sup> ; Nominal current 32 A; light gray   | <a href="http://www.wago.com/2006-499">www.wago.com/2006-499</a>                 |
|    | <b>Item no.: 2009-412</b><br>Push-in type wire jumper; insulated; wire length 60 mm; Conductor cross section 1.5 mm <sup>2</sup> ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks; black         | <a href="http://www.wago.com/2009-412">www.wago.com/2009-412</a>                 |
|    | <b>Item no.: 2009-414</b><br>Push-in type wire jumper; insulated; wire length 110 mm; Conductor cross section 1.5 mm <sup>2</sup> ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks; black        | <a href="http://www.wago.com/2009-414">www.wago.com/2009-414</a>                 |
|    | <b>Item no.: 2009-414/000-005</b><br>Push-in type wire jumper; insulated; wire length 110 mm; Conductor cross section 1.5 mm <sup>2</sup> ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks; red  | <a href="http://www.wago.com/2009-414/000-005">www.wago.com/2009-414/000-005</a> |
|    | <b>Item no.: 2009-414/000-006</b><br>Push-in type wire jumper; insulated; wire length 110 mm; Conductor cross section 1.5 mm <sup>2</sup> ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks; blue | <a href="http://www.wago.com/2009-414/000-006">www.wago.com/2009-414/000-006</a> |
|    | <b>Item no.: 2009-416</b><br>Push-in type wire jumper; insulated; wire length 250 mm; Conductor cross section 1.5 mm <sup>2</sup> ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks; black        | <a href="http://www.wago.com/2009-416">www.wago.com/2009-416</a>                 |
|   | <b>Item no.: 210-103</b><br>Wire commoning chain; insulated; 50 connections; black   | <a href="http://www.wago.com/210-103">www.wago.com/210-103</a>                   |
|  | <b>Item no.: 210-123</b><br>Wire commoning chain; insulated; 50 connections  | <a href="http://www.wago.com/210-123">www.wago.com/210-123</a>                   |
| <b>Marking accessories</b>   |  |  |
|  | <b>Item no.: 2009-110</b><br>Marking strips; on reel; not stretchable; plain; snap-on type; white  | <a href="http://www.wago.com/2009-110">www.wago.com/2009-110</a>                 |
|  | <b>Item no.: 2009-114</b><br>WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; white  | <a href="http://www.wago.com/2009-114">www.wago.com/2009-114</a>                 |
|  | <b>Item no.: 2009-114/000-002</b><br>WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; yellow   | <a href="http://www.wago.com/2009-114/000-002">www.wago.com/2009-114/000-002</a> |
|  | <b>Item no.: 2009-114/000-005</b><br>WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; red  | <a href="http://www.wago.com/2009-114/000-005">www.wago.com/2009-114/000-005</a> |
|  | <b>Item no.: 2009-114/000-006</b><br>WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; blue   | <a href="http://www.wago.com/2009-114/000-006">www.wago.com/2009-114/000-006</a> |
|  | <b>Item no.: 2009-114/000-007</b><br>WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; gray   | <a href="http://www.wago.com/2009-114/000-007">www.wago.com/2009-114/000-007</a> |





|  |  |  |
|--|--|--|
|    | <b>Item no.: 2009-114/000-012</b><br>WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; orange     | <a href="http://www.wago.com/2009-114/000-012">www.wago.com/2009-114/000-012</a> |
|    | <b>Item no.: 2009-114/000-023</b><br>WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; green      | <a href="http://www.wago.com/2009-114/000-023">www.wago.com/2009-114/000-023</a> |
|    | <b>Item no.: 2009-114/000-024</b><br>WMB-Inline; for Smart Printer; on reel; stretchable 4 - 4.2 mm; plain; snap-on type; violet     | <a href="http://www.wago.com/2009-114/000-024">www.wago.com/2009-114/000-024</a> |
|    | <b>Item no.: 793-4501</b><br>WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; white                           | <a href="http://www.wago.com/793-4501">www.wago.com/793-4501</a>                 |
|    | <b>Item no.: 793-4501/000-002</b><br>WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; yellow                  | <a href="http://www.wago.com/793-4501/000-002">www.wago.com/793-4501/000-002</a> |
|    | <b>Item no.: 793-4501/000-005</b><br>WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; red                     | <a href="http://www.wago.com/793-4501/000-005">www.wago.com/793-4501/000-005</a> |
|    | <b>Item no.: 793-4501/000-006</b><br>WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; blue                    | <a href="http://www.wago.com/793-4501/000-006">www.wago.com/793-4501/000-006</a> |
|  | <b>Item no.: 793-4501/000-007</b><br>WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; gray                    | <a href="http://www.wago.com/793-4501/000-007">www.wago.com/793-4501/000-007</a> |
|  | <b>Item no.: 793-4501/000-012</b><br>WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; orange                  | <a href="http://www.wago.com/793-4501/000-012">www.wago.com/793-4501/000-012</a> |
|  | <b>Item no.: 793-4501/000-017</b><br>WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; light green             | <a href="http://www.wago.com/793-4501/000-017">www.wago.com/793-4501/000-017</a> |
|  | <b>Item no.: 793-4501/000-023</b><br>WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; green                   | <a href="http://www.wago.com/793-4501/000-023">www.wago.com/793-4501/000-023</a> |
|  | <b>Item no.: 793-4501/000-024</b><br>WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type; violet                  | <a href="http://www.wago.com/793-4501/000-024">www.wago.com/793-4501/000-024</a> |
| <b>Carrier rail</b>  |  |  |
|  | <b>Item no.: 210-112</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm | <a href="http://www.wago.com/210-112">www.wago.com/210-112</a>                   |
|  | <b>Item no.: 210-113</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715                  | <a href="http://www.wago.com/210-113">www.wago.com/210-113</a>                   |
|  | <b>Item no.: 210-114</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715                   | <a href="http://www.wago.com/210-114">www.wago.com/210-114</a>                   |
|  | <b>Item no.: 210-115</b>   |  |

|  |  |  |
|--|--|--|
|    | Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm   | <a href="http://www.wago.com/210-115">www.wago.com/210-115</a>   |
|    | <b>Item no.: 210-118</b><br>Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715   | <a href="http://www.wago.com/210-118">www.wago.com/210-118</a>   |
|    | <b>Item no.: 210-196</b><br>Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored   | <a href="http://www.wago.com/210-196">www.wago.com/210-196</a>   |
|    | <b>Item no.: 210-197</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715   | <a href="http://www.wago.com/210-197">www.wago.com/210-197</a>   |
|    | <b>Item no.: 210-198</b><br>Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; copper-colored  | <a href="http://www.wago.com/210-198">www.wago.com/210-198</a>   |
| <b>ferrule</b>   |  |  |
|     | <b>Item no.: 216-241</b><br>Ferrule; Sleeve for 0.5 mm <sup>2</sup> / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white | <a href="http://www.wago.com/216-241">www.wago.com/216-241</a>   |
|     | <b>Item no.: 216-242</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray | <a href="http://www.wago.com/216-242">www.wago.com/216-242</a>   |
|     | <b>Item no.: 216-243</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red     | <a href="http://www.wago.com/216-243">www.wago.com/216-243</a>   |
|   | <b>Item no.: 216-244</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black | <a href="http://www.wago.com/216-244">www.wago.com/216-244</a>   |
| <b>Insulation stop</b>   |  |  |
|  | <b>Item no.: 2001-171</b><br>Insulation stop; 0.25 - 0.5 mm <sup>2</sup> ; 5 pieces/strip; light gray  | <a href="http://www.wago.com/2001-171">www.wago.com/2001-171</a> |
| <b>check</b>   |  |  |
|  | <b>Item no.: 2001-511</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 1-pole; 1,50 mm <sup>2</sup> ; gray   | <a href="http://www.wago.com/2001-511">www.wago.com/2001-511</a> |
|  | <b>Item no.: 2001-549</b><br>Spacer module; modular; e.g., for bridging commoned terminal blocks; gray   | <a href="http://www.wago.com/2001-549">www.wago.com/2001-549</a> |
|  | <b>Item no.: 2001-552</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 2-pole; 1,50 mm <sup>2</sup> ; gray   | <a href="http://www.wago.com/2001-552">www.wago.com/2001-552</a> |
|  | <b>Item no.: 2001-553</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 3-pole; 1,50 mm <sup>2</sup> ; gray   | <a href="http://www.wago.com/2001-553">www.wago.com/2001-553</a> |
|  | <b>Item no.: 2001-554</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 4-pole; 1,50 mm <sup>2</sup> ; gray   | <a href="http://www.wago.com/2001-554">www.wago.com/2001-554</a> |
|  | <b>Item no.: 2001-555</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 5-pole; 1,50 mm <sup>2</sup> ; gray   | <a href="http://www.wago.com/2001-555">www.wago.com/2001-555</a> |
|  | <b>Item no.: 2001-556</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 6-pole; 1,50 mm <sup>2</sup> ; gray   | <a href="http://www.wago.com/2001-556">www.wago.com/2001-556</a> |
|  | <b>Item no.: 2001-557</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 7-pole; 1,50 mm <sup>2</sup> ; gray   | <a href="http://www.wago.com/2001-557">www.wago.com/2001-557</a> |



|  |   |  |
|--|---|--|
|  | <b>Item no.: 2001-558</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 8-pole; 1,50 mm <sup>2</sup> ; gray              | <a href="http://www.wago.com/2001-558">www.wago.com/2001-558</a> |
|  | <b>Item no.: 2001-559</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 9-pole; 1,50 mm <sup>2</sup> ; gray              | <a href="http://www.wago.com/2001-559">www.wago.com/2001-559</a> |
|  | <b>Item no.: 2001-560</b><br>Modular TOPJOB®S connector; modular; for jumper contact slot; 10-pole; 1,50 mm <sup>2</sup> ; gray             | <a href="http://www.wago.com/2001-560">www.wago.com/2001-560</a> |
|  | <b>Item no.: 2009-174</b><br>Test plug adapter; for 4 mm Ø test plugs; for testing TOPJOB®S rail-mounted terminal blocks; gray              | <a href="http://www.wago.com/2009-174">www.wago.com/2009-174</a> |
|  | <b>Item no.: 2009-182</b><br>Testing tap; for max. 2.5 mm <sup>2</sup> ; tool-free connection for individual test wires 0.08 - 2.5 mm; gray | <a href="http://www.wago.com/2009-182">www.wago.com/2009-182</a> |

**General accessories**

|  |  |  |
|--|--|--|
|    | <b>Item no.: 2002-880/1000-411</b><br>Component plug; 2-pole; with diode 1N4007; 10.4 mm wide; Operating temperature 85°C max.; gray | <a href="http://www.wago.com/2002-880/1000-411">www.wago.com/2002-880/1000-411</a> |
|    | <b>Item no.: 2002-880/1000-541</b><br>Component plug; 2-pole; LED (red); 10.4 mm wide; Operating temperature 85°C max.; gray         | <a href="http://www.wago.com/2002-880/1000-541">www.wago.com/2002-880/1000-541</a> |
|    | <b>Item no.: 2002-880/1000-542</b><br>LED module; with red LED; 10.4 mm wide; 30 - 65 V; Operating temperature 85°C max.             | <a href="http://www.wago.com/2002-880/1000-542">www.wago.com/2002-880/1000-542</a> |
|  | <b>Item no.: 2002-880/1000-836</b><br>Component plug; 2-pole; LED (red); 10.4 mm wide; Operating temperature 85°C max.; gray         | <a href="http://www.wago.com/2002-880/1000-836">www.wago.com/2002-880/1000-836</a> |

**Downloads**

**Documentation**

**Bid Text**

|           |  |                 |          |
|-----------|--|-----------------|----------|
| 2201-1204 |  | docx<br>15.0 kB | Download |
|-----------|--|-----------------|----------|

**Additional Information**

|                        |             |               |          |
|------------------------|-------------|---------------|----------|
| Technical explanations | Apr 3, 2019 | pdf<br>2.1 MB | Download |
|------------------------|-------------|---------------|----------|

**CAD/CAE-Data**

**CAD data**

|                       |  |     |          |
|-----------------------|--|-----|----------|
| 3D Download 2201-1204 |  | URL | Download |
|-----------------------|--|-----|----------|

**EPLAN**

|                   |  |  |          |
|-------------------|--|--|----------|
| EPLAN Data Portal |  |  | Download |
|-------------------|--|--|----------|



Subject to changes.

---

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.