

## Diode block - EMG 22-DIO 4E-1N5408 - 2952790

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Diode module, with 4 diodes, individually wired, diode type 1N 5408


The illustration shows version EMG 22-DIO 4E

### Why buy this product

- Electrical decoupling of messages in fault reporting systems
- Spark-suppression diodes for limiting surge voltages of inductive loads



### Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 084486
Weight per Piece (excluding packing)	47.25 g
Custom tariff number	85411000
Country of origin	Germany

### Technical data

#### Dimensions

Width	22.5 mm
Height	75 mm
Depth	55 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

#### General

Diode type	1 N 5408
Max. operating voltage	250 V AC
Peak reverse voltage per diode	1000 V

# Diode block - EMG 22-DIO 4E-1N5408 - 2952790

## Technical data

### General

Reverse current per diode	10 µA
Conducting state voltage per diode	approx. 0.8 V
Conducting state current per diode	1.5 A (with single load)
	1 A (with simultaneous loads)
Overvoltage category	III, basic insulation (as per EN 50178)
Mounting position	any
Assembly instructions	In rows with zero spacing

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section flexible min.	0.2 mm <sup>2</sup>
Conductor cross section flexible max.	2.5 mm <sup>2</sup>
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12
Stripping length	8 mm
Screw thread	M3
Connection method	Screw connection

### Standards and Regulations

Low Voltage Directive	Conformance with LV directive 2006/95/EC
Conformance	CE-compliant

## Classifications

### eCl@ss

eCl@ss 4.0	27250312
eCl@ss 4.1	27260801
eCl@ss 5.0	27260801
eCl@ss 5.1	27260801
eCl@ss 6.0	27242602
eCl@ss 7.0	27242602
eCl@ss 8.0	27371010

### ETIM

ETIM 2.0	EC001432
ETIM 3.0	EC001597
ETIM 4.0	EC001597
ETIM 5.0	EC000683

### UNSPSC

UNSPSC 6.01	30211506
-------------	----------

# Diode block - EMG 22-DIO 4E-1N5408 - 2952790

## Classifications

### UNSPSC

UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	39121008

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

## Accessories

### Accessories

Marking material - EMG-GKS 12 - 2947035



Equipment marker, width 12 mm

## Drawings

## Diode block - EMG 22-DIO 4E-1N5408 - 2952790

Circuit diagram

