


Vishay BCcomponents

Interference Suppression Film Capacitor - Class Y2 Radial MKP 300 V_{AC} - Line to Ground Application



FEATURES

- AEC-Q200 qualified (rev. C)
- THB grade IIB compliant (pitch \geq 15 mm): 85 °C, 85 % RH, 500 h at U_{RAC}
- High temperature capabilities, up to 125 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912





RoHS COMPLIANT


APPLICATIONS

- Standard line bypass (between line and ground) Y2 applications
- Line bypass application for continuous operation
 See also application note: www.vishav.com/doc?28153

OHICK DEFEDENCE DATA	
QUICK REFERENCE DATA	
Capacitance range (E12 series)	0.001 μF to 0.47 μF (preferred values acc. to E6)
Capacitance tolerance	± 20 %, ± 10 %, ± 5 %
Rated AC voltage	300 V _{AC} ; 50 Hz to 60 Hz
Permissible DC voltage	1000 V _{DC} at 105 °C
Climatic testing class acc. to IEC 60068-1	55/105/56/C for product volumes ≤ 1750 mm ³ 55/105/56/B for volumes > 1750 mm ³
Rated temperature	105 °C
Maximum permissible temperature	125 °C for limited time
Reference standards	IEC 60384-14:2013; IEC 60384-14:2013 / AMD1:2016 EN 60384-14:2013 + AMD1:2016 IEC 60065 requires pass. flamm. class B for volumes > 1750 mm ³ UL 60384-14 2 nd edition; ENEC; CSA E60384-1:14 3 rd edition
Dielectric	Polypropylene film
Electrodes	Metallized film
Construction	Series construction (for > 10 mm pitch) Triple construction (for 7.5 mm and 10 mm pitch)
Encapsulation	Plastic case, epoxy resin sealed, flame retardant class UL 94 V-0
Leads	Tinned wire
Marking	C-value; tolerance; rated voltage; sub-class; manufacturer's type designation; code for dielectric material; manufacturer location, year and week; manufacturer's logo or name; safety approvals

Note


For more detailed data and test requirements, contact <u>rfi@vishay.com</u>



Revision: 14-Dec-2021 1 Document Number: 28114



COMPOSITION OF CATALOG NUMBER



TYPE	PACKAGING	LEAD CONFIGURATION (see tables for details)	C-TOL.	PREFERRED TYPES		
	l accesion beau	Lead length 3.5 mm + 1 mm / - 0.5 mm (pitch 7.5 mm and 10 mm) Lead length 3.5 mm ± 0.3 mm (pitch > 10 mm)		BFC2 338 60		
	Loose in box	Lead length 5.0 mm ± 1.0 mm	20.07	BFC2 338 62		
338 6 Y2		Lead length 25.0 mm ± 2.0 mm	± 20 %	BFC2 338 64		
12	Taped ammo ⁽¹⁾	Pitch = 7.5 mm H = 18.5 mm; P ₀ = 12.7 mm		BFC2 338 66		
	Taped reel	Pitch 7.5 mm only to 15 mm; H = 18.5 mm		BFC2 338 68		
		ALTERNATIVE PITCH SIZES		ON REQUEST		
338 6	Loose in box	Lead length 3.5 mm + 1 mm / - 0.5 mm (pitch 7.5 mm and 10 mm) Lead length 3.5 mm ± 0.3 mm (pitch > 10 mm)	± 20 %	See tables for detail		
Y2	Loose in box	Lead length 5.0 mm ± 1.0 mm	± 20 %	See tables for detail		
		Lead length 25.0 mm ± 2.0 mm				
		ALTERNATIVE TAPED VERSIONS		ON REQUEST		
338 6	Taped reel (1)	Pitch = 7.5 mm and 10.0 mm H = 18.5 mm; P_0 = 12.7 mm; reel diameter = 500 mm		See tables for detail		
Y2	Tapou reci	Pitch bent back to 7.5 mm H = 16.0 mm; P_0 = 15.0 mm; reel diameter = 500 mm	± 20 %			
		ALTERNATIVE C-TOL.		ON REQUEST		
		Lead length 3.5 mm + 1 mm / - 0.5 mm (pitch 7.5 mm and 10 mm)	± 10 %			
		Lead length 3.5 mm ± 0.3 mm (pitch > 10 mm)	±5%			
	Loose in box	Lead length 5.0 mm ± 1.0 mm	± 10 %			
	Loose III box	Lead length 5.0 mm ± 1.0 mm	±5%			
		Lead length 25.0 mm ± 2.0 mm	± 10 %			
338 6		Lead length 25.0 mm ± 2.0 mm	± 5 %	Coo tables for detail		
Y2	Taped ammo (1)	Pitch = 7.5 mm	± 10 %	See tables for detail		
	raped amino V	$H = 18.5 \text{ mm}; P_0 = 12.7 \text{ mm}$	±5%			
		Pitch bent back to 7.5 mm	± 10 %			
	Taped reel (1)	$H = 16.0 \text{ mm}$; $P_0 = 15.0 \text{ mm}$; reel diameter = 500 mm	± 5 %			
	raped reer (*)	Pitch = 7.5 mm and 10 mm	± 10 %]		
		$H = 18.5 \text{ mm}$; $P_0 = 12.7 \text{ mm}$; reel diameter = 500 mm	±5%	1		

Note

⁽¹⁾ For detailed tape specification refer to "Packaging Information" www.vishay.com/doc?28139



Vishay BCcomponents

SPECIFIC REFERENCE DATA					
DESCRIPTION	VAL	UE			
Rated AC voltage (U _{RAC})	300	V			
Permissible DC voltage (U _{RDC})	1000	0 V			
Tangent of loss angle	at 1 kHz	at 10 kHz			
C ≤ 470 nF	≤ 10 x 10 ⁻⁴	≤ 20 x 10 ⁻⁴			
Rated voltage pulse slope (dU/dt) _R at 420 V _{DC}	100 \	//μs			
R between leads, for C \leq 0.33 μ F at 100 V; 1 min	> 15 000 MΩ				
RC between leads, for C > 0.33 µF at 100 V; 1 min	> 500	00 s			
R between leads and case; 100 V; 1 min	> 30 00	00 MΩ			
Withstanding (DC) voltage (cut off current 10 mA) (1); rise time ≤ 1000 V/s	3400 V;	1 min			
Withstanding (AC) voltage between leads and case	2100 V; 1 min				
Rated temperature	105	°C			
Maximum permissible temperature	125 °C up to 500 h				

Note

⁽¹⁾ See "Voltage Proof Test for Metalized Film Capacitors": www.vishay.com/doc?28169

ELE	ECTRIC	CAL DATA AN	D ORD	PERING IN						01/40	INO	
					CATALOG NUMBER BFC2 338 6X XXX AND PACKAGING LOOSE IN BOX REFI							
U _{RAC}	CAP.	DIMENSIONS	MASS	SHORT LEADS LONG LEADS					AMMOPACK		REEL Ø = 500 mm ⁽¹⁾⁽²⁾	
(V)	(μF)	w x h x l (mm)	(g) ⁽³⁾	I _t = 3.5 mm + 1 mm / - 0.5 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ
		PITCH	l = 7.5 n	nm ± 0.4 mm	; d _t = 0.50 mr	n ± 0.0	5 mm; C-T	OL. = ±	± 20 % (U _{RDC} =	1000 V		
	0.0010 0.0012			60102 60122	62102 62122		64102 64122		66102 66122		68129 68131	
	0.0015 0.0018	4.0 x 9.0 x 10.0	0.4	60152 60182	62152 62182	1500	64152 64182	1000	66152 66182	1250	68132 68133	2500
	0.0022 0.0027			60222 60272	62222 62272		64222 64272		66222 66272		68134 68135	
	0.0033 0.0039	5.0 x 10.5 x 10.0	0.4	60332 60392	62332 62392	1000	64332 64392	1250	66332 66392	1000	68136 68137	2000
	0.0047 0.0056	6.0 x 11.5 x 10.0	0.8	60472 60562	62472 62562	750	64472 64562	1000	66472 66562	750	68138 68139	1900
		PITC	d = 7.5 n	nm ± 0.4 mm	; d _t = 0.50 mr	n ± 0.0	5 mm; C-T	OL. = ±	± 10 % (U _{RDC} =	1000 V)	
	0.0010		9.0 x 10.0 0.4	61102	63102		65102	1000	67102	1250	68179	
	0.0012			61122	63122		65122		67122		68181	
	0.0015 0.0018	4.0 x 9.0 x 10.0		61152	63152	1500	65152		67152 67182		68182 68183	2500
300	0.0018			61182 61222	63182 63222		65182 65222		67222		68184	
	0.0027			61272	63272		65272		67272		68185	
	0.0033 0.0039	5.0 x 10.5 x 10.0	0.4	61332 61392	63332 63392	1000	65332 65392	1250	67332 67392	1000	68186 68187	2000
	0.0047 0.0056	6.0 x 11.5 x 10.0	0.8	61472 61562	63472 63562	750	65472 65562	1000	67472 67562	750	68188 68189	1900
		PITC	H = 7.5 ı	mm ± 0.4 mm	n; d _t = 0.50 m	m ± 0.0)5 mm; C-T	OL. =	± 5 % (U _{RDC} = 1	000 V)		
	0.0010 0.0012			68215 68216	68225 68226		68235 68236		68335 68336		68346 68347	
	0.0015 0.0018	4.0 x 9.0 x 10.0	0.4	68217 68218	68227 68228	1500	68237 68238	1000	68337 68338	1250	68348 68349	2500
	0.0022			68219	68229		68239		68339		68351	_
	0.0027 0.0033	5.0 x 10.5 x 10.0	0.4	68221 68222	68231 68232	1000	68241 68242	1250	68341 68342	1000	68352 68353	2000
	0.0039 0.0047	6.0 x 11.5 x 10.0	0.8	68223 68224	68233 68234	750	68243 68244	1000	68343 68344	750	68354 68355	1900

- SPQ = Standard Packing Quantity
- (1) H = in-tape height; P₀ = sprocket hole distance; for detailed specifications refer to packaging information: www.vishay.com/doc?28139
 (2) Reel diameter = 365 mm is available on request
- (3) Weight for short lead product only



Vishay BCcomponents

ELE	ELECTRICAL DATA AND ORDERING INFORMATION - PITCH 10 mm											
					CATALO	OG NU	MBER BFC	2 338	6X XXX AND PA	CKAG	ING	
		DIMENSIONS			LOOSE	N BOX			AMMOPAC	cĸ	REEL	(4)(0)
U _{RAC} (V)	CAP. (µF)	wxhxl	MASS (g) ⁽³⁾		RT LEADS	1	LONG LE	ADS			Ø = 500 mm	(1)(2)
(•)	(μ.)	(mm)	(9)	l _t = 3.5 mm + 1 mm / - 0.5 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ
		PITCH	l = 10.0 r	mm ± 0.4 mm	; d _t = 0.60 m	m ± 0.0	6 mm; C-T	OL. =	± 20 % (U _{RDC} =	1000 V	/)	
	0.0010			68392	68401		68409				68418	
	0.0012			68393	68402		68411				68419	
	0.0015			68394	68403		68412				68421	
	0.0018	4.0 x 10.0 x 12.5	0.6	68395	68404	1000	68413	1250			68422	1400
	0.0022	4.0 X 10.0 X 12.5	0.0	68396	68405	1000	68414	1230			68423	1400
	0.0027			68397	68406		68415				68424	
	0.0033			68398	68407		68416		-	-	68425	
	0.0039			68399	68408		68417				68426	
	0.0047			68101	68106		68112				68141	
	0.0056	5.0 x 11.0 x 12.5	0.82	68102	68107	1000	68113	1000			68142	1100
	0.0068			68103	68108		68114				68143	
	0.0082	6.0 x 12.0 x 12.5	1.1	68104	68109	750	68115	750			68144	900
	0.010	0.0 X 12.0 X 12.5	1.1	68105	68111	750	68116	750			68145	900
	PITCH = 10.0 mm \pm 0.4 mm; d _t = 0.60 mm \pm 0.06 mm; C-TOL. = \pm 10 % (U _{RDC} = 1000 V)											
	0.0010			68436	68445		68454				68463	
	0.0012			68437	68446		68455				68464	
	0.0015			68438	68447		68456				68465	•
	0.0018			68439	68448		68457				68466	-
	0.0022	4.0 x 10.0 x 12.5	0.6	68441	68449	1000	68458	1250			68467	1400
000	0.0027			68442			68459				68468	-
300					68451				-	-		-
	0.0033			68443	68452		68461				68469	_
	0.0039			68444	68453		68462				68471	
	0.0047	5.0 x 11.0 x 12.5	0.82	68159	68164	1000	68168	1000			68191	1100
	0.0056	0.0 % 1.110 % 12.0	0.02	68161	68165	.000	68169				68192	
	0.0068	6.0 x 12.0 x 12.5	1.1	68162	68166	750	68171	750			68193	900
	0.0082	0.0 X 12.0 X 12.3	1.1	68163	68167	730	68172	730			68194	900
		PITCH	H = 10.0	mm ± 0.4 mn	n; d _t = 0.60 m	m ± 0.	06 mm; C-	TOL. =	± 5 % (U _{RDC} =	1000 V)	
	0.0010			68481	68489		68498				68507	
	0.0012			68482	68491		68499				68508	
	0.0015			68483	68492		68501				68509	
	0.0018			68484	68493		68502				68511	
	0.0022	4.0 x 10.0 x 12.5	0.6	68485	68494	1000	68503	1250			68512	1400
	0.0027			68486			68504				68513	
					68495				-	-		
	0.0033			68487	68496		68505				68514	
	0.0039			68488	68497		68506				68515	<u> </u>
	0.0047	5.0 x 11.0 x 12.5	0.82	68245	68249	1000	68254	1000			68357	1100
	0.0056			68246	68251		68255				68358	
	0.0068	6.0 x 12.0 x 12.5	1.1	68247	68252	750	68256	750			68359	900
	0.0082	0.0 X 12.0 X 12.0	'.'	68248	68253	7.50	68257	1 30			68361	500

- SPQ = Standard Packing Quantity
- (1) H = in-tape height; P₀ = sprocket hole distance; for detailed specifications refer to packaging information: <u>www.vishay.com/doc?28139</u>
- (2) Reel diameter = 365 mm is available on request
- (3) Weight for short lead product only



ELE	ECTRICAL DATA AND ORDERING INFORMATION - PITCH 15 mm											
					CATALO	OG NU	MBER BFC	2 338	6X XXX AND PA	CKAG	iING	
		DIMENSIONS		LOOSE IN BOX					AMMOPAC	`K	REEL	
URAC	CAP.	w x h x l	MASS (g) ⁽³⁾	SHC	RT LEADS		LONG LE	ADS	AMMOI AON		$Ø = 500 \text{ mm}^{(1)(2)}$	
(V)	(μF)	(mm)	(9)	l _t = 3.5 mm ± 0.3 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ
		PITCH	= 15.0 n	nm ± 0.4 mm	; d _t = 0.60 mr	m ± 0.0	6 mm; C-1	ΓOL. =	± 20 % (U _{RDC} =	1000	v)	
	0.0068			60682	62682		64682				68146	
	0.0082	E 0 × 11 0 × 17 E	1.0	60822	62822	1000	64822	1000			68147	1100
	0.010	5.0 x 11.0 x 17.5	1.0	60103	62103	1000	64103	1000			68148	1100
	0.012			60123	62123		64123		-	-	68149	
	0.015			60153	62153		64153				68151	
	0.018	6.0 x 12.0 x 17.5	1.4	60183	62183	1000	64183	1000			68152	900
		PITCH	= 15.0 n	nm ± 0.4 mm	; d _t = 0.80 mr	m ± 0.0	8 mm; C-1	ГОL. =	± 20 % (U _{RDC} =	1000	V)	l
	0.022			60223	62223		64223				68153	
	0.027	7.0 x 13.5 x 17.5	1.8	60273	62273	750	64273	500			68154	800
	0.033			60333	62333		64333		_		68155	
	0.039	8.5 x 15.0 x 17.5	2.4	60393	62393	750	64393	500		-	68156	650
	0.047			60473	62473		64473					68157
	0.056	10.0 x 16.5 x 17.5	3.0	60563	62563	500	64563	450			68158	600
	0.000	PITCH	l = 15.0 r			m + 0.0		OL =	<u> </u> ± 10 % (U _{RDC} =	1000 \		
	0.0068	1 11 011	1 - 10.01	61682	63682		65682	<u> </u>	10 70 (ORDC =	1000	68202	
	0.0082		61822	63822		65822				68203		
	0.0002	5.0 x 11.0 x 17.5	1.0	61103	63103		65103				68204	1100
	0.010			61123	63123	1000	65123	1000	-	-	68205	
300	0.012			61153	63153		65153				68206	
300	0.013	6.0 x 12.0 x 17.5	1.4	61183	63183		65183				68207	900
	0.016	DITCH	150.			0 (l .		. 10.0/ (11	1000 \		
	0.000	l		I		m ± 0.0		OL. =	± 10 % (U _{RDC} =	1000 1		000
	0.022	7.0 x 13.5 x 17.5	1.8	61223	63223	750	65223	500			68208	800
	0.027	8.5 x 15.0 x 17.5	2.4	61273	63273	750	65273	500			68209	650
	0.033			61333	63333		65333		-	-	68211	
	0.039	10.0 x 16.5 x 17.5	3	61393	63393	500	65393	450			68212	600
	0.047			61473	63473		65473	<u> </u>			68213	
	0.0000		1 = 15.0	ı		ım ± 0.		1 OL. =	± 5 % (U _{RDC} =	1000 V	1	1
	0.0068			68258	68284		68309				68381	
	0.0082	5.0 x 11.0 x 17.5	1.0	68259	68285		68311				68382	1100
	0.010			68261	68286	1000	68312	1000	-	-	68383	
	0.012	6.0 x 12.0 x 17.5	1.4	68262	68287		68313				68384	900
	0.015			68263	68288		68314				68385	
		PITCH	H = 15.0	mm ± 0.4 mn		m ± 0.	08 mm; C-	TOL. =	± 5 % (U _{RDC} =	1000 V		
	0.018	7.0 x 13.5 x 17.5	1.8	68264	68289		68315				68386	800
	0.022	7.0 X 10.0 X 17.0	1.0	68265	68291	750	68316	500			68387	550
	0.027	8.5 x 15.0 x 17.5	2.4	68266	68292	7.50	68317	300	-	-	68388	650
	0.033	0.0 x 10.0 x 17.5	۷.4	68267	68293		68318				68389	
1	0.039	10.0 x 16.5 x 17.5	3.0	68268	68294	500	68319	450		1	68391	600

- SPQ = Standard Packing Quantity
- (1) H = in-tape height; P₀ = sprocket hole distance; for detailed specifications refer to packaging information: www.vishay.com/doc?28139
- (2) Reel diameter = 365 mm is available on request
- (3) Weight for short lead product only



Vishay BCcomponents

ELE	CTRIC	CAL DATA AN	D ORD	ERING IN	IFORMAT	ION -	PITCH 2	22.5	mm				
				CATALOG NUMBER BFC2 338 6X XXX AND PACKAGING									
	040	DIMENSIONS		LOOSE IN BOX				AMMOPACK		REEL (1)(2)			
U _{RAC} (V)	CAP. (µF)	wxhxl	MASS (g) ⁽³⁾	SHC	RT LEADS	1	LONG LE	ADS	1		Ø = 500 mm ⁽¹⁾⁽²⁾		
, ,	(μ.)	(mm)	107	l _t = 3.5 mm ± 0.3 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ	
		PITCH	l = 22.5 r	nm ± 0.4 mm	ı; d _t = 0.80 m	m ± 0.0	08 mm; C-T	OL. =	± 20 % (U _{RDC} =	1000 V	/)		
	0.047	7.0 x 16.5 x 26.0	2.9	68123	68125	200	68127	250					
	0.056	7.0 X 16.5 X 26.0	2.9	68124	68126	200	68128	250					
	0.068	8.5 x 18.0 x 26.0	3.8	60683	62683	200	64683	250					
	0.082	6.5 X 16.0 X 26.0	3.0	60823	62823	200	64823		-	-	-	-	
	0.10	10.0 x 19.5 x 26.0	6.8	60104	62104	200	64104	200					
	0.12	12.0 x 22.0 x 26.0	7.8	60124	62124	150	64124	200					
	0.15	12.0 % 22.0 % 20.0	7.0	60154	62154	130	64154	200					
		PITCH	l = 22.5 r	mm ± 0.4 mm	n; d _t = 0.80 m	m ± 0.0	08 mm; C-T	OL. =	± 10 % (U _{RDC} =	1000 \	/)		
	0.047	7.0 x 16.5 x 26.0	2.9	68173	68175		68177						
	0.056	8.5 x 18.0 x 26.0	3.8	68174	68176		68178	250					
300	0.068	6.5 X 16.0 X 20.0	3.0	61683	63683	200	65683						
	0.082	10.0 x 19.5 x 26.0	6.8	61823	63823		65823	200	-	-	-	-	
	0.10	10.0 x 19.5 x 20.0	0.0	61104	63104		65104	200					
	0.12	12.0 x 22.0 x 26.0	7.8	61124	63124	150	65124	200					
	0.15	12.0 % 22.0 % 20.0	7.0	61154	63154	130	65154	200					
		PITCI	H = 22.5	mm ± 0.4 mr	n; d _t = 0.80 m	ım ± 0.	08 mm; C-1	ΓOL. =	± 5 % (U _{RDC} =	1000 V)		
	0.047	7.0 x 16.5 x 26.0	2.9	68269	68295		68321						
	0.056	8.5 x 18.0 x 26.0	3.8	68271	68296	200	68322		250				
	0.068	0.0 X 10.0 X 20.0	0.0	68272	68297	200	68323					_	
	0.082	10.0 x 19.5 x 26.0	6.8	68273	68298		68324						
	0.10	12.0 x 22.0 x 26.0	7.8	68274	68299	150	68325	200					
	0.12	12.0 % 22.0 % 20.0	7.0	68275	68301	130	68326						

[•] SPQ = Standard Packing Quantity

⁽¹⁾ H = in-tape height; P₀ = sprocket hole distance; for detailed specifications refer to packaging information: <u>www.vishay.com/doc?28139</u>

⁽²⁾ Reel diameter = 365 mm is available on request

⁽³⁾ Weight for short lead product only



Vishay BCcomponents

ELE	CTRI	CAL DATA AN	D ORE	ERING IN					mm 6X XXX AND PA	CKAG	ING	
					LOOSE			2 330			REEL	
URAC	CAP.	DIMENSIONS wxhxl	MASS	SHC	RT LEADS		LONG LE	ADS	AMMOPAC	K	Ø = 500 mm ⁽¹⁾⁽²⁾	
(V)	(μ F)	(mm)	(g) ⁽³⁾	I _t = 3.5 mm ± 0.3 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ	H = 18.5 mm; P ₀ = 12.7 mm	SPQ
		PITCH	= 27.5 ı	mm ± 0.4 mm	; d _t = 0.80 m	m ± 0.0	08 mm; C-T	OL. =	± 20 % (U _{RDC} =	1000 V	/)	
	0.18	13.0 x 23.0 x 31.0	9.2	60184	62184	100	64184	64184 125				
	0.22	13.0 X 23.0 X 31.0	9.2	60224	62224	100	64224	125				
	0.27	15.0 x 25.0 x 31.0	12.3	60274	62274	100	64274	125				
	0.33	18.0 x 28.0 x 31.0	16.1	60334	62334	100	64334	100	_	_	_	_
	0.39	16.0 x 26.0 x 31.0	10.1	60394	62394	100	64394	100				
	0.47	21.0 x 31.0 x 31.0	20.3	60474	62474	50	64474	75				
		PITCH	= 27.5 ı	mm ± 0.4 mm	ı; d _t = 0.80 m	m ± 0.0	08 mm; C-T	OL. =	± 10 % (U _{RDC} =	1000 \	/)	
	0.18	13.0 x 23.0 x 31.0	9.2	61184	63184		65184	125				-
	0.22	15.0 x 25.0 x 31.0	12.3	61224	63224	100	65224	123				
300	0.27	18.0 x 28.0 x 31.0	16.1	61274	63274	100	65274	100	_			
	0.33	10.0 % 20.0 % 01.0	10.1	61334	63334		65334	100				
	0.39	21.0 x 31.0 x 31.0	20.3	61394	63394	50	65394	75				
	0.47			61474	63474		65474					
		PITCH	l = 27.5	mm ± 0.4 mn	n; d _t = 0.80 m	m ± 0.	08 mm; C-1	ΓOL. =	± 5 % (U _{RDC} =	1000 V)	
	0.15	13.0 x 23.0 x 31.0	9.2	68276	68302		68327					
	0.18	10.0 % 20.0 % 01.0	0.2	68277	68303		68328 100 68329 68331	125				
	0.22	15.0 x 25.0 x 31.5	12.3	68278	68304	100			_	_	_	_
	0.27	18.0 x 28.0 x 31.5	16.1	68279	68305			100] -	-	-	-
	0.33	10.0 % 20.0 % 01.0	10.1	68281	68306		68332					
	0.39	21.0 x 31.0 x 31.0	20.3	68282	68307	50	68333	75				

Notes

- SPQ = Standard Packing Quantity
- (1) H = in-tape height; P₀ = sprocket hole distance; for detailed specifications refer to packaging information: www.vishay.com/doc?28139
- (2) Reel diameter = 365 mm is available on request
- (3) Weight for short lead product only

APPROVALS								
SAFETY APPROVALS Y2	VOLTAGE	VALUE	FILE NUMBERS	LINK				
EN 60384-14 (ENEC) (= IEC 60384-14 ed-4 (2013))	300 V _{AC}	1 nF to 470 nF	ENEC16/FI/21/01048	www.vishay.com/doc?28212				
UL 60384-14 2 nd edition	300 V _{AC}	1 nF to 470 nF	E354331	www.vishav.com/doc?28189				
CSA E60384-1:14 3 rd edition	300 V _{AC}	1 nF to 470 nF	E354331	www.visnay.com/doc?28189				
CB-test certificate	300 V _{AC}	1 nF to 470 nF	FI-39810/A1	www.vishay.com/doc?28213				

The ENEC-approval together with the CB-certificate replace all national marks of the following countries (they have already signed the ENEC-agreement): Austria; Belgium; Czech. Republic; Denmark; Finland; France; Germany; Greece; Hungary; Ireland; Italy; Luxembourg; Netherlands; Norway; Portugal; Slovenian; Spain; Switzerland and United Kingdom.







MOUNTING

Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoleers are designed for mounting in printed circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to packaging information: www.vishay.com/doc?28139

Specific Method of Mounting to Withstand Vibration and Shock

In order to withstand vibration and shock tests, it must be ensured that the stand-off pips are in good contact with the printed-circuit board:


- For pitches ≤ 15 mm capacitors shall be mechanically fixed by the leads
- For larger pitches the capacitors shall be mounted in the same way and the body clamped

Space Requirements on Printed-Circuit Board

The maximum space for length ($I_{max.}$), width ($w_{max.}$), and height ($h_{max.}$) of film capacitors to take in account on the printed-circuit board is shown in the drawings:

- For products with pitch ≤ 15 mm, $\Delta w = \Delta l = 0.3$ mm; $\Delta h = 0.1$ mm
- For products with 15 mm < pitch, \leq 27.5 mm, $\Delta w = \Delta I = 0.5$ mm; $\Delta h = 0.1$ mm

Eccentricity defined as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.



SOLDERING CONDITIONS

For general soldering conditions and wave soldering profile, we refer to the application note:

"Soldering Guidelines for Film Capacitors": www.vishay.com/doc?28171

Storage Temperature


 T_{stg} = -25 °C to +35 °C with RH maximum 75 % without condensation

Ratings and Characteristics Reference Conditions


Unless otherwise specified, all electrical values apply to an ambient temperature of 23 °C \pm 1 °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of 50 % \pm 2 %.

For reference testing, a conditioning period shall be applied over 96 h \pm 4 h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.


CHARACTERISTICS




Capacitance as a function of ambient temperature (typical curve)




Impedance as a function of frequency (typical curve)




Max. RMS voltage as a function of frequency




Tangent of loss angle as a function of frequency (typical curve)



Resonant frequency as a function of capacitance (typical curve)



Max. RMS current as a function of frequency



Insulation resistance as a function of ambient temperature

APPLICATION NOTES

- For Y2 electromagnetic interference suppression in standard line bypass applications (between line and ground) (50 Hz / 60 Hz) with a maximum mains voltage of 300 V_{AC}.
- For series impedance applications we refer to the application note: www.vishay.com/doc?28153
- For capacitors connected in parallel, normally the proof voltage and possibly the rated voltage must be reduced. For information depending of the capacitance value and the number of parallel connections contact rfi@vishay.com
- These capacitors are not intended for continuous pulse applications. For these situations, capacitors of the AC and pulse program must be used.
- The maximum ambient temperature must not exceed 105 °C.
- Rated voltage pulse slope:
 if the pulse voltage is lower than the rated voltage, the values of the specific reference data can be multiplied by 420 V_{DC} and divided by the applied voltage.

INSPECTION REQUIREMENTS

General Notes

Sub-clause numbers of tests and performance requirements refer to the "Sectional Specification, Publication IEC 60384-14 ed-4 (2013) and Specific Reference Data."

GROUP C INSPECTION REQUIR	GROUP C INSPECTION REQUIREMENTS							
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS						
SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1								
4.1 Dimensions (detail)		As specified in chapters "General Data" of this specification						
Initial measurements	Capacitance Tangent of loss angle: at 10 kHz							
4.3 Robustness of terminations	Tensile: load 10 N; 10 s Bending: load 5 N; 4 x 90°	No visible damage						
4.4 Resistance to soldering heat	No pre-drying Method: 1A Solder bath: 280 °C ± 5 °C Duration: 10 s							



GROUP C INSPECTION REQUIR	ı	
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1		
4.19 Component solvent resistance	Isopropylalcohol at room temperature Method: 2 Immersion time: 5 min ± 0.5 min Recovery time: min. 1 h, max. 2 h	
4.4.2 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \le 5$ % of the value measured initially
	Tangent of loss angle	Increase of tan $\delta \leq 0.008$ Compared to values measured initially
	Insulation resistance	As specified in section "Insulation Resistance" of this specification
SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1		
Initial measurements	Capacitance Tangent of loss angle: at 10 kHz	
4.20 Solvent resistance of the marking:	Isopropylalcohol at room temperature Method: 1 Rubbing material: cotton wool Immersion time: 5 min ± 0.5 min	No visible damage Legible marking
4.6 Rapid change of temperature	$\theta A = -55 ^{\circ}C$ $\theta B = +105 ^{\circ}C$ 5 cycles Duration t = 30 min	
4.6.1 Inspection	Visual examination	No visible damage
4.7 Vibration	Mounting: see section "Mounting" of this specification Procedure B4: Frequency range: 10 Hz to 55 Hz Amplitude: 0.75 mm or Acceleration 98 m/s² (whichever is less severe) Total duration 6 h	
4.7.2 Final inspection	Visual examination	No visible damage
4.9 Shock	Mounting: see section "Mounting" for more information Pulse shape: half sine Acceleration: 490 m/s² Duration of pulse: 11 ms	
4.9.2 Final measurements	Visual examination	No visible damage
	Capacitance	$ \Delta C/C \le 5$ % of the value measured initially
	Tangent of loss angle	Increase of tan $\delta \le 0.008$ Compared to values measured initially
	Insulation resistance	As specified in section "Insulation Resistance" of this specification



GROUP C INSPECTION REQUIR	REMENTS	
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B		
4.11 Climatic sequence		
4.11.1 Initial measurements	Capacitance measured in 4.4.2 and 4.9.2 Tangent of loss angle: measured initially in C1A and C1B	
4.11.2 Dry heat	Temperature: 105 °C Duration: 16 h	
4.11.3 Damp heat cyclic Test Db First cycle		
4.11.4 Cold	Temperature: -55 °C Duration: 2 h	
4.11.5 Damp heat cyclic Test Db remaining cycles		
4.11.6 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \le 5$ % of the value measured in 4.11.1.
	Tangent of loss angle	Increase of tan $\delta \le 0.008$ Compared to values measured in 4.11.1
	Voltage proof 2250 V _{DC} ; 1 min between terminations	No permanent breakdown or flash-over
	Insulation resistance	≥ 50 % of values specified in section "Insulation Resistance" of this specification
SUB-GROUP C2		
4.12 Damp heat steady state	56 days, 40 °C, 90 % to 95 % RH, no load Capacitance	
4.12.1 Initial measurements	Tangent of loss angle at 1 kHz	
4.12.3 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \le 5$ % of the value measured in 4.12.1.
	Tangent of loss angle	Increase of tan $\delta \le 0.007$ Compared to values measured in 4.12.1.
	Voltage proof 2250 V _{DC} ; 1 min between terminations	No permanent breakdown or flash-over
	Insulation resistance	≥ 50 % of values specified in section "Insulation Resistance" of this specification



GROUP C INSPECTION REQUIREMENTS SUB-CLAUSE NUMBER AND TEST CONDITIONS PERFORMANCE REQUIREMENTS		
SUB-GROUP C3	CONDITIONS	PERFORMANCE REQUIREMENTS
4.13.1 Initial measurements	Compaignment	
4.13.1 Initial measurements	Capacitance Tangent of loss angle: at 10 kHz	
4.13 Impulse voltage	3 successive impulses, full wave, peak voltage: X1: 5 kV Max. 24 pulses	No selfhealing breakdowns or flash-over
4.14 Endurance	Duration: 1000 h 1.7 x U_{RAC} at 105 °C Once in every hour the voltage is increased to 1000 V_{RMS} for 0.1 s via resistor of 47 Ω ± 5 %	
4.14.7 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	ΔC/C ≤10 % compared to values measured in 4.13.1.
	Tangent of loss angle	Increase of tan $\delta \le 0.008$ Compared to values measured in 4.13.1.
	Voltage proof 2250 V_{DC} ; 1 min between terminations 2100 V_{AC} ; 1 min between terminations and case	No permanent breakdown or flash-over
	Insulation resistance	≥ 50 % of values specified in section "Insulation Resistance" of this specification
SUB-GROUP C4		
4.15 Charge and discharge	10 000 cycles charged to 420 V_{DC} Discharge resistance: $R = \frac{420 \ V_{DC}}{1.5 \ x \ C \ (dU/dt)}$	
4.15.1 Initial measurements	Capacitance Tangent of loss angle: at 10 kHz	
4.15.3 Final measurements	Capacitance	∆C/C ≤10 % compared to values measured in 4.15.1.
	Tangent of loss angle	Increase of $\tan \delta \le 0.008$ Compared to values measured in 4.15.1.
	Insulation resistance	≥ 50 % of values specified in section "Insulation Resistance" of this specification
SUB-GROUP C5		
4.16 Radio frequency characteristic	Resonance frequency	≥ 0.9 times the value as specified in section "Resonant Frequency" of this specification



GROUP C INSPECTION REQUIREMENTS			
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS	
SUB-GROUP C6			
4.17 Passive flammability Class B	Bore of gas jet: Ø 0.5 mm Fuel: Butane Test duration for actual volume V in mm ³ : $V \le 250$: 10 s $250 < V \le 500$: 20 s $500 < V \le 1750$: 30 s V > 1750: 60 s One flame application	After removing test flame from capacitor, the capacitor must not continue to burn for more than 10 s. No burning particle must drop from the sample.	
	45.0°		
SUB-GROUP C7			
4.18 Active flammability	20 cycles of 5 kV discharges on the test capacitor connected to U _{RAC} .	The cheese cloth around the capacitors shall not burn with a flame. No electrical measurements are required.	
SUB-GROUP ADDITIONAL TEST (FOR PITCH ≥ 15 mm)			
Damp heat steady state with voltage	RH: 85 %, temperature: 85 °C; Voltage: 300 V _{AC} , duration: 500 h		
Initial measurements	Capacitance Tangent of loss angle: at 10 kHz		
Final measurements	Visual examination	No visible damage Legible marking	
	Capacitance	$ \Delta C/C $ ≤ 10 % of the value with initial measurement	
	Tangent of loss angle	Increase of tan $\delta \leq 0.024$ Compared to values with initial measurement	
	Insulation resistance	≥ 50 % of values specified in section "Insulation Resistance" of this specification	

Legal Disclaimer Notice



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.