

# Product data sheet

Specifications

## Easy UPS On-Line SRVS 3000VA RM 230V with Rail Kit



SRVS3KRIRK

### Overview

Presentation	For small to medium businesses, Easy UPS 1 Ph On-Line provides essential power protection for unstable power conditions, ensuring consistent and reliable connectivity at the most critical moments.
Lead time	Usually in Stock

### Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	2400 W
Rated power in VA	3000 VA
Plug standard	IEC 60320 C14
Nb of power socket outlets	6 IEC 60320 C13 1 IEC 60320 C19
Number of rack unit	2U
Cable length	1.48 m
Number of cables	1
Provided equipment	Basic UPS signalling RS-232 cable CD with software Rack mounting brackets User manual USB cable

### General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

### Physical

Colour	Black
Height	8.6 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	43.8 cm
Depth	63.2 cm
Net weight	27.0 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
USB compatible	Yes
Mounting position	Horizontal

### Input

Input voltage limits	110...285 V half load 160...280 V full load
Network frequency	40...70 Hz auto sensing

### Output

Maximum configurable power in VA	3000 VA
Maximum configurable power in W	2400 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Double conversion online
Wave type	Sine wave
Efficiency	88 % (full load)
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1

### Conformance

Product certifications	CE
Standards	EN/IEC 62040-1 EN/IEC 62040-2

### Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...15000 m
Acoustic level	50 dBA
IP degree of protection	IP20

### Batteries & Runtime

Battery type	Lead-acid battery
Battery voltage	72 V
Number of battery filled slots	0

Number of battery free slots	0
Battery recharge time	4 h
Battery life	3...5 year(s)
Battery charger power	118 W rated

### Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control panel	Multifunction LCD status and control console
Free slots	1

### Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	29 kg
Package 1 Height	22.9 cm
Package 1 width	56.9 cm
Package 1 Length	79.5 cm
Unit Type of Package 2	P06
Number of Units in Package 2	1
Package 2 Weight	35 kg
Package 2 Height	68 cm
Package 2 width	60 cm
Package 2 Length	80 cm

### Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------