

KERN EOE 150K50L



Parcel scales with big platform for fast and easy weighing in the office, production, dispatch etc.



Measuring system

Adjustment options:	External calibration
Linearity:	100 g
Readability [d]:	50 g
Recommended adjusting weight:	100 kg (M3)
Repeatability:	50 g
Resolution:	3000
Tare range:	150 kg
Warm up time:	10 min
Weighing capacity [Max]:	150 kg
Weighing system:	Strain gauge
Weighing units:	kg lb

Display

Display digit height:	2,500 cm
-----------------------	----------

Functions

Data hold function:	yes
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	4x1.5 V AA
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter/adaptor included:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time:	100 h
-----------------	-------

Service

Adjustment at the location of installation:	961-249
---	---------

DAkkS Certificate:	963-129
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Platform scale

Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	660 x 600 x 90 mm
Gross weight:	15,300 kg
Net weight:	13,800 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	2,700 m
Casing material:	plastic
Dimensions of display device (WxDxH):	235 x 115 x 51 mm
Dimensions of weighing plate (WxDxH):	550 x 550 x 57 mm
Material weighing plate:	Steel lacquered
Wall mount:	yes
Weighing surface (WxD):	550 x 550 mm

Piktogramme

STANDARD



OPTION

