


BYW52, BYW53, BYW54, BYW55, BYW56

Vishay Semiconductors

Standard Avalanche Sinterglass Diode



MECHANICAL DATA

Case: SOD-57

Terminals: plated axial leads, solderable per MIL-STD-750, method 2026

Polarity: color band denotes cathode end

Mounting position: any

Weight: approx. 369 mg

FEATURES

- Controlled avalanche characteristics
- Glass passivated junction
- Hermetically sealed package
- Low reverse current
- High surge current loading
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

• Rectification, general purpose

ORDERING INFORMATION (Example)					
DEVICE NAME	ORDERING CODE	TAPED UNITS	MINIMUM ORDER QUANTITY		
BYW56	BYW56-TR	5000 per 10" tape and reel	25 000		
BYW56	BYW56-TAP	5000 per ammopack	25 000		

PARTS TABLE				
PART	TYPE DIFFERENTIATION	PACKAGE		
BYW52	V _R = 200 V; I _{F(AV)} = 2 A	SOD-57		
BYW53	V _R = 400 V; I _{F(AV)} = 2 A	SOD-57		
BYW54	V _R = 600 V; I _{F(AV)} = 2 A	SOD-57		
BYW55	$V_{R} = 800 \text{ V}; \text{ I}_{F(AV)} = 2 \text{ A}$	SOD-57		
BYW56	V _R = 1000 V; I _{F(AV)} = 2 A	SOD-57		

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	PART	SYMBOL	VALUE	UNIT	
	See electrical characteristics	BYW52	$V_{R} = V_{RRM}$	200	V	
_		BYW53	$V_{R} = V_{RRM}$	400	V	
Reverse voltage = repetitive peak reverse voltage		BYW54	$V_{R} = V_{RRM}$	600	V	
voluge		BYW55	$V_{R} = V_{RRM}$	800	V	
		BYW56	$V_{R} = V_{RRM}$	1000	V	
Peak forward surge current	t _p = 10 ms, half sine wave		I _{FSM}	50	А	
Repetitive peak forward current			I _{FRM}	12	А	
Average forward current	φ = 180 °		I _{F(AV)}	2	А	
Pulse avalanche peak power	t_p = 20 µs half sine wave, T_j = 175 °C		PR	1000	W	
Pulse energy in avalanche mode, non repetitive (inductive load switch off)	l _{(BR)R} = 1 Α, Τ _j = 175 °C		E _R	20	mJ	
i ² t-rating			i²t	8	A ² s	
Junction and storage temperature range			$T_j = T_{stg}$	-55 to +175	°C	

Rev. 1.9, 04-Nov-15

1





Vishay Semiconductors

MAXIMUM THERMAL RESISTANCE (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Junction ambient	Lead length I = 10 mm, T_L = constant	R _{thJA}	45	K/W	
	On PC board with spacing 25 mm	R _{thJA}	100	K/W	

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	I _F = 1 A	V _F	-	0.9	1	V
Reverse current	$V_{\rm R} = V_{\rm RRM}$	I _R	-	0.1	1	μA
neverse current	$V_R = V_{RRM}, T_j = 100 \ ^\circ C$	I _R	-	5	10	μA
Breakdown voltage	$I_{\rm R}$ = 100 µA, $t_{\rm p}/T$ = 0.01, $t_{\rm p}$ = 0.3 ms	V _(BR)	-	-	1600	V
Diode capacitance	$V_R = 4 V, f = 1 MHz$	CD	-	18	-	pF
	$I_F = 0.5 \text{ A}, I_R = 1 \text{ A}, i_R = 0.25 \text{ A}$	t _{rr}	-	-	4000	ns
Reverse recovery time	$I_F = 1 \text{ A}, \text{ dI/dt} = 5 \text{ A/}\mu\text{s}, \text{V}_R = 50 \text{ V}$	t _{rr}	-	-	4000	ns
Reverse recovery charge	$I_F = 1 \text{ A}, \text{ dI/dt} = 5 \text{ A/}\mu\text{s}$	Q _{rr}	-	-	200	nC

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Typ. Thermal Resistance vs. Lead Length




Fig. 2 - Forward Current vs. Forward Voltage




Fig. 3 - Max. Average Forward Current vs. Ambient Temperature





Fig. 4 - Reverse Current vs. Junction Temperature

Rev. 1.9, 04-Nov-15

2

Document Number: 86049

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



= 25 °C

10

I_{FRM} - Repetitive Peak

Forward Current (A)

= 60 °C


70 °C

T_{amb} = 100 °C

1

45 °C

100



10⁻³

10⁻²

10⁻¹

tp - Pulse Length (s)

/T = 0.1

t_/T = 0.05

t_o/T = 0.02


 $t_{p}/T = 0.01$

10⁻⁴

10

10⁻⁵

94 9178



10⁰

Fig. 7 - Thermal Response

10¹

20543 Rev. 3 - Date: 09.February 2005 Document no.:6.563-5006.3-4

Rev. 1.9, 04-Nov-15 Document Number: 86049 3 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.