

SEMITRANS<sup>®</sup> 3

### Trench IGBT Modules

#### SKM 400GB066D

### Features

- Trench = Trenchgate technology
- V<sub>CE(sat)</sub> with positive temperature coefficient
- High short circuit capability, self limiting to 6 x I<sub>C</sub>

#### **Typical Applications\***

- AC inverter drives
- UPS
- Electronic welders

### Remarks

- Case temperature limited to  $T_c = 125^{\circ}C$  max, recommended  $T_{op} = -40 \dots +150^{\circ}C$
- Product reliability results are valid for T<sub>i</sub> ≤150°C
- Short circuit data:  $t_p \le 6\mu$ s;  $V_{GE} \le 15V$ ;  $T_j = 150^{\circ}$ C;  $V_{cc} \le 360V$ , use of soft  $R_G$  necessary !
- Take care of over-voltage caused by stray inductances

Absolute Maximum Ratings T <sub>case</sub> = 25°C, unless otherwise specified				
Symbol	-		Values	Units
IGBT				•
V <sub>CES</sub>	T <sub>j</sub> = 25 °C		600	V
I <sub>C</sub>	T <sub>j</sub> = 175 °C	T <sub>c</sub> = 25 °C	500	А
		T <sub>c</sub> = 80 °C	380	А
I <sub>CRM</sub>	I <sub>CRM</sub> =2xI <sub>Cnom</sub>		800	А
V <sub>GES</sub>			± 20	V
t <sub>psc</sub>	$V_{CC}$ = 360 V; $V_{GE} \le$ 15 V; VCES < 600 V	T <sub>j</sub> = 150 °C	6	μs
Inverse	Diode			•
I <sub>F</sub>	T <sub>j</sub> = 175 °C	T <sub>c</sub> = 25 °C	450	А
		T <sub>c</sub> = 80 °C	320	А
I <sub>FRM</sub>	I <sub>FRM</sub> =2xI <sub>Fnom</sub>		800	А
Module				
I <sub>t(RMS)</sub>			500	А
T <sub>vj</sub>			- 40 +175	°C
T <sub>stg</sub>			- 40 +125	°C
V <sub>isol</sub>	AC, 1 min.		4000	V

Characteristics T <sub>case</sub> =			25°C, unless otherwise specified			
Symbol	Conditions		min.	typ.	max.	Units
IGBT			_			
V <sub>GE(th)</sub>	$V_{GE} = V_{CE}$ , $I_C = 6,4$ mA		5	5,8	6,5	V
I <sub>CES</sub>	$V_{GE}$ = 0 V, $V_{CE}$ = $V_{CES}$	T <sub>j</sub> = 25 °C		0,25	0,75	mA
V <sub>CE0</sub>		T <sub>j</sub> = 25 °C		0,9	1	V
		T <sub>j</sub> = 150 °C		0,85	0,9	V
r <sub>CE</sub>	V <sub>GE</sub> = 15 V	T <sub>j</sub> = 25°C		1,4	2,3	mΩ
		T <sub>j</sub> = 150°C		2,1	3	mΩ
V <sub>CE(sat)</sub>	I <sub>Cnom</sub> = 400 A, V <sub>GE</sub> = 15 V	T <sub>j</sub> = 25°C <sub>chiplev.</sub>		1,45	1,9	V
		$T_j = 150^{\circ}C_{chiplev.}$		1,7	2,1	V
C <sub>ies</sub>				24,7		nF
C <sub>oes</sub>	$V_{CE}$ = 25, $V_{GE}$ = 0 V	f = 1 MHz		1,54		nF
C <sub>res</sub>				0,73		nF
$Q_{G}$	V <sub>GE</sub> = -8V+15V			3000		nC
R <sub>Gint</sub>	$T_j = °C$			2		Ω
t <sub>d(on)</sub>				200		ns
t,	R <sub>Gon</sub> = 1,5 Ω	V <sub>CC</sub> = 300V		60		ns
E <sub>on</sub>		I <sub>C</sub> = 400A		8		mJ
t <sub>d(off)</sub>	$R_{Goff}$ = 1,5 $\Omega$	T <sub>j</sub> = 150 °C V <sub>GE</sub> = -8V/+15V		560 53		ns
t <sub>f</sub> E <sub>off</sub>		•GE0 0/+ 150		55 16		ns mJ
				10		-
R <sub>th(j-c)</sub>	per IGBT				0,12	K/W





SEMITRANS<sup>®</sup> 3

### Trench IGBT Modules

#### SKM 400GB066D

Characte	ristics					
Symbol	Conditions		min.	typ.	max.	Units
Inverse D	Diode					
$V_F = V_{EC}$	$I_{Fnom}$ = 400 A; $V_{GE}$ = 0 V	$T_j = 25 \ ^{\circ}C_{chiplev.}$		1,4	1,6	V
V <sub>F0</sub>		T <sub>j</sub> = 25 °C		0,95	1	V
r <sub>F</sub>		T <sub>j</sub> = 25 °C		1,1	1,5	mΩ
I <sub>RRM</sub> Q <sub>rr</sub>	I <sub>F</sub> = 400 A di/dt = 7250 A/μs	T <sub>j</sub> = 150 °C		410 62		A µC
Err	$V_{GE}$ = -8 V; $V_{CC}$ = 300 V			14		mJ
R <sub>th(j-c)D</sub>	per diode				0,2	K/W
Module						
L <sub>CE</sub>				15	20	nH
R <sub>CC'+EE'</sub>	res., terminal-chip	T <sub>case</sub> = 25 °C		0,35		mΩ
		T <sub>case</sub> = 125 °C		0,5		mΩ
R <sub>th(c-s)</sub>	per module				0,038	K/W
M <sub>s</sub>	to heat sink M6		3		5	Nm
M <sub>t</sub>	to terminals M6		2,5		5	Nm
w					325	g

#### Features

- Trench = Trenchgate technology
- V<sub>CE(sat)</sub> with positive temperature coefficient
- High short circuit capability, self limiting to 6 x I<sub>C</sub>

#### **Typical Applications\***


- AC inverter drives
- UPS
- Electronic welders

### Remarks

- Case temperature limited to  $T_c = 125^{\circ}C$  max, recommended  $T_{op} = -40 \dots + 150^{\circ}C$
- Product reliability results are valid for  $T_i \leq \! 150^\circ C$
- Short circuit data:  $t_p \le 6\mu$ s;  $V_{GE} \le 15V$ ;  $T_j$  = 150°C;  $V_{cc} \le 360V$ , use of soft  $R_G$  necessary !
- Take care of over-voltage caused by stray inductances

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

\* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.





Trench	IGBT	Modules
--------	------	---------

Z <sub>th</sub> Symbol	Conditions	Values	Units
$Z_{th(i, \alpha)}$			
Z <sub>th(j-c)l</sub> R₁	i = 1	80	mk/W
R <sub>i</sub>	i = 2	22,5	mk/W
R <sub>i</sub>	i = 3	6,4	mk/W
R <sub>i</sub>	i = 4	1,1	mk/W
tau <sub>i</sub>	i = 1	0,0447	s
tau <sub>i</sub>	i = 2	0,0223	s
tau <sub>i</sub>	i = 3	0,0015	s
tau <sub>i</sub>	i = 4	0,0002	s
Z Ri <b>th(j-c)D</b>			ŀ
R <sub>i</sub>	i = 1	130	mk/W
R <sub>i</sub>	i = 2	55	mk/W
R <sub>i</sub>	i = 3	12,5	mk/W
R <sub>i</sub>	i = 4	2,5	mk/W
tau <sub>i</sub>	i = 1	0,054	s
tau	i = 2	0,01	s
tau <sub>i</sub>	i = 3	0,0015	S
tau <sub>i</sub>	i = 4	0,1	s

### Features

**SKM 400GB066D** 


- Trench = Trenchgate technology
- V<sub>CE(sat)</sub> with positive temperature coefficient
- High short circuit capability, self limiting to 6 x I<sub>C</sub>


#### **Typical Applications\***


- AC inverter drives
- UPS
- Electronic welders


### Remarks


- Case temperature limited to  $T_c = 125^{\circ}C$  max, recommended  $T_{op} = -40 \dots +150^{\circ}C$
- Product reliability results are valid for  $T_i \leq 150^{\circ}C$
- Short circuit data:  $t_p \le 6\mu$ s;  $V_{GE} \le 15V$ ;  $T_j = 150^{\circ}$ C;  $V_{cc} \le 360V$ , use of soft  $R_G$  necessary !
- Take care of over-voltage caused by stray inductances







































UL recognized, file no. E 63 532

