

1

2

3

4

5

6

7

A

A

B

B

C

C

D

D

E

E

F

F

G

G

H

H

NOTES:

MATERIAL

- 1. Insulator Material: PBT+30%GF(UL94V-0), Black
- 2. Contact Material : Phosphor Bronze
- 3. Contact Plating : Gold flash/ Tin Over Ni







ELECTRICAL

- 1. Current Rating : 1AMP
- 2. Withstand Voltage : 500V AC/DC
- 3. Contact Resistance : 20mΩ max
- 4. Insulation Resistance: 1000MΩ min

ENVIRONMENTAL

- 1. Operation Temperature: -40°C to +105°C
- 2. Packing: Tray

No. of contacts: 06, 08, 10, 12, 14, 16, 18, 20, 22, 24, 26, 30, 34, 36, 40, 44, 50, 60, 64, 68



RoHS compliant

Scale	1:1					Date	Name	Customer-No.	
TOLERANCE					Drawn	25.01.2006	Alex	ASSMANN WSW-No. AWP2 xx-7240 ^②	
X.X	±0.40	④	Added 68 Pin	24.12.2009	Dean	Approved	24.12.2009		Hellwig
X.XX	±0.25	③	Correct P/N	28.10.2009	Dean				
X.XXX	±0.15	②	Update	29.06.2009	Dean				
Angle	±3°	①	Drawn	25.01.2006	Alex			Drawing-No.	
		Id.	Modification	Date	Name	Replace		Sheet 1/2	

1

2

3

4

5

6

7

1

2

3

4


5

6




7

A

A



Insulator Material:PBT+30%GF(UL94V-0). Black
No. of contacts: 06, 08,10,12,14,16,18,20,22,24,26
30,34,36,40,44,50,60,64 ,68



B

B

C

C

D

D

E

E

F

F

RoHS compliant

Scale	1:1					Date	Name	Customer-No.
TOLERANCE					Drawn	25.01.2006	Alex	
X.X	±0.10	④	Added 68 Pin	24.12.2009	Dean	Approved	24.12.2009	HELLWIG
X.XX	±0.05	③	Correct P/N	28.10.2009	Dean			ASSMANN WSW-No. AWZ2-xx
X.XXX	±0.02	②	Update	29.06.2009	Dean			Drawing-No. ASS 2309 CO
Angle	±2°	①	Drawn	25.01.2006	Alex			rev04
		Id.	Modification	Date	Name			Sheet 2 / 2
								Replace

G

H

H

1

2

3

4

5

6

7

SV1751