

## Stainless Steel-Retaining cables

with 2 mounting tabs

### SPECIFICATION

#### Types

- Type **A**: with 2 key rings
- Type **B**: with tab and key ring
- Type **C**: with 2 tabs
- Type **D**: without tab and without key ring

Retaining cable  
Stainless Steel A2  
coated with clear plastic (PVC)

Tab  
Stainless Steel AISI 304

Key ring  
Stainless Steel AISI 301

Suitable for ball lock pins and locking pins with axial lock  
(see pages 870):

\* GN 113.1, GN 113.3, GN 113.4, GN 113.7, GN 113.8, GN 214.2, GN 214.3, GN 214.6 for pins  $\varnothing 5$ ,  $\varnothing 6$ ,  $\varnothing 8$

and

\* GN 113.5, GN 113.6, GN 114.2, GN 114.3, GN 114.6, GN 124.1, GN 124.2 for all pins

\*\* GN 113.1, GN 113.3, GN 113.4, GN 113.7, GN 113.8, GN 214.2, GN 214.3, GN 214.6 for pins  $\varnothing 10$ ,  $\varnothing 12$ ,  $\varnothing 16$ ,  $\varnothing 20$

### INFORMATION

The key rings are supplied fixed to the retaining cable. In Type A, both rings have the same diameter  $d_1$ .

The details on static loads are guide values given without warranty.





Type A and B are suitable for ball lock pins and pins with axial lock:

### TECHNICAL INFORMATION


- Stainless Steel characteristics (see page A26)

### ACCESSORY

- Single key rings are supplied with code no. GN 111.3-d1  
(see page 903)




#### Application example



Locking pins  
Ball lock pins

**GN 111.2**

**STAINLESS STEEL**

Description	l	d1	d2	Static load in N ≈ with key ring	Static load in N ≈ without key ring	Static load in N ≈	
GN 111.2-150-14-A	150	14 *	1	50	1800	-	5
GN 111.2-150-18-A	150	18 **	1.3	90	1800	-	7
GN 111.2-150-24-A	150	24	1.5	100	1800	-	8
GN 111.2-150-30-A	150	30	1.8	120	1800	-	12
GN 111.2-200-14-A	200	14 *	1	50	1800	-	6
GN 111.2-200-18-A	200	18 **	1.3	90	1800	-	8
GN 111.2-200-24-A	200	24	1.5	100	1800	-	9
GN 111.2-200-30-A	200	30	1.8	120	1800	-	13
GN 111.2-320-14-A	320	14 *	1	50	1800	-	9
GN 111.2-320-18-A	320	18 **	1.3	90	1800	-	10
GN 111.2-320-24-A	320	24	1.5	100	1800	-	11
GN 111.2-320-30-A	320	30	1.8	120	1800	-	15
GN 111.2-500-14-A	500	14 *	1	50	1800	-	12
GN 111.2-500-18-A	500	18 **	1.3	90	1800	-	14
GN 111.2-500-24-A	500	24	1.5	100	1800	-	15
GN 111.2-500-30-A	500	30	1.8	120	1800	-	20
GN 111.2-150-14-B	150	14 *	1	50	1800	-	7
GN 111.2-150-18-B	150	18 **	1.3	90	1800	-	7
GN 111.2-150-24-B	150	24	1.5	100	1800	-	7
GN 111.2-150-30-B	150	30	1.8	120	1800	-	10
GN 111.2-200-14-B	200	14 *	1	50	1800	-	7
GN 111.2-200-18-B	200	18 **	1.3	90	1800	-	8
GN 111.2-200-24-B	200	24	1.5	100	1800	-	11
GN 111.2-200-30-B	200	30	1.8	120	1800	-	15
GN 111.2-320-14-B	320	14 *	1	50	1800	-	10
GN 111.2-320-18-B	320	18 **	1.3	90	1800	-	11
GN 111.2-320-24-B	320	24	1.5	100	1800	-	12
GN 111.2-320-30-B	320	30	1.8	120	1800	-	16
GN 111.2-500-14-B	500	14 *	1	50	1800	-	13
GN 111.2-500-18-B	500	18 **	1.3	90	1800	-	15
GN 111.2-500-24-B	500	24	1.5	100	1800	-	18
GN 111.2-500-30-B	500	30	1.8	120	1800	-	21
GN 111.2-150-C	150	-	-	-	-	1800	10
GN 111.2-200-C	200	-	-	-	-	1800	10
GN 111.2-320-C	320	-	-	-	-	1800	12
GN 111.2-500-C	500	-	-	-	-	1800	12
GN 111.2-150-D	150	-	-	-	-	1800	4
GN 111.2-200-D	200	-	-	-	-	1800	5
GN 111.2-320-D	320	-	-	-	-	1800	7
GN 111.2-500-D	500	-	-	-	-	1800	10



**18**

Indexing elements