

**A-series, W-Series
ZQV 1.5N/20**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

| | |
|------------|----------------------------|
| Type | ZQV 1.5N/20 |
| Order No. | 1985600000 |
| GTIN (EAN) | 4050118370225 |
| Qty. | 20 pc(s). |

Data sheet

A-series, W-Series ZQV 1.5N/20

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Width | 70 mm | Width (inches) | 2.756 inch |
| Height | 21.9 mm | Height (inches) | 0.862 inch |
| Depth | 2.8 mm | Depth (inches) | 0.11 inch |
| Net weight | 6.52 g | | |

Temperatures

| | | | |
|---------------------------|---------------|---------------------------|-------|
| Storage temperature, max. | 40 °C | Storage temperature, min. | 10 °C |
| Storage temperature | 10 °C...40 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Material | Wemid | Colour | orange |
| UL 94 flammability rating | V-0 | | |

Additional technical data

| | | | |
|--------------------------|-----|----------------|---------|
| Explosion-tested version | Yes | Type of fixing | Plugged |
|--------------------------|-----|----------------|---------|

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 3.5 mm |
|-----------------|--------|

Rating data

| | |
|---------------|--------|
| Rated current | 17.5 A |
|---------------|--------|

Classifications

| | | | |
|-------------|-------------|------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| eClass 9.0 | 27-14-11-40 | eClass 9.1 | 27-14-11-40 |
| eClass 10.0 | 27-14-11-40 | | |

Product information

| | |
|---------------------|---|
| Product information | Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used |
|---------------------|---|

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | STEP |
| User Documentation | 2434520000_BED-ANL.ZQV_A_REIHE.pdf StorageConditionsTerminalBlocks |

Creation date March 10, 2020 9:57:11 AM CET