## CHIP COIL (CHIP INDUCTORS) LQM18PN□□□□FRL Reference Specification

#### 1. Scope

This reference specification applies to LQM18PN\_FR series, Chip Coil (Chip Inductors).

#### 2. Part Numbering

\*B: Bulk packing also available

#### 3. Rating

Operating Temperature Range
 Storage Temperature Range
 40°C to +85°C
 55°C to +125°C

| Customer    | MURATA<br>Part Number | Inductance |           | DC                | Self<br>Resonant        | Rated           |
|-------------|-----------------------|------------|-----------|-------------------|-------------------------|-----------------|
| Part Number |                       | (μH)       | Tolerance | Resistance<br>(Ω) | Frequency<br>(MHz min.) | Current<br>(mA) |
|             | LQM18PNR22NFRL        | 0.22       | . 200/    | 0.11±25%          |                         | 1250            |
|             | LQM18PNR47NFRL        | 0.47       | ±30%      | 0.15±25%          | 400                     | 1100            |
|             | LQM18PN1R0MFRL        | 1.0        |           | 0.20±25%          | 100                     | 950             |
|             | LQM18PN1R5MFRL        | 1.5        |           | 0.23±25%          |                         | 800             |
|             | LQM18PN2R2MFRL        | 2.2        | ±20%      | 0.30±25%          | 70                      | 750             |
|             | LQM18PN3R3MFRL        | 3.3        |           | 0.35±25%          | 60                      | 700             |
|             | LQM18PN4R7MFRL        | 4.7        |           | 0.44±25%          | 40                      | 620             |


## 4. Testing Conditions

《Unless otherwise specified》 《In case of doubt》

Humidity: Ordinary Humidity: / 25%(RH) to 85%(RH) Humidity: 60%(RH) to 70%(RH)

Atmospheric Pressure: 86kPa to 106kPa

5. Appearance and Dimensions



■ Unit Mass (Typical value) 0.005g

# Reference Only

## 6. Electrical Performance

| No. | Item                                  | Specification                                       | Test Method  |
|-----|---------------------------------------|---|--|
| 6.1 | Inductance                            | Inductance shall meet item 3.                       | Measuring Equipment:  KEYSIGHT 4294A or equivalent (1mA)  Measuring Frequency: 1MHz  |
| 6.2 | DC Resistance                         | DC Resistance shall meet item 3.                    | Measuring Equipment: Digital multi meter Digital multi meter (TR6846 or equivalent)  terminal 1—sw terminal 2  DC resistance shall be measured after putting chip coil between the terminal 2 under the condition of opening between a and b. Every measurement the terminal 1 shall be shorted between a and b when changing chip coil. |
| 6.3 | Self Resonant<br>Frequency<br>(S.R.F) | S.R.F shall meet item 3.                            | Measuring Equipment:  KEYSIGHT 4294A or equivalent   |
| 6.4 | Rated Current                         | Self temperature rise shall be limited to 40°C max. | The rated current is applied.  |

## 7. Mechanical Performance

| No. | Item         | Specification   | Test Method  |
|-----|--------------|---|--|
| 7.1 | Shear Test   | Chip coil shall not be damaged after tested as follows. | Applied Direction  Chip Coil  Substrate  Force: 10N  Hold Duration: 5s±1s  Applied Direction: Parallel to PCB  |
| 7.2 | Bending Test | Appearance: No damage                                   | Substrate: Glass-epoxy substrate (100mm × 40mm × 1.0mm)  Pressure jig  F  Deflection  45  Speed of Applying Force: 0.5mm / s  Deflection: 2mm  Hold Duration: 30 s |

| No. | Item                            | Specification  | Test Method  |
|-----|---------------------------------|--|--|
| 7.3 | Vibration                       | Appearance: No damage  | Oscillation Frequency: 10Hz to 2000Hz to 10Hz for 20 min Total amplitude 3.0 mm or Acceleration amplitude 245m/s² whichever is smaller. Testing Time: A period of 4h in each of 3 mutually perpendicular directions.                             |
| 7.4 | Drop                            |  | It shall be dropped on concrete or steel board.  Method: free fall Height: 1m Total of 10 cycles   |
| 7.5 | Solderability                   | The wetting area of the electrode shall be at least 90% covered with new solder coating. | Flux: Ethanol solution of rosin 25(wt)% (Immersed for 5s to 10s) Solder: Sn-3.0Ag-0.5Cu Pre-Heating: 150°C±10°C / 60s to 90s Solder Temperature: 240°C±5°C Immersion Time: 3s±1s   |
| 7.6 | Resistance to<br>Soldering Heat | Appearance: No damage Inductance Change: within ±30%                                     | Flux: Ethanol solution of rosin 25(wt)% (Immersed for 5s to 10s) Solder: Sn-3.0Ag-0.5Cu Pre-Heating: 150°C±10°C / 60s to 90s Solder Temperature: 270°C±5°C Immersion Time: 10s±1s Then measured after exposure in the room condition for 24h±2h. |


## 8. Environmental Performance

It shall be soldered on the substrate.

| No. | Item            | Specification                  | Test Method                               |
|-----|-----------------|--------------------------------|---|
| 8.1 | Heat Resistance | Appearance: No damage          | Temperature: 85°C±2°C                     |
|     |                 | Inductance Change: within ±30% | Time:1000h (+48h, -0h)                    |
|     |                 |                                | Then measured after exposure in the room  |
|     |                 |                                | condition for 24h±2h.                     |
| 8.2 | Cold Resistance |                                | Temperature: - 40°C±2°C                   |
|     |                 |                                | Time: 1000h (+48h, -0h)                   |
|     |                 |                                | Then measured after exposure in the room  |
|     |                 |                                | condition for 24h±2h.                     |
| 8.3 | Humidity        |                                | Temperature: 70°C±2°C                     |
|     |                 |                                | Humidity: 90%(RH) to 95%(RH)              |
|     |                 |                                | Time: 1000h (+48h, -0h)                   |
|     |                 |                                | Then measured after exposure in the room  |
|     |                 |                                | condition for 24h±2h.                     |
| 8.4 | Temperature     |                                | 1 cycle:                                  |
|     | Cycle           |                                | 1 step: - 40°C±2°C / 30 min±3 min         |
|     |                 |                                | 2 step: Ordinary temp. / 10 min to 15 min |
|     |                 |                                | 3 step: +85°C±2°C / 30 min to 3 min       |
|     |                 |                                | 4 step: Ordinary temp. / 10 min to15 min  |
|     |                 |                                | Total of 100cycles                        |
|     |                 |                                | Then measured after exposure in the room  |
|     |                 |                                | condition for 24h±2h.                     |

#### 9. Specification of Packaging

#### 9.1 Appearance and Dimensions of plastic tape (8mm-wide)



#### 9.2 Specification of Taping

- (1) Packing quantity (standard quantity)
  - 4,000 pcs / reel
- (2) Packing Method

Products shall be packed in the each embossed cavity of plastic tape and sealed by cover tape.

- (3) Sprocket hole
  - The sprocket holes are to the right as the tape is pulled toward the user.
- (4) Spliced point

Plastic tape and Cover tape has no spliced point.

(5) Missing components number


Missing components number within 0.1% of the number per reel or 1 pc., whichever is greater, and are not continuous. The Specified quantity per reel is kept.

#### 9.3 Pull Strength

| Plastic tape | 10N min. |
|--------------|----------|
| Cover tape   | 5N min.  |


#### 9.4 Peeling off force of cover tape

| Speed of Peeling off | 300mm / min                |
|----------------------|----------------------------|
| Dealing off force    | Plastic tape: 0.1N to 0.7N |
| Peeling off force    | (minimum value is typical) |



#### 9.5 Dimensions of Leader-tape, Trailer and Reel

There shall be leader-tape (cover tape) and trailer-tape (empty tape) as follows.





#### 9.6 Marking for reel

Customer part number, MURATA part Inspection number (\*1), RoHS marking (\*2), Quantity number,

\*1) < Expression of Inspection No.>

(1) Factory Code

: Year / Last digit of year (2) Date First digit

: Month / Jan. to Sep.  $\rightarrow$  1 to 9, Oct. to Dec.  $\rightarrow$  O, N, D Second digit

Third, Fourth digit: Day

(3) Serial No.

\*2) <Expression of RoHS marking>

 $ROHS - \underline{Y}(\underline{\Delta})$ 


(1) RoHS regulation conformity parts.

(2) MURATA classification number

#### 9.7 Marking for Outside package (corrugated paper box)

Customer name, Purchasing order number, Customer part number, MURATA part number, RoHS marking (\*2), Quantity, etc · · ·

#### 9.8 Specification of Outer Case



| Outer Case Dimensions (mm) |     | ensions | Standard Reel Quantity in Outer Case (Reel) |
|----------------------------|-----|---------|---|
| W                          | D   | Н       | III Outer Case (Reel)                       |
| 186                        | 186 | 93      | 5   |

\* Above Outer Case size is typical. It depends on a quantity of an order.

## 10. 🛕 Caution

#### **Limitation of Applications**

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.


- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment Power plant control equipment
- (5) Medical equipment
- (6) Transportation equipment (vehicles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- (9) Data-processing equipment (10) Applications of similar complexity and /or reliability requirements to the applications listed in the above

#### 11. Notice

This product is designed for solder mounting.

Please consult us in advance for applying other mounting method such as conductive adhesive.

#### 11.1 Land pattern designing



#### 11.2 Flux, Solder

·Use rosin-based flux.

Don't use highly acidic flux with halide content exceeding 0.2(wt) % (chlorine conversion value). Don't use water-soluble flux.

- •Use Sn-3.0Ag-0.5Cu solder.
- •Standard thickness of solder paste: 100 µm to 150 µm.

## 11.3 Flow soldering / Reflow soldering conditions

•Pre-heating should be in such a way that the temperature difference between solder and product surface is limited to 150°C max. Cooling into solvent after soldering also should be in such a way that the temperature difference is limited to 100°C max.


Insufficient pre-heating may cause cracks on the product, resulting in the deterioration of products quality.

•Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and/or resulting in the deterioration of product quality.


#### Soldering profile

#### (1) Flow soldering profile



|               | Standard Profile | Limit Profile |  |
|---------------|------------------|---------------|--|
| Pre-heating   | 150°C, 60s min.  |               |  |
| Heating       | 250°C, 4s∼6s     | 265°C±3°C, 5s |  |
| Cycle of flow | 2 times          | 2 times       |  |

## (2) Reflow soldering profile



|                  | Standard Profile     | Limit Profile         |
|------------------|----------------------|-----------------------|
| Pre-heating      | 150°C∼180°           | C, 90s±30s            |
| Heating          | above 220°C, 30s∼60s | above 230°C, 60s max. |
| Peak temperature | 245°C±3°C            | 260°C,10s             |
| Cycle of reflow  | 2 times              | 2 times               |

P.7/9

followed

strictly

#### 11.4 Reworking with soldering iron


The following conditions must be when using a soldering iron.

| Pre-heating           | 150°C,1 min |
|-----------------------|-------------|
| Tip temperature       | 350°C max.  |
| Soldering iron output | 80W max.    |
| Tip diameter          | ¢3mm max.   |
| Soldering time        | 3(+1, -0)s  |
| Time                  | 2 times     |

Note: Do not directly touch the products with the tip of the soldering iron in order to prevent the crack on the products due to the thermal shock.

#### 11.5 Solder Volume


- Solder shall be used not to be exceeded the upper limits as shown below.
- · Accordingly increasing the solder volume, the mechanical stress to Chip is also increased. Exceeding solder volume may cause the failure of mechanical or electrical performance.



#### 11.6 Product's location

The following shall be considered when designing and laying out P.C.B.'s.

(1) P.C.B. shall be designed so that products are not subject to the mechanical stress due to warping the board.




Products shall be located in the sideways direction (Length: a/b) to the mechanical

(2)Components location on P.C.B. separation.

It is effective to implement the following measures, to reduce stress in separating the board. It is best to implement all of the following three measures; however, implement as many measures as possible to reduce stress.

| Contents of Measures   | Stress Level |
|--|--------------|
| (1) Turn the mounting direction of the component parallel to the board separation surface. | A > D*1      |
| (2) Add slits in the board separation part.  | A > B        |
| (3) Keep the mounting position of the component away from the board separation surface.    | A > C        |




- \*1 A > D is valid when stress is added vertically to the perforation as with Hand Separation. If a Cutting Disc is used, stress will be diagonal to the PCB, therefore A > D is invalid.
  - (3) Mounting Components Near Screw Holes

When a component is mounted near a screw hole, it may be affected by the board deflection that occurs during the tightening of the screw. Mount the component in a position as far away from the screw holes

## Reference Only

as possible.



#### 11.7 Cleaning Conditions

Products shall be cleaned on the following conditions.

- (1) Cleaning temperature shall be limited to 60°C max. (40°C max for IPA.)
- (2) Ultrasonic cleaning shall comply with the following conditions with avoiding the resonance phenomenon at the mounted products and P.C.B.

Power: 20 W / I max. Frequency: 28kHz to 40kHz Time: 5 min max.

- (3) Cleaner
  - 1. Alcohol type cleaner Isopropyl alcohol (IPA)
  - 2. Aqueous agent PINE ALPHA ST-100S
- (4) There shall be no residual flux and residual cleaner after cleaning. In the case of using aqueous agent, products shall be dried completely after rinse with de-ionized water in order to remove the cleaner.
- (5) Other cleaning Please contact us.

#### 11.8 Resin coating

The inductance value may change and/or it may affect on the product's performance due to high cure-stress of resin to be used for coating/molding products. So please pay your careful attention when you select resin.

In prior to use, please make the reliability evaluation with the product mounted in your application set.

#### 11.9 Caution for use

There is possibility that the inductance value change due to magnetism. Don't use a magnet or a pair of tweezers with magnetism when chip coil are handled. (The tip of the tweezers should be molded with resin or pottery.)

#### 11.10 Magnetic Saturation


When the excessive current over rated current is applied, the inductance value may change due to magnetism.

#### 11.11 Handling of a substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.

Excessive mechanical stress may cause cracking in the product.

Bending Twisting





#### 11.12 Storage and Handing Requirements

(1) Storage period

Use the products within 6 months after delivered.

Solderability should be checked if this period is exceeded.

#### (2) Storage conditions

• Products should be stored in the warehouse on the following conditions.

Temperature : -10°C to 40°C

Humidity : 15% to 85% relative humidity No rapid change on temperature and humidity

Don't keep products in corrosive gases such as sulfur, chlorine gas or acid, or it may cause oxidization of electrode, resulting in poor solderability.

- Products should be stored on the palette for the prevention of the influence from humidity, dust and so on.
- Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be stored under the airtight packaged condition.

#### (3) Handling Condition

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.

## 12. ANotes

- (1)Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2) You are requested not to use our product deviating from the reference specifications.
- (3)The contents of this reference specification are subject to change without advance notice.

Please approve our product specifications or transact the approval sheet for product specifications before ordering.