multicomp PRO

RoHS


Compliant



Specifications

Case Size	: 2512
Power Rating at 70°C	: 3W
Max. Working Voltage	: 250V
Max. Overload Voltage	: 500V
Dielectric Withstanding Voltage	: 500V
Temperature Range	: -55°C to +155°C
Ambient Temperature	: 70°C

Dimensions and Power Rating



Туре	Power Rating	L	w	н	£ 1	£2
2512	3W	6.35 ±1	3.2 ±0.15	0.55 ±0.1	0.6 ±0.25	0.5 ±0.2

Dimensions : Millimetres

Туре	Power Rating at 70°C	Tolerance %	Resistance Range	Standard Series
2512	2)///	± 1	10 to 190K0	E-96
2012	2512 3W ± 5	± 5	1Ω to 180KΩ	E-24


Jumper

Туре	Power Rating	L	w	н	୧1	£2
2512	3W	6.35 ±1	3.2 ±0.15	1.1 ±0.1	0.6 ±0.25	1.8 ±0.2

Туре	Power Rating	Rated Current at 70°C	Resistance Range	Max. Overload Current
2512	3W	2A	Jumper	10A


Power Rating

Resistors shall have a power rating based on continuous load operation at an ambient temperature of 70°C. For temperature in excess of 70°C, the load shall be derate as shown in figure.





multicomp PRO



Jumper Characteristics

Characteristics	Values
Max. Resistance	1% : 30mΩ
Max. Resistance	5% : 50mΩ
Insulation Resistance	1,000MΩ or More
Dielectric-Withstanding Voltage	Apply 500V AC between protective coating and termination for 1 minute.
Solderability	245 ±3°C, 2~3 seconds 95 % Coverage Min.

Performance Specification

Characteristics	Limits	Test Methods (JIS C 5201-1)
Dielectric withstanding voltage	No evidence of flashover mechanical damage, arcing or insulation break down	Clamped in the trough of a 90°C metallic v-block and shall be tested at ac potential respectively specified in the type for 60-70 seconds
Temperature	1Ω to 10Ω ≤± 200PPM/°C	Natural resistance change per temperature degree centigrade. $\frac{R2-R1}{R1(t2-t1)} \times 10^{6} (PPM/^{\circ}C)$
Coefficient	10.1Ω to 10MΩ ≤± 100PPM/°C	R1: Resistance value at room temperature (T1) R2: Resistance value at room temp. plus 100°C (T2) Test pattern: room temp. (T1), room temp. +100°C (T2)
Short time overload	Resistance change rate is ±5% (2% +0.1Ω) Max. ±1% (1% +0.1Ω) Max.	Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds
Soldering temperature	Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95 % coverage Min.)	Wave soldering condition: (2 cycles Max.) Pre-heat : 100°C to 120°C, 30 ± 5 sec. Suggestion solder temp.: 235°C to 255°C, 10 sec. (Max.) Peak temp.: 260°C
reference		Reflow soldering condition : (2 cycles Max.) Pre-heat : 150°C to 180°C, 90 to 120 sec. Suggestion solder temp.: 235°C to 255°C, 20 ~ 40 sec. Peak temp.: 260°C




multicomp PRO

Characteristics	Limits	Test Methods (JIS C 5201-1)	
Soldering temperature reference			
Soldering heat	bldering heat $\begin{array}{c} \text{Resistance change rate is:} \\ \pm (1\%+0.05\Omega) \text{ Max.} \end{array} \qquad \begin{array}{c} \text{Dip the resistor into a solder bath having a temperat} \\ 260^\circ \text{C} \pm 3^\circ \text{C} \text{ and hold it for 10} \pm 1 \text{ seconds.} \end{array}$		
Humidity	HumidityResistance change rate is $\pm 5\% (3\% + 0.1\Omega)$ Max. $\pm 1\% (0.5\% + 0.1\Omega)$ Max.Temporary resistance change after 240 hours exponent humidity test chamber controlled at 40±2°C and 90 humidity		
Load life in humidity	Resistance change rate is ± 5% (3% + 0.1Ω) Max. ± 1% (1.0% + 0.1Ω) Max.	Resistance change after 1,000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity chamber controlled at $40^{\circ}C \pm 2^{\circ}C$ and 90 to 95 % relative humidity	
Load Life	Resistance change rate is ± 5% (3% + 0.1Ω) Max. ± 1% (1% + 0.1Ω) Max.	Permanent resistance change after 1,000 hours operating at RCWV, with duty cycle of (1.5 hours"on", 0.5 hour"off") at $70^{\circ}C \pm 2^{\circ}C$ ambient	
Terminal bending	Resistance change rate is ± (1.0% + 0.05Ω) Max.	Twist of Test Board : Y/X = 3/90 mm for 60 seconds	
		Resistance change after continuous 5 cycles for duty cycle specified below : Step Temperature	
Temperature cycling	Resistance change rate is $\pm 5\% (1.0\% + 0.1\Omega)$ Max.	1 -55°C ±3°C 30 mins	
	± 1% (0.5% + 0.1Ω) Max.	2 Room temp. 10 to 15 mins	
		3 +155°C ±2°C 30 mins	
		4 Room temp. 10 to 15 mins	

Packing specification

Taping Dimension




Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro


multicomp PRO

multicomp PRO

Peeling Strength of Top Cover Tape Test Condition: 0.1 to 0.7 N at a peel-off speed of 300mm / min.




Reel Dimension



Туре	A ±0.5	B ± 0.5	C ±0.5	D ±1	M ±2	W ±1
2512	2	13.5	21	60	178	13.5

Dimensions : Millimetres

Recommended solder pad



Α	В	С
3.7	2.8	2.7

Dimensions : Millimetres

Part Number Table

Description	Part Number
Chip Resistor, Thick Film, 1%, 200R, ± 100ppm/°C, 3W, 2512	MP001037
Chip Resistor, Thick Film, 1%, 5R1, ± 200ppm/°C, 3W, 2512	MP001038
Chip Resistor, Thick Film, 1%, 15R, ± 100ppm/°C, 3W, 2512	MP001039
Chip Resistor, Thick Film, 1%, 20R, ± 100ppm/°C, 3W, 2512	MP001040
Chip Resistor, Thick Film, 1%, 33R, ± 100ppm/°C, 3W, 2512	MP001041
Chip Resistor, Thick Film, 1%, 16R, ± 100ppm/°C, 3W, 2512	MP001042
Chip Resistor, Thick Film, 1%, 2K, ± 100ppm/°C, 3W, 2512	MP001043
Chip Resistor, Thick Film, 1%, 36K, ± 100ppm/°C, 3W, 2512	MP001044



multicomp PRO

Description	Part Number
Chip Resistor, Thick Film, 1%, 750R, ± 100ppm/°C, 3W, 2512	MP001045
Chip Resistor, Thick Film, 1%, 51R, ± 100ppm/°C, 3W, 2512	MP001046
Chip Resistor, Thick Film, 1%, 390R, ± 100ppm/°C, 3W, 2512	MP001047
Chip Resistor, Thick Film, 1%, 27R, ± 100ppm/°C, 3W, 2512	MP001048
Chip Resistor, Thick Film, 1%, 10R, ± 200ppm/°C, 3W, 2512	MP001049
Chip Resistor, Thick Film, 1%, 12R, ± 100ppm/°C, 3W, 2512	MP001050
Chip Resistor, Thick Film, 1%, 1K, ± 100ppm/°C, 3W, 2512	MP001051
Chip Resistor, Thick Film, 1%, 30R, ± 100ppm/°C, 3W, 2512	MP001052
Chip Resistor, Thick Film, 1%, 36R, ± 100ppm/°C, 3W, 2512	MP001053
Chip Resistor, Thick Film, 1%, 150R, ± 100ppm/°C, 3W, 2512	MP001054
Chip Resistor, Thick Film, 1%, 100R, ± 100ppm/°C, 3W, 2512	MP001055
Chip Resistor, Thick Film, 1%, 22R, ± 100ppm/°C, 3W, 2512	MP001056
Chip Resistor, Thick Film, 1%, 91R, ± 100ppm/°C, 3W, 2512	MP001057
Chip Resistor, Thick Film, 1%, 3K, ± 100ppm/°C, 3W, 2512	MP001058
Chip Resistor, Thick Film, 1%, 75R, ± 100ppm/°C, 3W, 2512	MP001059
Chip Resistor, Thick Film, 1%, 430R, ± 100ppm/°C, 3W, 2512	MP001060
Chip Resistor, Thick Film, 1%, 100K, ± 100ppm/°C, 3W, 2512	MP001061
Chip Resistor, Thick Film, 1%, 120R, ± 100ppm/°C, 3W, 2512	MP001062
Chip Resistor, Thick Film, 1%, 62R, ± 100ppm/°C, 3W, 2512	MP001063
Chip Resistor, Thick Film, 1%, 330R, ± 100ppm/°C, 3W, 2512	MP001064
Chip Resistor, Thick Film, 1%, 910R, ± 100ppm/°C, 3W, 2512	MP001065
Chip Resistor, Thick Film, 1%, 18R, ± 100ppm/°C, 3W, 2512	MP001066
Chip Resistor, Thick Film, 1%, 47R, ± 100ppm/°C, 3W, 2512	MP001067
Chip Resistor, Thick Film, 1%, 110R, ± 100ppm/°C, 3W, 2512	MP001068
Chip Resistor, Thick Film, 1%, 560R, ± 100ppm/°C, 3W, 2512	MP001069
Chip Resistor, Thick Film, 1%, 2K2, ± 100ppm/°C, 3W, 2512	MP001070
Chip Resistor, Thick Film, 1%, 24K, ± 100ppm/°C, 3W, 2512	MP001071
Chip Resistor, Thick Film, 1%, 33K, ± 100ppm/°C, 3W, 2512	MP001072
Chip Resistor, Thick Film, 1%, 24R, ± 100ppm/°C, 3W, 2512	MP001073
Chip Resistor, Thick Film, 1%, 39R, ± 100ppm/°C, 3W, 2512	MP001074
Chip Resistor, Thick Film, 1%, 300R, ± 100ppm/°C, 3W, 2512	MP001075
Chip Resistor, Thick Film, 1%, 680R, ± 100ppm/°C, 3W, 2512	MP001076
Chip Resistor, Thick Film, 5%, 15R, ± 100ppm/°C, 3W, 2512	MP001077
Chip Resistor, Thick Film, 5%, 2K2, ± 100ppm/°C, 3W, 2512	MP001079
Chip Resistor, Thick Film, 5%, 47R, ± 100ppm/°C, 3W, 2512	MP001080
Chip Resistor, Thick Film, 5%, 1R, ± 200ppm/°C, 3W, 2512	MP001081
Chip Resistor, Thick Film, 5%, 4R7, ± 200ppm/°C, 3W, 2512	MP001082
Chip Resistor, Thick Film, 5%, 3R9, ± 200ppm/°C, 3W, 2512	MP001083
Chip Resistor, Thick Film, 5%, 220R, ± 100ppm/°C, 3W, 2512	MP001084



multicomp PRO

Description	Part Number
Chip Resistor, Thick Film, 5%, 120R, ± 100ppm/°C, 3W, 2512	MP001085
Chip Resistor, Thick Film, 5%, 2R2, ± 200ppm/°C, 3W, 2512	MP001086
Chip Resistor, Thick Film, 5%, 33K, ± 100ppm/°C, 3W, 2512	MP001087
Chip Resistor, Thick Film, 5%, 100K, ± 100ppm/°C, 3W, 2512	MP001088
Chip Resistor, Thick Film, 5%, 10R, ± 200ppm/°C, 3W, 2512	MP001089
Chip Resistor, Thick Film, 5%, 470R, ± 100ppm/°C, 3W, 2512	MP001090
Chip Resistor, Thick Film, 5%, 5R6, ± 200ppm/°C, 3W, 2512	MP001091
Chip Resistor, Thick Film, 5%, 2R7, ± 200ppm/°C, 3W, 2512	MP001092
Chip Resistor, Thick Film, 5%, 68R, ± 100ppm/°C, 3W, 2512	MP001093
Chip Resistor, Thick Film, 5%, 15K, ± 100ppm/°C, 3W, 2512	MP001094
Chip Resistor, Thick Film, 5%, 180R, ± 100ppm/°C, 3W, 2512	MP001095
Chip Resistor, Thick Film, 5%, 10K, ± 100ppm/°C, 3W, 2512	MP001096
Chip Resistor, Thick Film, 5%, 39K, ± 100ppm/°C, 3W, 2512	MP001097
Chip Resistor, Thick Film, 5%, 27R, ± 100ppm/°C, 3W, 2512	MP001098
Chip Resistor, Thick Film, 5%, 1R2, ± 200ppm/°C, 3W, 2512	MP001099
Chip Resistor, Thick Film, 5%, 3R3, ± 200ppm/°C, 3W, 2512	MP001100
Chip Resistor, Thick Film, 5%, 8R2, ± 200ppm/°C, 3W, 2512	MP001101
Chip Resistor, Thick Film, 5%, 47K, ± 100ppm/°C, 3W, 2512	MP001102
Chip Resistor, Thick Film, 5%, 6R8, ± 200ppm/°C, 3W, 2512	MP001103
Chip Resistor, Thick Film, 5%, 18R, ± 100ppm/°C, 3W, 2512	MP001104
Chip Resistor, Thick Film, 5%, 100R, ± 100ppm/°C, 3W, 2512	MP001105
Chip Resistor, Thick Film, 5%, 1K, ± 100ppm/°C, 3W, 2512	MP001106
Chip Resistor, Thick Film, 5%, 5K6, ± 100ppm/°C, 3W, 2512	MP001107
Chip Resistor, Thick Film, 5%, 560R, ± 100ppm/°C, 3W, 2512	MP001108
Chip Resistor, Thick Film, 5%, 1K5, ± 100ppm/°C, 3W, 2512	MP001109
Chip Resistor, Thick Film, 5%, 12R, ± 100ppm/°C, 3W, 2512	MP001110
Chip Resistor, Thick Film, 5%, 150R, ± 100ppm/°C, 3W, 2512	MP001111
Chip Resistor, Thick Film, 5%, 180K, ± 100ppm/°C, 3W, 2512	MP001112
Chip Resistor, Thick Film, 5%, 1R8, ± 200ppm/°C, 3W, 2512	MP001113
Chip Resistor, Thick Film, 5%, 270R, ± 100ppm/°C, 3W, 2512	MP001114
Chip Resistor, Thick Film, 5%, 27K, ± 100ppm/°C, 3W, 2512	MP001115
Chip Resistor, Thick Film, 5%, 12K, ± 100ppm/°C, 3W, 2512	MP001116
Chip Resistor, Thick Film, Jumper, 3W, 2512	MP001078

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

