

### WSX240-1000-13

#### Electrical Specifications (@25C)

1. Input Voltage rating: 100-240VAC, 50-60Hz
2. Input Voltage range: 90-264VAC
3. Input current: 0.7A(RMS) @ 115VAC
4. Max Inrush Current: 60A @ 115VAC (Cold start)
5. Output Voltage: 24.0VDC
6. Output Current: 1.0A
7. Regulation (line & load):  $\pm 5\%$
8. Ripple: 150mVpk-pk Max
9. No load power (stand by): < 100 mW typ.
10. Efficiency @ 10% load: 82.68% typ.
11. Average Efficiency: 83.50% Typ. Meets minimum level VI efficiency.

#### Environmental Specifications

1. Operating Temperature Range: 0°C to +45° C @ full load
2. Storage Temperature Range: -20°C to 60°C
3. Humidity: 5% to 95%, Non-condensing

#### Reliability Specifications

1. Leakage Current: <0.25mA (264VAC)
2. Dielectric Strength (Hi-pot): 4242VDC/3secs., 5mA Max
3. Warranty: 5 years

#### Mechanical Parameters

Case Type: Thermoplastic molded enclosure.

Output Cord: 24 AWG, 6 Ft. Long Nom.

#### Safety & EMI

UL: 62368-1 Class II, Double Insulated

UL File Number: E345519

TUV: IEC 62368-1:2014 (Second Edition)

AS/NZS: AS/NZS 62368.1:2018 & AS/NZS 3112:2017

GS (S50452256): EN 62368-1: 2014 + A11

RCM: RCM201901745 Rev01

EMI standard: FCC part15 Subpart B, ICES-003 Issue 6, ANSI C63.4-2014



Over voltage and short circuit protected



**EISA 2007/CEC Compliance:** This power supply meets the minimum efficiency requirements per Department of Energy and California Energy Commission.


**RoHS Compliance:** As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

Upon printing, this document is considered “uncontrolled”. Please contact Triad Magnetics’ website for the most current version.




North America

European Union




United Kingdom

Australia/New Zealand



China



Dim.: mm

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Triad Magnetics:](#)

[WSX240-1000-13](#)