





**Contactor, 3 pole, 380 V 400 V 22 kW, 110 V 50 Hz, 120 V 60 Hz, AC operation, Screw terminals**

**Part no.** DILM50(110V50HZ,120V60HZ)  
**Catalog No.** 277827  
**Alternate Catalog No.** XTCE050D00A  
**EL-Nummer (Norway)** 4130446

**Delivery program**

|   |                |    |  |  |
|---|----------------|----|--|--|
| Product range   |                |    |  | Contactors   |
| Application   |                |    |  | Contactors for Motors  |
| Subrange  |                |    |  | Contactors up to 170 A, 3 pole   |
| Utilization category                                      |                |    |  | AC-1: Non-inductive or slightly inductive loads, resistance furnaces<br>NAC-3: Normal AC induction motors: starting, switch off during running<br>AC-4: Normal AC induction motors: starting, plugging, reversing, inching |
|   |                |    |  |    |
| Notes   |                |    |  | Also suitable for motors with efficiency class IE3.<br>IE3-ready devices are identified by the logo on their packaging.  |
| Connection technique                                      |                |    |  | Screw terminals  |
| Number of poles   |                |    |  | 3 pole   |
| <b>Rated operational current</b>                          |                |    |  |  |
| AC-3  |                |    |  |  |
| Notes   |                |    |  | At maximum permissible ambient temperature (open.)   |
| 380 V 400 V   | $I_e$          | A  |  | 50   |
| AC-1  |                |    |  |  |
| Conventional free air thermal current, 3 pole, 50 - 60 Hz |                |    |  |  |
| Open  |                |    |  |  |
| at 40 °C  | $I_{th} = I_e$ | A  |  | 80   |
| enclosed  | $I_{th}$       | A  |  | 58   |
| Conventional free air thermal current, 1 pole             |                |    |  |  |
| open  | $I_{th}$       | A  |  | 162  |
| enclosed  | $I_{th}$       | A  |  | 145  |
| <b>Max. rating for three-phase motors, 50 - 60 Hz</b>     |                |    |  |  |
| AC-3  |                |    |  |  |
| 220 V 230 V   | P              | kW |  | 15.5   |
| 380 V 400 V   | P              | kW |  | 22   |
| 660 V 690 V   | P              | kW |  | 30   |
| AC-4  |                |    |  |  |
| 220 V 230 V   | P              | kW |  | 6  |
| 380 V 400 V   | P              | kW |  | 10   |
| 660 V 690 V   | P              | kW |  | 14   |
| Contact sequence  |                |    |  |    |
| <b>Instructions</b>                                       |                |    |  | Contacts to EN 50 012.   |
| Can be combined with auxiliary contact                    |                |    |  | DILM150-XH(V)...<br>DILM1000-XH(V)...  |
| Actuating voltage   |                |    |  | 110 V 50 Hz, 120 V 60 Hz   |
| Voltage AC/DC   |                |    |  | AC operation   |
| Connection to SmartWire-DT                                |                |    |  | no   |
| Frame size  |                |    |  | 3  |

## Technical data

### General

|   |                                     |               |  |
|---|-------------------------------------|---------------|--|
| Standards   |                                     |               | IEC/EN 60947, VDE 0660, UL, CSA  |
| Lifespan, mechanical  |                                     |               |  |
| AC operated   | Operations                          | $\times 10^6$ | 10   |
| Operating frequency, mechanical                                       |                                     |               |  |
| AC operated   | Operations/h                        |               | 5000   |
| Climatic proofing   |                                     |               | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30     |
| Ambient temperature   |                                     |               |  |
| Open  | °C                                  |               | -25 - +60  |
| Enclosed  | °C                                  |               | - 25 - 40  |
| Storage   | °C                                  |               | - 40 - 80  |
| Mounting position   |                                     |               |  |
| Mechanical shock resistance (IEC/EN 60068-2-27)                       |                                     |               |  |
| Half-sinusoidal shock, 10 ms  |                                     |               |  |
| Main contacts   |                                     |               |  |
| N/O contact   | g                                   |               | 10   |
| Auxiliary contacts  |                                     |               |  |
| N/O contact   | g                                   |               | 7  |
| N/C contact   | g                                   |               | 5  |
| Mechanical shock resistance (IEC/EN 60068-2-27) when tabletop-mounted |                                     |               |  |
| Half-sinusoidal shock, 10 ms  |                                     |               |  |
| Main contacts   |                                     |               |  |
| N/O contact   | g                                   |               | 10   |
| Auxiliary contacts  |                                     |               |  |
| N/O contact   | g                                   |               | 7  |
| N/C contact   | g                                   |               | 5  |
| Degree of Protection  |                                     |               | IP00   |
| Protection against direct contact when actuated from front (EN 50274) |                                     |               | Finger and back-of-hand proof  |
| Altitude  | m                                   |               | Max. 2000  |
| Weight  |                                     |               |  |
| AC operated   | kg                                  |               | 0.872  |
| Screw connector terminals   |                                     |               |  |
| Terminal capacity main cable  |                                     |               |  |
| Solid   | mm <sup>2</sup>                     |               | 1 x (0.75 - 16)<br>2 x (0.75 - 16)   |
| Flexible with ferrule   | mm <sup>2</sup>                     |               | 1 x (0.75 - 35)<br>2 x (0.75 - 25)   |
| Stranded  | mm <sup>2</sup>                     |               | 1 x (16 - 50)<br>2 x (16 - 35)   |
| Solid or stranded   | AWG                                 |               | single 14 - 1, double 14 - 2   |
| Flat conductor  | Lamellenzahl<br>x Breite x<br>Dicke | mm            | 2 x (6 x 9 x 0.8)  |
| Stripping length  | mm                                  |               | 14   |
| Terminal screw  |                                     |               | M6   |
| Tightening torque   | Nm                                  |               | 3.3  |
| Tool  |                                     |               |  |
| Pozidriv screwdriver  | Size                                |               | 2  |
| Standard screwdriver  | mm                                  |               | 0.8 x 5.5<br>1 x 6   |
| Terminal capacity control circuit cables                              |                                     |               |  |

|                       |  |                 |                                      |
|-----------------------|--|-----------------|--------------------------------------|
| Solid                 |  | mm <sup>2</sup> | 1 x (0.75 - 4)<br>2 x (0.75 - 2.5)   |
| Flexible with ferrule |  | mm <sup>2</sup> | 1 x (0.75 - 2.5)<br>2 x (0.75 - 2.5) |
| Solid or stranded     |  | AWG             | 18 - 14                              |
| Stripping length      |  | mm              | 10                                   |
| Terminal screw        |  |                 | M3.5                                 |
| Tightening torque     |  | Nm              | 1.2                                  |
| Tool                  |  |                 |                                      |
| Pozidriv screwdriver  |  | Size            | 2                                    |
| Standard screwdriver  |  | mm              | 0.8 x 5.5<br>1 x 6                   |

### Main conducting paths

|  |             |      |       |
|--|-------------|------|-------|
| Rated impulse withstand voltage        | $U_{imp}$   | V AC | 8000  |
| Overvoltage category/pollution degree  |             |      | III/3 |
| Rated insulation voltage               | $U_i$       | V AC | 690   |
| Rated operational voltage              | $U_e$       | V AC | 690   |
| Safe isolation to EN 61140             |             |      |       |
| between coil and contacts              |             | V AC | 440   |
| between the contacts                   |             | V AC | 440   |
| Making capacity (p.f. to IEC/EN 60947) |             |      |       |
|  | Up to 690 V | A    | 700   |
| Breaking capacity                      |             |      |       |
| 220 V 230 V                            |             | A    | 500   |
| 380 V 400 V                            |             | A    | 500   |
| 500 V                                  |             | A    | 500   |
| 660 V 690 V                            |             | A    | 320   |
| Short-circuit rating                   |             |      |       |
| Short-circuit protection maximum fuse  |             |      |       |
| Type "2" coordination                  |             |      |       |
| 400 V                                  | gG/gL 500 V | A    | 80    |
| 690 V                                  | gG/gL 690 V | A    | 63    |
| Type "1" coordination                  |             |      |       |
| 400 V                                  | gG/gL 500 V | A    | 160   |
| 690 V                                  | gG/gL 690 V | A    | 80    |

### AC

|   |                |   |  |
|---|----------------|---|--|
| AC-1  |                |   |  |
| Rated operational current                                 |                |   |  |
| Conventional free air thermal current, 3 pole, 50 - 60 Hz |                |   |  |
| Open  |                |   |  |
| at 40 °C  | $I_{th} = I_e$ | A | 80   |
| at 50 °C  | $I_{th} = I_e$ | A | 71   |
| at 55 °C  | $I_{th} = I_e$ | A | 68   |
| at 60 °C  | $I_{th} = I_e$ | A | 65   |
| enclosed  | $I_{th}$       | A | 58   |
| Conventional free air thermal current, 1 pole             |                |   |  |
| open  | $I_{th}$       | A | 162  |
| enclosed  | $I_{th}$       | A | 145  |
| AC-3  |                |   |  |
| Rated operational current                                 |                |   |  |
| Open, 3-pole: 50 - 60 Hz                                  |                |   |  |
| Notes   |                |   | At maximum permissible ambient temperature (open.) |
| 220 V 230 V   | $I_e$          | A | 50   |
| 240 V   | $I_e$          | A | 50   |
| 380 V 400 V   | $I_e$          | A | 50   |
| 415 V   | $I_e$          | A | 50   |

|                          |                |     |      |
|--------------------------|----------------|-----|------|
| 440V                     | I <sub>e</sub> | A   | 50   |
| 500 V                    | I <sub>e</sub> | A   | 50   |
| 660 V 690 V              | I <sub>e</sub> | A   | 32   |
| 380 V 400 V              | I <sub>e</sub> | A   | 50   |
| Motor rating             | P              | kWh |      |
| 220 V 230 V              | P              | kW  | 15.5 |
| 240V                     | P              | kW  | 17   |
| 380 V 400 V              | P              | kW  | 22   |
| 415 V                    | P              | kW  | 30   |
| 440 V                    | P              | kW  | 32   |
| 500 V                    | P              | kW  | 36   |
| 660 V 690 V              | P              | kW  | 30   |
| <b>AC-4</b>              |                |     |      |
| Open, 3-pole: 50 – 60 Hz |                |     |      |
| 220 V 230 V              | I <sub>e</sub> | A   | 21   |
| 240 V                    | I <sub>e</sub> | A   | 21   |
| 380 V 400 V              | I <sub>e</sub> | A   | 21   |
| 415 V                    | I <sub>e</sub> | A   | 21   |
| 440 V                    | I <sub>e</sub> | A   | 21   |
| 500 V                    | I <sub>e</sub> | A   | 21   |
| 660 V 690 V              | I <sub>e</sub> | A   | 17   |
| Motor rating             | P              | kWh |      |
| 220 V 230 V              | P              | kW  | 6    |
| 240 V                    | P              | kW  | 6.5  |
| 380 V 400 V              | P              | kW  | 10   |
| 415 V                    | P              | kW  | 11   |
| 440 V                    | P              | kW  | 12   |
| 500 V                    | P              | kW  | 13   |
| 660 V 690 V              | P              | kW  | 14   |

## DC

|                                 |                |   |    |
|---------------------------------|----------------|---|----|
| Rated operational current, open |                |   |    |
| DC-1                            |                |   |    |
| 60 V                            | I <sub>e</sub> | A | 60 |
| 110 V                           | I <sub>e</sub> | A | 50 |
| 220 V                           | I <sub>e</sub> | A | 45 |

## Current heat loss

|   |  |    |      |
|---|--|----|------|
| 3 pole, at I <sub>th</sub> (60°)                  |  | W  | 16.7 |
| Current heat loss at I <sub>e</sub> to AC-3/400 V |  | W  | 9.9  |
| Impedance per pole                                |  | mΩ | 1.9  |

## Magnet systems

|  |          |                  |           |
|--|----------|------------------|-----------|
| Voltage tolerance  |          |                  |           |
| AC operated  | Pick-up  | x U <sub>c</sub> | 0.8 - 1.1 |
| Drop-out voltage AC operated   | Drop-out | x U <sub>c</sub> | 0.3 - 0.6 |
| Power consumption of the coil in a cold state and 1.0 x U <sub>S</sub> |          |                  |           |
| 50 Hz  | Pick-up  | VA               | 149       |
| 50 Hz  | Sealing  | VA               | 16        |
| 50 Hz  | Sealing  | W                | 4.1       |
| 60 Hz  | Pick-up  | VA               | 178       |
| 60 Hz  | Sealing  | VA               | 19        |
| 60 Hz  | Sealing  | W                | 4.1       |
| Duty factor  |          | % DF             | 100       |
| Changeover time at 100 % U <sub>S</sub> (recommended value)            |          |                  |           |
| Main contacts  |          |                  |           |
| AC operated  |          |                  |           |

|               |    |         |
|---------------|----|---------|
| Closing delay | ms | 12 - 18 |
| Opening delay | ms | 8 - 13  |
| Arcing time   | ms | 10      |

### Electromagnetic compatibility (EMC)

|                       |  |               |
|-----------------------|--|---------------|
| Emitted interference  |  | to EN 60947-1 |
| Interference immunity |  | to EN 60947-1 |

### Rating data for approved types

|                                      |    |                 |
|--------------------------------------|----|-----------------|
| Switching capacity                   |    |                 |
| Maximum motor rating                 |    |                 |
| Three-phase                          |    |                 |
| 200 V<br>208 V                       | HP | 15              |
| 230 V<br>240 V                       | HP | 20              |
| 460 V<br>480 V                       | HP | 40              |
| 575 V<br>600 V                       | HP | 50              |
| Single-phase                         |    |                 |
| 115 V<br>120 V                       | HP | 3               |
| 230 V<br>240 V                       | HP | 10              |
| General use                          | A  | 80              |
| Short Circuit Current Rating         |    |                 |
| Basic Rating                         |    |                 |
| SCCR                                 | kA | 10              |
| max. Fuse                            | A  | 250             |
| max. CB                              | A  | 250             |
| 480 V High Fault                     |    |                 |
| SCCR (fuse)                          | kA | 30/100          |
| max. Fuse                            | A  | 250/150 Class J |
| SCCR (CB)                            | kA | 65              |
| max. CB                              | A  | 100             |
| 600 V High Fault                     |    |                 |
| SCCR (fuse)                          | kA | 30/100          |
| max. Fuse                            | A  | 250/150 Class J |
| SCCR (CB)                            | kA | 30              |
| max. CB                              | A  | 250             |
| Special Purpose Ratings              |    |                 |
| Electrical Discharge Lamps (Ballast) |    |                 |
| 480V 60Hz 3phase, 277V 60Hz 1phase   | A  | 79              |
| 600V 60Hz 3phase, 347V 60Hz 1phase   | A  | 79              |
| Incandescent Lamps (Tungsten)        |    |                 |
| 480V 60Hz 3phase, 277V 60Hz 1phase   | A  | 74              |
| 600V 60Hz 3phase, 347V 60Hz 1phase   | A  | 74              |
| Resistance Air Heating               |    |                 |
| 480V 60Hz 3phase, 277V 60Hz 1phase   | A  | 79              |
| 600V 60Hz 3phase, 347V 60Hz 1phase   | A  | 79              |
| Elevator Control                     |    |                 |
| 200V 60Hz 3phase                     | HP | 10              |
| 200V 60Hz 3phase                     | A  | 32.2            |
| 240V 60Hz 3phase                     | HP | 15              |
| 240V 60Hz 3phase                     | A  | 42              |
| 480V 60Hz 3phase                     | HP | 30              |
| 480V 60Hz 3phase                     | A  | 40              |
| 600V 60Hz 3phase                     | HP | 40              |
| 600V 60Hz 3phase                     | A  | 41              |

## Design verification as per IEC/EN 61439

| Technical data for design verification   |            |    |  |
|--|------------|----|--|
| Rated operational current for specified heat dissipation   | $I_n$      | A  | 50   |
| Heat dissipation per pole, current-dependent   | $P_{vid}$  | W  | 3.3  |
| Equipment heat dissipation, current-dependent  | $P_{vid}$  | W  | 9.9  |
| Static heat dissipation, non-current-dependent   | $P_{vs}$   | W  | 4.1  |
| Heat dissipation capacity  | $P_{diss}$ | W  | 0  |
| Operating ambient temperature min.   |            | °C | -25  |
| Operating ambient temperature max.   |            | °C | 60   |
| IEC/EN 61439 design verification   |            |    |  |
| 10.2 Strength of materials and parts   |            |    |  |
| 10.2.2 Corrosion resistance  |            |    |  |
|  |            |    | Meets the product standard's requirements.   |
| 10.2.3.1 Verification of thermal stability of enclosures   |            |    |  |
|  |            |    | Meets the product standard's requirements.   |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat   |            |    |  |
|  |            |    | Meets the product standard's requirements.   |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects |            |    |  |
|  |            |    | Meets the product standard's requirements.   |
| 10.2.4 Resistance to ultra-violet (UV) radiation   |            |    |  |
|  |            |    | Meets the product standard's requirements.   |
| 10.2.5 Lifting   |            |    |  |
|  |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.2.6 Mechanical impact   |            |    |  |
|  |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.2.7 Inscriptions  |            |    |  |
|  |            |    | Meets the product standard's requirements.   |
| 10.3 Degree of protection of ASSEMBLIES  |            |    |  |
|  |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.4 Clearances and creepage distances   |            |    |  |
|  |            |    | Meets the product standard's requirements.   |
| 10.5 Protection against electric shock   |            |    |  |
|  |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.6 Incorporation of switching devices and components   |            |    |  |
|  |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.7 Internal electrical circuits and connections  |            |    |  |
|  |            |    | Is the panel builder's responsibility.   |
| 10.8 Connections for external conductors   |            |    |  |
|  |            |    | Is the panel builder's responsibility.   |
| 10.9 Insulation properties   |            |    |  |
| 10.9.2 Power-frequency electric strength   |            |    |  |
|  |            |    | Is the panel builder's responsibility.   |
| 10.9.3 Impulse withstand voltage   |            |    |  |
|  |            |    | Is the panel builder's responsibility.   |
| 10.9.4 Testing of enclosures made of insulating material   |            |    |  |
|  |            |    | Is the panel builder's responsibility.   |
| 10.10 Temperature rise   |            |    |  |
|  |            |    | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating   |            |    |  |
|  |            |    | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 Electromagnetic compatibility  |            |    |  |
|  |            |    | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 Mechanical function  |            |    |  |
|  |            |    | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |

## Technical data ETIM 7.0

| Low-voltage industrial components (EG000017) / Power contactor, AC switching (EC000066)   |  |    |                  |
|---|--|----|------------------|
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Contactor (LV) / Power contactor, AC switching (ecl@ss10.0.1-27-37-10-03 [AAB718015]) |  |    |                  |
| Rated control supply voltage $U_s$ at AC 50HZ   |  | V  | 110 - 110        |
| Rated control supply voltage $U_s$ at AC 60HZ   |  | V  | 120 - 120        |
| Rated control supply voltage $U_s$ at DC  |  | V  | 0 - 0            |
| Voltage type for actuating  |  |    | AC               |
| Rated operation current $I_e$ at AC-1, 400 V  |  | A  | 80               |
| Rated operation current $I_e$ at AC-3, 400 V  |  | A  | 50               |
| Rated operation power at AC-3, 400 V  |  | kW | 22               |
| Rated operation current $I_e$ at AC-4, 400 V  |  | A  | 21               |
| Rated operation power at AC-4, 400 V  |  | kW | 10               |
| Rated operation power NEMA  |  | kW | 29.8             |
| Modular version   |  |    | No               |
| Number of auxiliary contacts as normally open contact   |  |    | 0                |
| Number of auxiliary contacts as normally closed contact   |  |    | 0                |
| Type of electrical connection of main circuit   |  |    | Screw connection |
| Number of normally closed contacts as main contact  |  |    | 0                |

## Approvals

|                                      |  |
|--------------------------------------|--|
| Product Standards                    | IEC/EN 60947-4-1; UL 60947-4-1; CSA - C22.2 No. 60947-4-1-14; CE marking |
| UL File No.                          | E29096   |
| UL Category Control No.              | NLDX   |
| CSA File No.                         | 012528   |
| CSA Class No.                        | 2411-03, 3211-04   |
| North America Certification          | UL listed, CSA certified   |
| Specially designed for North America | No   |

## Characteristics



- 1: Overload relay
- 2: Suppressor
- 3: Auxiliary contact modules

# DILM1000-XHI(V)11-...



on the side: 2 x DILM1000-XHI(V)11-SI; surface mounting: 1 x DILM150-XHIA11  
 on the side: 2 x DILM1000-XHI(V)11-SA; surface mounting: 1 x DILM150-XHI (2 pole)  
 on the side: 1 x DILM1000-XHI(V)11-SI; surface mounting: 1 x DILM150-XHIA22  
 on the side: 1 x DILM1000-XHI(V)11-SA; surface mounting: 1 x DILM150-XHI (4 pole)






Squirrel-cage motor  
 Operating characteristics  
 Starting: from rest  
 Stopping: after attaining full running speed  
 Electrical characteristics  
 Make: up to 6 x rated motor current  
 Break: up to 1 x rated motor current  
 Utilization category  
 100 % AC-3  
 Typical applications  
 Compressors  
 Lifts  
 Mixers  
 Pumps  
 Escalators  
 Agitators  
 Fans  
 Conveyor belts  
 Centrifuges  
 Hinged flaps  
 Bucket-elevators  
 Air conditioning system  
 General drives in manufacturing and processing machines




Extreme switching duty  
 Squirrel-cage motor  
 Operating characteristics  
 Inching, plugging, reversing  
 Electrical characteristics  
 Make: up to 6 x rated motor current  
 Break: up to 6 x rated motor current  
 Utilization category  
 100 % AC-4  
 Typical applications  
 Printing presses  
 Wire-drawing machines  
 Centrifuges  
 Special drives for manufacturing and processing machines




Switching conditions for non-motor consumers, 3 pole, 4 pole  
 Operating characteristics  
 Non inductive and slightly inductive loads  
 Electrical characteristics  
 Switch on: 1 x rated operational current  
 Switch off: 1 x rated operational current  
 Utilization category  
 100 % AC-1  
 Typical examples of application  
 Electric heat

## Dimensions



Contacteur avec module de contact auxiliaire



Lateral clearance to earthed parts: 6 mm

DILM40...DILM72  
DILMC40...DILMC65  
DILMF40...DILMF65