




RX 8140PS-RX 8161PS Precision Diagonal Cutters with Tapered Head & ESD Safe Handle for hard materials









PRODUCT DETAILS

- PS Series precision oval head diagonal cutters developed according to the scientific ERGO™ process, Oval and robust head
- Designed to get the most precise cut on guidewires, catheter coil wires & cardiology & urology stents
- ERGO™ handles with two-component combination, thermoplastic surface, for comfortable grip, on tough polypropylene core for rigidity
- Micro-bevel cut
- Sharp & fully aligned edges
- High performance alloyed steel
- Phosphate finish
- Numerically controlled machine grinding guarantees edge angle accuracy & contact, increases the tool's reliability & consistency
- Precision induction-hardened edges 63-65 HRC
- Screw joint minimises friction & maximises alignment of cutting edges
- ESD safe handles in two-component synthetic material
- Bio spring limits the tension throughout the working cycle of the tool & can be adjusted to 3 different positions or removed
- Robust head for cutting multiple hard wire stents, guidewires and multiple catheter fillars









PRODUCT ATTRIBUTES







Product: **RX8140PSF**

	Oval		S	A	135.5 mm
A	5.33 in	B	10,5 mm	B	0,41 in
C	10 mm	C	0.39 in	D	6 mm
D	0,24 inch	E	0,8 mm	E	0,03 in
	0.1-1.0 mm		0.01-0.04 in		Micro-Bevel®
	70 g				







Product: **RX8140PS**

	Oval		S	A	135.5 mm
A	5.33 in	B	10,5 mm	B	0,41 in
C	10 mm	C	0.39 in	D	6 mm
D	0,24 inch	E	0,8 mm	E	0,03 in
	0.1-1.0 mm		0.01-0.04 in		Micro-Bevel®
	70 g				







Product: **8154PSP**

	Tapered		M	A	112.5 mm
A	4.43 in	B	12,5 mm	B	0,5 in
C	12,5 mm	C	0.49 in	D	6 mm
D	0,24 inch	E	1,2 mm	E	0,05 in
	0.1-1.25 mm		0.00-0.05 in		Micro-Bevel®
	50 g				







Product: **RX8141PS**

	Oval		S	A	135.5 mm
A	5.33 in	B	10,5 mm	B	0,41 in
C	10 mm	C	0.39 in	D	6 mm
D	0,24 inch	E	0,8 mm	E	0,03 in
	0.1-1.0 mm		0.01-0.04 in		Flush
	70 g				







Product: **RX 8142PS**

	Oval		S	A	135.5 mm
A	5.33 in	B	10,5 mm	B	0,41 in
C	10 mm	C	0.39 in	D	6 mm
D	0,24 inch	E	0,8 mm	E	0,03 in
	0.1-1.0 mm		0.01-0.04 in		Micro-Bevel®
	70 g				







Product: **RX8150PS**

	Oval		M	A	135.5 mm
A	5.33 in	B	12,5 mm	B	0,5 in
C	12,5 mm	C	0.49 in	D	6 mm
D	0,24 inch	E	1,2 mm	E	0,05 in
	0.1-1.0 mm		0.01-0.04 in		Micro-Bevel®
	70 g				

Product: **RX8160BPS**

	Oval		L	A	147.0 mm
A	5.80 in	B	16 mm	B	0,63 in
C	16 mm	C	0.63 in	D	8 mm
D	0,31 inch	E	1,6 mm	E	0,06 in
	0.1-1.0 mm		0.01-0.04 in		Micro-Bevel [®]
	97 g				

Product: **RX 8161PS**

	Oval		L	A	147 mm
A	5.80 in	B	16 mm	B	0,63 in
C	16 mm	C	0.63 in	D	8 mm
D	0,31 inch	E	1,6 mm	E	0,06 in
	0.3-1.6 mm		0.01-0.06 in		Flush
	70 g				