

UM-1 SMD

STANDARD QUARTZ CRYSTAL WITH GULLWING

The UM-1 series provides a broad range of frequencies, and a small profile, packaged in a robust, high reliability enclosure. The UM-1 has an extremely tight tolerance, and excellent mechanical characteristics.

ADVANTAGES

- † Surface Mount
- † Small Package
- † Hermetic Package
- † 350MHz Operating Frequency

APPLICATIONS


- † Telecommunications
- † Base Station
- † Microprocessors
- † 2nd LO
- † Two Way Radio
- † Automotive



ELECTRICAL PERFORMANCE (Ta=25°C)

PARAMETER	MINIMUM	MAXIMUM	UNITS
Center Frequency	8.000	350.000	MHz
Oscillation Mode	Fundamental, 3 rd , 5 th , and 7 th Overtone		
Maximum Series Resistance (See Note 4)	20.0	100.0	Ohms
Frequency Stability at +25°C (See Note 2)	±5.0	±100.0	ppm
Frequency Stability Over Temperature	±5.0	±100.0	ppm
Operating Temperature Range (See Note 2)	-20	+70	°C
Storage Temperature Range	-55	+125	°C
Drive Level	100.0uW Typical		
Seal Method	Resistance Weld		
Shunt Capacitance	1.0	7.0	pF
Motional Capacitance	Customer Request		
Load Capacitance	Series	40.0	pF
Aging per year	±1.0	±5.0	ppm

Parameter	Standard Observed
Mechanical Shock	MIL-STD-202 Method 213, Condition C
Vibration	MIL-STD-202 Method 201, 204, and 214
Hermeticity	MIL-STD-202, Method 112
Solderability	IPC/EIA-STD-002A



- NOTES**
- 1) To order, state part number, options and nominal frequency e.g. L4 100.000MHz
 - 2) Other temperature ranges, stabilities and electrical parameters are readily available upon request.
 - 3) Other specifications available upon request.
 - 4) Depends on frequency

Precision Devices INC. – 8840N. Greenview Drive, Middleton WI 53562, Tel- 1-800-274-XTAL, Fax- 1-608-831-3343, www.pdixtal.com Outside US Phone- 608-381-4445, E-mail- sales@pdixtal.com
 PD (HK) Ltd. – Tel- (852)-2367-3626, Fax- (852)-2646-3122, E-mail- sales@pdixtal.com.hk
 PD (UK) Ltd. – Tel- +44 (0)1223 834444, Fax- +44(0)1223 834589, E-mail- sales@pdixtal.co.uk