

650 V Power SiC Merged PIN Schottky Diode, 10 A



LINKS TO ADDITIONAL RESOURCES








PRIMARY CHARACTERISTICS					
I _{F(AV)} 10 A					
V _R	650 V				
V _F at I _F at 150 °C	1.75 V				
T _J max.	175 °C				
I _R at V _R at 175 °C	5 μΑ				
Q _C (V _R = 400 V)	28 nC				
Package	2L TO-220AC				
Circuit configuration	Single				

FEATURES

 Majority carrier diode using Schottky technology on SiC wide band gap material





- · Virtually no recovery tail and no switching losses
- Temperature invariant switching behavior
- 175 °C maximum operating junction temperature
- MPS structure for high ruggedness to forward current surge events
- Meets JESD 201 class 1A whisker test
- Solder bath temperature 275 °C maximum, 10 s per JESD 22-B106
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

DESCRIPTION / APPLICATIONS

Wide band gap SiC based 650 V Schottky diode, designed for high performance and ruggedness.

Optimum choice for high speed hard switching and efficient operation over a wide temperature range, it is also recommended for all applications suffering from Silicon ultrafast recovery behavior.

Typical applications include AC/DC PFC and DC/DC ultra high frequency output rectification in FBPS and LLC converters.

MECHANICAL DATA

Case: 2L TO-220AC

Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant

Terminals: matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

Mounting torque: 10 in-lbs maximum

ABSOLUTE MAXIMUM RATINGS (T _A = 25 °C unless otherwise specified)					
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Peak repetitive reverse voltage	V_{RRM}		650	V	
Average rectified forward current	I _{F(AV)}	T _C = 125 °C (DC)	10	Α	
DC blocking voltage	V_{DC}		650	V	
Repetitive peak surge current	I _{FRM}	T_C = 25 °C, f = 50 Hz, square wave, DC = 25 %	35	Α	
Non-months and formand arms armed	I _{FSM}	$T_C = 25$ °C, $t_p = 10$ ms, half sine wave	68	Α	
Non-repetitive peak forward surge current		T_C = 110 °C, t_p = 10 ms, half sine wave	60	A	
Danier diametra	P _{tot} (1)	$T_C = 25 ^{\circ}C$	60	W	
Power dissipation		T _C = 110 °C	26		
I ² t value	∫i ² dt	T _C = 25 °C	23	- A ² s	
		T _C = 110 °C	18		
Operating junction and storage temperatures	T _J ⁽²⁾ , T _{Stg}		-55 to +175	°C	

Notes

⁽¹⁾ Based on maximum Rth

⁽²⁾ The heat generated must be less than the thermal conductivity from junction-to-ambient: dP_D/dT_J < 1/R_{0JA}



ELECTRICAL SPECIFICATIONS (T _J = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
		I _F = 10 A	-	1.50	1.80	
Forward voltage	V_{F}	I _F = 10 A, T _J = 150 °C	-	1.75	1.95	V
		I _F = 10 A, T _J = 175 °C	-	1.85	-	
		$V_R = V_R$ rated	-	-	55	
Reverse leakage current	I _R	V _R = V _R rated, T _J = 150 °C	-	-	125	μΑ
		V _R = V _R rated, T _J = 175 °C	-	5	-	
Total capacitance	С	V _R = 1 V, f = 1 MHz	-	430	-	pF
		V _R = 400 V, f = 1 MHz	-	45	-	PΓ
Total capacitive charge	Q _C	V _R = 400 V, f = 1 MHz	-	28	-	nC

THERMAL - MECHANICAL SPECIFICATIONS (T _A = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Thermal resistance, junction-to-case	R _{thJC}		-	1.8	2.5	°C/W
Marking device				C10E	T07T	




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Non-Repetitive Peak Forward Surge Current vs. Pulse Duration (Square Wave)




Fig. 5 - Typical Thermal Impedance Z_{thJC} Characteristics




Fig. 6 - Maximum Allowable Case Temperature vs. Average Forward Current




Fig. 7 - Forward Power Loss Characteristics




Fig. 8 - Typical Capacitive Energy vs. Reverse Voltage





Fig. 9 - Typical Capacitive Charge vs. Reverse Voltage



ORDERING INFORMATION TABLE

Device code



1 - Vishay Semiconductors product

C = SiC diode

Current rating (10 = 10 A)

- E = single diode

5 - Package TO-220

6 - Voltage rating: (07 = 650 V)

7 - T = true 2 pin

8 - Environmental digit:

-M3 = halogen-free, RoHS-compliant, and termination lead (Pb)-free

ORDERING INFORMATION				
PREFERRED P/N	BASE QUANTITY	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION	
VS-C10ET07T-M3	50/tube	1000	Antistatic plastic tubes	

LINKS TO RELATED DOCUMENTS			
Dimensions <u>www.vishay.com/doc?96069</u>			
Part marking information	www.vishay.com/doc?95391		
SPICE model	www.vishay.com/doc?96832		



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.