

DAISY-MINI-M

~30° wide beam

TECHNICAL SPECIFICATIONS:

Dimensions	279.5 x 21.0 mm
Height	13.3 mm
Fastening	pin, screw, snaps
ROHS compliant	yes ⓘ


MATERIAL SPECIFICATIONS:

Component	Type	Material	Colour	Finish
F17029_DAISY-MINI-M	Linear lens	PMMA	clear	
F17028_DAISY-MINI-SHD	Shade	PC	black	gloss
F17033_DAISY-MINI-SHD-WHT	Shade	PC	white	gloss
F17034_DAISY-MINI-SHD-MATT	Shade	PC	black	matt
F17465_DAISY-MINI-SHD-WHT-MATT	Shade	PC	white	matt
F17666_DAISY-MINI-SHD-MET	Shade	PC	metal	gloss
F17667_DAISY-MINI-SHD-MET-MATT	Shade	PC	metal	matt


ORDERING INFORMATION:

Quantities for one set:

Linear lens	1
Shade	1








Component		Qty in box	MOQ	MPQ	Box weight (kg)
F17029_DAISY-MINI-M	Linear lens	252	252	12	5.8
» Box size: 398 x 298 x 265 mm					
F17033_DAISY-MINI-SHD-WHT	Shade	252	252	4	5.9
» Box size: 398 x 298 x 265 mm					
F17667_DAISY-MINI-SHD-MET-MATT	Shade	252	252	4	6.2
» Box size: 398 x 298 x 265 mm					
F17034_DAISY-MINI-SHD-MATT	Shade	252	252	4	6.1
» Box size: 398 x 298 x 265 mm					
F17028_DAISY-MINI-SHD	Shade	252	252	4	5.9
» Box size: 398 x 298 x 265 mm					
F17465_DAISY-MINI-SHD-WHT-MATT	Shade	252	252	4	6.2
» Box size: 398 x 298 x 265 mm					
F17666_DAISY-MINI-SHD-MET	Shade	252	252	4	5.9
» Box size: 398 x 298 x 265 mm					



See also our general installation guide: www.ledil.com/installation_guide





PHOTOMETRIC DATA (MEASURED):

 <p> LED Opticus Daisy Mini M L28W2 FWHM / FWTM 34.0° / 68.0° Efficiency 73 % Peak intensity 1.6 cd/lm LEDs/each optic 1 Light colour White Required components: F17034_DAISSY-MINI-SHD-MATT </p>		
 <i>Your solutions</i> <p> LED LinLED 280x20mm 1100lm 8x0 2C 42V Opt G1 FWHM / FWTM 58.0° / 87.0° Efficiency 59 % Peak intensity 0.6 cd/lm LEDs/each optic 2 Light colour White Required components: F17028_DAISSY-MINI-SHD </p>		

PHOTOMETRIC DATA (SIMULATED):

<p>CREE LED</p> <p>LED: XQ-E HI FWHM / FWTM: 30.0° / 72.0° Efficiency: 80 % Peak intensity: 1.8 cd/lm LEDs/each optic: 1 Light colour: White Required components: F17028_DAISSY-MINI-SHD</p>	
<p>CREE LED</p> <p>LED: XQ-E HI FWHM / FWTM: 34.0° / 75.0° Efficiency: 88 % Peak intensity: 1.8 cd/lm LEDs/each optic: 1 Light colour: White Required components: F17666_DAISSY-MINI-SHD-MET</p>	
<p>CREE LED</p> <p>LED: XQ-E HI FWHM / FWTM: 32.0° / 72.0° Efficiency: 78 % Peak intensity: 1.8 cd/lm LEDs/each optic: 1 Light colour: White Required components: F17034_DAISSY-MINI-SHD-MATT</p>	
<p>NICHIA</p> <p>LED: NCSxE17A FWHM / FWTM: 30.0° / 62.0° Efficiency: 87 % Peak intensity: 2.4 cd/lm LEDs/each optic: 1 Light colour: White Required components: F17028_DAISSY-MINI-SHD</p>	


PHOTOMETRIC DATA (SIMULATED):

<p>NICHIA</p> <p>LED NFSWE11A FWHM / FWTM 26.0° / 55.0° Efficiency 89 % Peak intensity 3 cd/lm LEDs/each optic 1 Light colour White Required components: F17028_DAISSY-MINI-SHD</p>	
<p>NICHIA</p> <p>LED NFSWE11A FWHM / FWTM 34.0° / 68.0° Efficiency 79 % Peak intensity 1.7 cd/lm LEDs/each optic 4 Light colour White Required components: F17028_DAISSY-MINI-SHD</p>	
<p>SAMSUNG</p> <p>LED LM28xB Series FWHM / FWTM 32.8° / 68.0° Efficiency 82 % Peak intensity 2 cd/lm LEDs/each optic 1 Light colour White Required components: F17028_DAISSY-MINI-SHD</p>	
<p>SAMSUNG</p> <p>LED LM302D FWHM / FWTM 28.0° / 62.0° Efficiency 87 % Peak intensity 2.5 cd/lm LEDs/each optic 1 Light colour White Required components: F17028_DAISSY-MINI-SHD</p>	

PHOTOMETRIC DATA (SIMULATED):

SAMSUNG

LED	LM302D
FWHM / FWTM	28.0° / 62.0°
Efficiency	91 %
Peak intensity	2.5 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	
	F17465_DAISY-MINI-SHD-WHT-MATT



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)