




Visual Signals XENON

BEACONS



Industrial Xenon Beacons > X125 DIN Base Series

Product overview

The X125 DIN Base Series utilises a discharge capacitor and converter circuit to ignite xenon gas inside a tube, resulting in a brilliant flash of light. Xenon gas ignites virtually instantaneously so maximum brightness is obtained immediately. The design of the X125 DIN Base

Series ensures a 360 degree light output. Xenon beacons are one of the most efficient, effective and brightest visual signals available. The Audible XA125 offers 2.7 joules of flash energy and two piezo sounders located in the base of the unit and offers a choice of either continuous tone or a pulsed tone that can operate independently of the beacon. A M12 sealing grommet in the base for cable entry and termination inside the enclosure.

Features

- Continuously rated
- Suitable for surface or wall mounting
- Combined audible & visual option available - XA125 only
- Optional wall bracket & protective guard available - see accessory page
- 360° visibility
- 3 point fix external
- IP65

Material

- UV Stable Polycarbonate Lens
- UV Stable ABS Plastic Base

Code No:	Voltage:	Light Source:	Current:
X125-64	10-100v Dc --- 20-72v Ac ~	Xenon 2.0 J	130 mA •
X125-62	115v Ac ~	Xenon 2.3 J	30 mA
X125-63	230v Ac ~	Xenon 2.7 J	21 mA
Audible Option			
XA125-63 NEW	230v Ac ~	Xenon 2.7 J	120mA ••

• Pre-set at 24v Dc ---

•• With both audible & visual signals operating at the same time



Kg 0.25 X125
0.34 XA125

50/60 Hz

°C -25+55

IP 65

FPM 60

INDUSTRIAL

APPROVED AND CONFORMITIES



ADD THE FOLLOWING LENS CODES TO THE PRODUCT WHEN ORDERING

01 02 03 04 05

dB 90 XA125