
DISCRETE SEMICONDUCTORS



Product specification Supersedes data of 2003 Nov 04 2004 Apr 15



PEMD9; PUMD9

FEATURES

- Built-in bias resistors
- Simplifies circuit design
- Reduces component count
- Reduces pick and place costs.

APPLICATIONS

- Low current peripheral driver
- Replacement of general purpose transistors in digital applications
- Control of IC inputs.

DESCRIPTION

NPN/PNP resistor-equipped transistors in a SOT666 plastic package.

PRODUCT OVERVIEW

TYPE NUMBER	PACKAGE		MARKING CODE	PNP/PNP	NPN/NPN	
	PHILIPS	EIAJ		COMPLEMENT	COMPLEMENT	
PEMD9	SOT666	_	D9	PEMB9	PEMH9	
PUMD9	SOT363	SC-88	D*9 ⁽¹⁾	PUMB9	PUMH9	

Note

- 1. * = p: Made in Hong Kong.
 - * = t: Made in Malaysia.
 - * = W: Made in China.

SIMPLIFIED OUTLINE, SYMBOL AND PINNING

TYPE NUMBER	SIMPLIFIED OUTLINE AND SYMBOL		PINNING		
ITPE NUMBER	SIMPLIFIED OUTLINE AND STMBOL	PIN	DESCRIPTION		
PEMD9; PUMD9	$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	1 2 3 4 5 6	emitter TR1 base TR1 collector TR2 emitter TR2 base TR2 collector TR1		

QUICK REFERENCE DATA

SYMBOL	PARAMETER	TYP.	MAX.	UNIT
V _{CEO}	collector-emitter voltage	-	50	V
lo	output current (DC)	_	100	mA
TR1	NPN	_	-	-
TR2	PNP	_	_	_
R1	bias resistor	10	_	kΩ
R2	bias resistor	47	-	kΩ

PEMD9; PUMD9

ORDERING INFORMATION

TYPE NUMBER		PACKAGE		
ITPE NOMBER	NAME	DESCRIPTION	VERSION	
PEMD9	MD9 – plastic surface mounted package; 6 leads S		SOT666	
PUMD9	 plastic surface mounted package; 6 leads SC 		SOT363	

LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
Per transistor;	for the PNP transistor with negative	e polarity			-
V _{CBO}	collector-base voltage	open emitter	_	50	V
V _{CEO}	collector-emitter voltage	open base	_	50	V
V _{EBO}	emitter-base voltage	open collector	_	10	V
VI	input voltage TR1				
	positive		_	+40	V
	negative		_	-6	V
VI	input voltage TR2				
	positive		_	+6	V
	negative		_	-40	V
lo	output current (DC)		_	100	mA
I _{CM}	peak collector current		_	100	mA
P _{tot}	total power dissipation	$T_{amb} \le 25 \ ^{\circ}C;$	_	-	
	SOT363	note 1	_	200	mW
	SOT666	notes 1 and 2	_	200	mW
T _{stg} storage temperature			-65	+150	°C
Tj	junction temperature		_	150	°C
T _{amb}	operating ambient temperature		-65	+150	°C
Per device					-
P _{tot}	total power dissipation	T _{amb} ≤ 25 °C;	_	-	
	SOT363	note 1	_	300	mW
	SOT666	notes 1 and 2	_	300	mW

Notes

1. Transistor mounted on an FR4 printed-circuit board, single-sided copper, standard footprint.

2. Reflow soldering is the only recommended soldering method.

PEMD9; PUMD9

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
Per transi	stor			
R _{th(j-a)}	thermal resistance from junction to ambient			
	SOT363	note 1	625	K/W
SOT666 notes 1 and		notes 1 and 2	625	K/W
Per device	Э			
R _{th(j-a)}	thermal resistance from junction to ambient			
	SOT363	note 1	416	K/W
	SOT666	notes 1 and 2	416	K/W

Notes

1. Transistor mounted on an FR4 printed-circuit board, single-sided copper, standard footprint.

2. Reflow soldering is the only recommended soldering method.


PEMD9; PUMD9

CHARACTERISTICS

 T_{amb} = 25 °C; unless otherwise specified.


SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT	
Per transis	Per transistor; for the PNP transistor with negative polarity						
I _{CBO}	collector-base cut-off current	$V_{CB} = 50 \text{ V}; I_E = 0 \text{ A}$	-	-	100	nA	
I _{CEO}	collector-emitter cut-off current	V _{CE} = 30 V; I _B = 0 A	-	-	1	μA	
		$V_{CE} = 30 \text{ V}; \text{ I}_{B} = 0 \text{ A}; \text{ T}_{j} = 150 ^{\circ}\text{C}$	-	-	50	μA	
I _{EBO}	emitter-base cut-off current	$V_{EB} = 5 \text{ V}; \text{ I}_{C} = 0 \text{ A}$	-	-	150	μA	
h _{FE}	DC current gain	$V_{CE} = 5 V; I_C = 5 mA$	100	-	_		
V _{CEsat}	collector-emitter saturation voltage	$I_{\rm C} = 5 \text{ mA}; I_{\rm B} = 0.25 \text{ mA}$	_	-	100	mV	
V _{i(off)}	input-off voltage	$V_{CE} = 5 \text{ V}; \text{ I}_{C} = 100 \mu\text{A}$	-	0.7	0.5	V	
V _{i(on)}	input-on voltage	$V_{CE} = 0.3 \text{ V}; I_{C} = 1 \text{ mA}$	1.4	0.8	_	V	
R1	input resistor		7	10	13	kΩ	
R2 R1	resistor ratio		3.7	4.7	5.7		
C _c	collector capacitance						
	TR1 (NPN)	$V_{CB} = 10 \text{ V}; I_E = i_e = 0 \text{ A};$ f = 1 MHz	-	-	2.5	pF	
	TR2 (PNP)		-	-	3	pF	

PACKAGE OUTLINES



PEMD9; PUMD9

PEMD9; PUMD9



PEMD9; PUMD9

DATA SHEET STATUS

LEVEL	DATA SHEET STATUS ⁽¹⁾	PRODUCT STATUS ⁽²⁾⁽³⁾	DEFINITION
I	Objective data	Development	This data sheet contains data from the objective specification for product development. Philips Semiconductors reserves the right to change the specification in any manner without notice.
II	Preliminary data	Qualification	This data sheet contains data from the preliminary specification. Supplementary data will be published at a later date. Philips Semiconductors reserves the right to change the specification without notice, in order to improve the design and supply the best possible product.
	Product data	Production	This data sheet contains data from the product specification. Philips Semiconductors reserves the right to make changes at any time in order to improve the design, manufacturing and supply. Relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN).

Notes

- 1. Please consult the most recently issued data sheet before initiating or completing a design.
- 2. The product status of the device(s) described in this data sheet may have changed since this data sheet was published. The latest information is available on the Internet at URL http://www.semiconductors.philips.com.
- 3. For data sheets describing multiple type numbers, the highest-level product status determines the data sheet status.

DEFINITIONS

Short-form specification — The data in a short-form specification is extracted from a full data sheet with the same type number and title. For detailed information see the relevant data sheet or data handbook.

Limiting values definition — Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 60134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

Application information — Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors make no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

DISCLAIMERS

Life support applications — These products are not designed for use in life support appliances, devices, or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips Semiconductors customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors for any damages resulting from such application.

Right to make changes — Philips Semiconductors reserves the right to make changes in the products including circuits, standard cells, and/or software described or contained herein in order to improve design and/or performance. When the product is in full production (status 'Production'), relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN). Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no licence or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified.

Philips Semiconductors – a worldwide company

Contact information

For additional information please visit http://www.semiconductors.philips.com. Fax: +31 40 27 24825 For sales offices addresses send e-mail to: sales.addresses@www.semiconductors.philips.com.

© Koninklijke Philips Electronics N.V. 2004

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

R75/05/pp9

Date of release: 2004 Apr 15

Document order number: 9397 750 13098

SCA76

Let's make things better.





Philips Semiconductors