

Data Sheet | Item Number: 206-1204

Variocrimp 4 crimping tool; for insulated and uninsulated ferrules; Crimping range: 0.25 to 4.0 mm²

<https://www.wago.com/206-1204>



Notes

Note

Application Notes

- With "Variocrimp 4," the built-in crimping pressure control automatically adjusts force to the conductor cross-section used.
- Only one crimping station is needed to handle the specified conductor range.
- Uniform, compact crimping all four sides for high conductor retention.
- No need to center the ferrules into the terminals.
- Crimping can be performed from either side (for left- or right-handed users).
- Built-in ratchet mechanism ensures gas-tight crimp connection.
- Crimping tools open automatically after crimping operation is complete.
- Ergonomically designed handles.

What is a "gas-tight" connection?

In a gas-tight connection, the conductor and the ferrule are compressed, eliminating all spaces. Under normal atmospheric conditions, neither a liquid nor gaseous medium can penetrate the crimped connection.

Oxidation between crimped single conductors is prevented, virtually eliminating the possibility of any increase in the crimped connection's resistance. In some exceptional cases, minute, isolated spaces may be present. However, these instances can be considered as closed off due to the twisted conductor.

Inadequate crimping can allow the conductor to be pulled out of the connection. Hollow spaces also remain, permitting oxidation formation and an increase in contact resistance.

Elevated resistance is detrimental for both signal transmission (signal flow is damped) and power transmission, resulting in power loss and contact heating (risk of fire).

Crimping tools with built-in ratchets are recommended (e.g., **WAGO Crimping Tools**). These tools open automatically after the crimping operation is complete. Space-saving crimping from all four sides is ideal for spring clamp termination.

Ferruled conductor cross-sections specified for WAGO products are based on this crimping method.

Physical data

Width	75 mm / 2.953 inches
Depth	200 mm / 7.874 inches

Material data

Fire load	0 MJ
Weight	496.6 g

Commercial data

ETIM 8.0	EC000168
ETIM 7.0	EC000168
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143868594
Customs tariff number	8203200000

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 206-1204 

1 Compatible Products

1.1 Optional Accessories

1.1.1 Tool

1.1.1.1 Crimping tool



[Item No.: 206-1205](#)
Spring clamp; large



[Item No.: 206-1206](#)
Spring clamp; small

Installation Notes



Insert the ferruled conductor into the crimping station.



Squeeze handles until ratchet mechanism is released.