

0805L Series

Surface Mount



Description

The 0805L Series PTC provides surface mount overcurrent protection for applications where space is at a premium and resettable protection is desired.

Features & Benefits

- RoHS compliant, lead-free and halogen-free
- Fast response to fault currents
- Compact design saves board space
- Low resistance
- Low-profile
- Compatible with high temperature solders

Additional Information



Resources



Accessories



Samples

Applications

- USB peripherals
- Disk drives
- CD-ROMs
- Plug and play protection for motherboards and peripherals
- Mobile phones - battery and port protection
- Disk drives
- PDAs / digital cameras
- Game console port protection

Agency Approvals

| Agency | Agency File Number |
|--------|--------------------|
| | E183209 |
| | R50119118 |

Electrical Characteristics

| Part Number | Marking | I_{hold} (A) | I_{trip} (A) | V_{max} (Vdc) | I_{max} (A) | P_d typ. (W) | Maximum Time To Trip | | Resistance | | Agency Approvals | |
|-----------------------|---------|----------------|----------------|-----------------|---------------|----------------|----------------------|-------------|------------------------|-------------------------|------------------|---------|
| | | | | | | | Current (A) | Time (Sec.) | R_{min} (Ω) | R_{1max} (Ω) | | |
| 0805L002 | ▲ | 0.02 | 0.06 | 63 | 40 | 0.5 | 0.10 | 1.50 | 12.000 | 70.000 | Pending | Pending |
| 0805L005/30 | f3 | 0.05 | 0.15 | 30 | 40 | 0.50 | 0.25 | 1.50 | 3.600 | 20.000 | X | X |
| 0805L010 | A | 0.10 | 0.30 | 15 | 100 | 0.5 | 0.50 | 1.50 | 1.000 | 6.000 | X | X |
| 0805L010/24 | J | 0.10 | 0.30 | 24 | 100 | 0.5 | 0.50 | 1.50 | 1.500 | 6.000 | X | X |
| 0805L020 | C | 0.20 | 0.50 | 9 | 100 | 0.5 | 8.00 | 0.02 | 0.650 | 3.500 | X | X |
| 0805L020/16 | C1 | 0.20 | 0.50 | 16 | 100 | 1.2 | 8.00 | 0.50 | 0.500 | 3.500 | X | Pending |
| 0805L020/24 | C2 | 0.20 | 0.50 | 24 | 100 | 1.2 | 8.00 | 0.50 | 0.500 | 3.500 | X | Pending |
| 0805L035 | E | 0.35 | 0.75 | 6 | 100 | 0.5 | 8.00 | 0.10 | 0.250 | 1.200 | X | X |
| 0805L050 ¹ | F | 0.50 | 1.00 | 6 | 100 | 0.5 | 8.00 | 0.10 | 0.150 | 0.850 | X | X |
| 0805L075 | G | 0.75 | 1.50 | 6 | 40 | 0.6 | 8.00 | 0.20 | 0.090 | 0.350 | X | X |
| 0805L100 | N | 1.00 | 1.95 | 6 | 40 | 0.6 | 8.00 | 0.30 | 0.060 | 0.210 | X | X |
| 0805L110 | H | 1.10 | 2.00 | 6 | 100 | 0.8 | 8.00 | 0.10 | 0.050 | 0.160 | X | X |

I_{hold} = Hold current: maximum current device will pass without tripping in 20°C still air.

I_{trip} = Trip current: minimum current at which the device will trip in 20°C still air.

V_{max} = Maximum voltage device can withstand without damage at rated current (I_{max})

I_{max} = Maximum fault current device can withstand without damage at rated voltage (V_{max})

P_d = Power dissipated from device when in the tripped state at 20°C still air.

R_{min} = Minimum resistance of device in initial (un-soldered) state.

R_{typ} = Typical resistance of device in initial (un-soldered) state.

R_{1max} = Maximum resistance of device at 20°C measured one hour after tripping or reflow soldering of 260°C for 20 sec.

Caution: Operation beyond the specified rating may result in damage and possible arcing and flame.

¹ Typical rating was selected to represent the whole series for AEC-Q200 test.

0805L Series


Surface Mount

Temperature Rerating

| Part Number | Ambient Operation Temperature | | | | | | | | |
|-------------|-------------------------------|-------|-------|-------|-------|-------|-------|-------|-------|
| | -40°C | -20°C | 0°C | 20°C | 40°C | 50°C | 60°C | 70°C | 85°C |
| 0805L002 | 0.030 | 0.027 | 0.024 | 0.020 | 0.017 | 0.016 | 0.014 | 0.012 | 0.010 |
| 0805L005/30 | 0.077 | 0.069 | 0.061 | 0.050 | 0.042 | 0.038 | 0.033 | 0.028 | 0.021 |
| 0805L010 | 0.14 | 0.12 | 0.11 | 0.10 | 0.08 | 0.07 | 0.06 | 0.05 | 0.03 |
| 0805L010/24 | 0.14 | 0.12 | 0.11 | 0.10 | 0.08 | 0.07 | 0.06 | 0.05 | 0.03 |
| 0805L020 | 0.28 | 0.25 | 0.23 | 0.20 | 0.17 | 0.14 | 0.12 | 0.10 | 0.07 |
| 0805L020/16 | 0.30 | 0.27 | 0.24 | 0.20 | 0.17 | 0.16 | 0.14 | 0.13 | 0.10 |
| 0805L020/24 | 0.30 | 0.27 | 0.24 | 0.20 | 0.17 | 0.16 | 0.14 | 0.13 | 0.10 |
| 0805L035 | 0.47 | 0.44 | 0.39 | 0.35 | 0.30 | 0.27 | 0.24 | 0.20 | 0.14 |
| 0805L050 | 0.68 | 0.62 | 0.55 | 0.50 | 0.40 | 0.37 | 0.33 | 0.29 | 0.23 |
| 0805L075 | 1.00 | 0.90 | 0.79 | 0.75 | 0.63 | 0.57 | 0.53 | 0.41 | 0.34 |
| 0805L100 | 1.35 | 1.25 | 1.10 | 1.00 | 0.82 | 0.74 | 0.65 | 0.55 | 0.42 |
| 0805L110 | 1.45 | 1.35 | 1.20 | 1.10 | 0.92 | 0.84 | 0.75 | 0.65 | 0.52 |


Notes: The temperature rerating data is only for reference, please contact Littelfuse technical support for detail temperature rerating information.

Average Time Current Curves



The average time current curves and Temperature Rerating curve performance is affected by a number of variables, and these curves provided as guidance only. Customer must verify the performance in their application.

Temperature Rerating Curve




Note: Typical Temperature rerating curve, refer to table for derating data

0805L Series

Surface Mount

Soldering Parameters

| | | |
|---|--|-------------------------|
| Profile Feature | | Pb-Free Assembly |
| Average Ramp-Up Rate ($T_{S(max)}$ to T_p) | | 3°C/second max |
| Pre Heat: | Temperature Min ($T_{s(min)}$) | 150°C |
| | Temperature Max ($T_{s(max)}$) | 200°C |
| | Time (Min to Max) (t_s) | 60 – 180 secs |
| Time Maintained Above: | Temperature (T_L) | 217°C |
| | Temperature (t_t) | 60 – 150 seconds |
| Peak / Classification Temperature (T_p) | | 260 ^{+0/-5} °C |
| Time within 5°C of actual peak Temperature (t_p) | | 20 – 40 seconds |
| Ramp-down Rate | | 6°C/second max |
| Time 25°C to peak Temperature (T_p) | | 8 minutes Max. |



Physical Specifications

| | |
|---------------------------|--|
| Terminal Material | Solder-Plated Copper (Solder Material: Matte Tin (Sn)) |
| Lead Solderability | Meets EIA Specification RS186-9E, ANSI/J-STD-002, Category 3 |


Environmental Specifications

| | |
|--|---|
| Operating Temperature | -40°C to +85°C |
| Maximum Device Surface Temperature in Tripped State | 125°C |
| Passive Aging | +85°C, 1000 hours -/+5% typical resistance change |
| Humidity Aging | +85°C, 85%, R.H., 1000 hours -/+5% typical resistance change |
| Thermal Shock | MIL-STD-202, Method 107 +85°C/-40°C 20 times -30% typical resistance change |
| Solvent Resistance | MIL-STD-202, Method 215 No change |
| Vibration | MIL-STD-883, Method 2007, Condition A No change |
| Moisture Sensitivity Level | Level 1, J-STD-020 |

0805L Series


Surface Mount

Dimensions



| Part Number | A | | | | B | | | | C | | | | D | | | | E | | | |
|-------------|--------|------|------|------|--------|------|------|------|--------|------|------|------|--------|------|------|------|--------|------|------|------|
| | Inches | | mm | | Inches | | mm | | Inches | | mm | | Inches | | mm | | Inches | | mm | |
| | Min | Max | Min | Max | Min | Max | Min | Max | Min | Max | Min | Max | Min | Max | Min | Max | Min | Max | Min | Max |
| 0805L002 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.03 | 0.05 | 0.75 | 1.25 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L005/30 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.03 | 0.05 | 0.75 | 1.25 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L010 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.02 | 0.04 | 0.55 | 1.00 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L010/24 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.02 | 0.04 | 0.55 | 1.00 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L020 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.02 | 0.04 | 0.55 | 1.00 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L020/16 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.02 | 0.03 | 0.45 | 0.75 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L020/24 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.02 | 0.03 | 0.45 | 0.75 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L035 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.02 | 0.03 | 0.45 | 0.75 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L050 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.03 | 0.05 | 0.75 | 1.25 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L075 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.03 | 0.05 | 0.75 | 1.25 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L100 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.02 | 0.07 | 0.50 | 1.80 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |
| 0805L110 | 0.08 | 0.09 | 2.00 | 2.20 | 0.05 | 0.06 | 1.20 | 1.50 | 0.03 | 0.06 | 0.80 | 1.40 | 0.01 | 0.02 | 0.20 | 0.55 | 0.002 | 0.02 | 0.05 | 0.45 |

Part Ordering Number System



Packaging

| Part Number | Ordering Number | Halogen Free | I _{hold} (A) | I _{hold} Code | Packaging Option | Quantity | Quantity & Packaging Codes |
|-------------|-----------------|--------------|-----------------------|------------------------|------------------|----------|----------------------------|
| 0805L002 | 0805L002YR | Yes | 0.02 | 002 | Tape and Reel | 4000 | YR |
| 0805L005/30 | 0805L005/30YR | Yes | 0.05 | 005 | Tape and Reel | 4000 | YR |
| 0805L010 | 0805L010YR | Yes | 0.10 | 010 | Tape and Reel | 4000 | YR |
| 0805L010/24 | 0805L010/24YR | Yes | 0.10 | 010 | Tape and Reel | 4000 | YR |
| 0805L020 | 0805L020YR | Yes | 0.20 | 020 | Tape and Reel | 4000 | YR |
| 0805L020/16 | 0805L020/16YR | Yes | 0.20 | 020 | Tape and Reel | 4000 | YR |
| 0805L020/24 | 0805L020/24YR | Yes | 0.20 | 020 | Tape and Reel | 4000 | YR |
| 0805L035 | 0805L035YR | Yes | 0.35 | 035 | Tape and Reel | 4000 | YR |
| 0805L050 | 0805L050WR | Yes | 0.50 | 050 | Tape and Reel | 3000 | WR |
| 0805L075 | 0805L075WR | Yes | 0.75 | 075 | Tape and Reel | 3000 | WR |
| 0805L100 | 0805L100WR | Yes | 1.00 | 100 | Tape and Reel | 3000 | WR |
| 0805L110 | 0805L110WR | Yes | 1.10 | 110 | Tape and Reel | 3000 | WR |

0805L Series


Surface Mount

Tape and Reel Specifications


| TAPE SPECIFICATIONS: EIA-481-1 (mm) | | | |
|-------------------------------------|---|---|-------------|
| | 0805L010 0805L020 0805L035 0805L010/24 0805L020/16 0805L020/24 | 0805L002 0805L050 0805L075 0805L100 0805L005/30 | 0805L110 |
| W | 8.00+/-0.10 | 8.00+/-0.30 | 8.00+/-0.30 |
| F | 3.50+/-0.05 | 3.50+/-0.05 | 3.50+/-0.05 |
| E ₁ | 1.75+/-0.10 | 1.75+/-0.10 | 1.75+/-0.10 |
| D ₀ | 1.55+/-0.05 | 1.55+/-0.05 | 1.55+/-0.05 |
| D ₁ | 1.00 (min) | 1.00+/-0.10 | 1.00+/-0.10 |
| P ₀ | 4.00+/-0.08 | 4.00+/-0.10 | 4.00+/-0.10 |
| P ₁ | 4.00+/-0.10 | 4.00+/-0.10 | 4.00+/-0.10 |
| P ₂ | 2.00+/-0.05 | 2.00+/-0.05 | 2.00+/-0.05 |
| A ₀ | 1.60+/-0.10 | 1.65+/-0.10 | 1.65+/-0.10 |
| B ₀ | 2.30+/-0.10 | 2.35+/-0.10 | 2.35+/-0.10 |
| T | 0.25+/-0.10 | 0.20+/-0.10 | 0.25+/-0.10 |
| K ₀ | 0.90+/-0.10 | 1.05+/-0.10 | 1.50+/-0.10 |
| Leader min. | 390 | 390 | 390 |
| Trailer min. | 160 | 160 | 160 |

| REEL DIMENSIONS: EIA-481-1 (mm) | |
|------------------------------------|-------------|
| C | Ø178+/-1.0 |
| D | ø60.2+/-0.5 |
| H | 11.0+/-0.5 |
| W | 9.0+/-1.5 |

Tape Specifications



Reel Specifications



Warning

- Users should independently evaluate the suitability of and test each product selected for their own application.
- Operation beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.
- These devices are intended for protection against damage caused by occasional overcurrent or overtemperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.
- Contamination of the PPTC material with certain silicone-based oils or some aggressive solvents can adversely impact the performance of the devices.
- Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.
- PPTC devices are not recommended for installation in applications where the device is constrained such that its PTC properties are inhibited, for example in rigid potting materials or in rigid housings, which lack adequate clearance to accommodate device expansion.
- Operation in circuits with a large inductance can generate a circuit voltage (Ldi/dt) above the rated voltage of the device.

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.