VY1 Series

RoHS

HALOGEN



www.vishay.com

Vishay BCcomponents

AC Line Rated Ceramic Disc Capacitors Class X1, 760 V_{AC} , Class Y1, 500 V_{AC}



QUICK REFERENCE DATA					
DESCRIPTION	VALUE				
Ceramic Class	1 2				
Ceramic Dielectric	U2J U2J		Y5S, Y5U	Y5S, Y5U	
Voltage (V _{AC})	500	760	500	760	
Min. Capacitance (pF)	10 33		3		
Max. Capacitance (pF)	22 4700		00		
Mounting	Radial				

OPERATING TEMPERATURE RANGE

- 40 °C to + 125 °C

TEMPERATURE CHARACTERISTICS

See Ordering Information table

CLIMATIC CATEGORY

40/125/21 according to EN 60068-1

COATING

According to UL 94 V-0 Epoxy resin, isolating, flame retardant

APPROVALS

IEC 60384-14.3 UL 60384-14 DIN EN 60384-14 CSA E60384-1:03, CSA E60384-14:09

PACKAGING

Bulk, tape and reel, taped ammopack

FEATURES

- Complying with IEC 60384-14, 3rd edition
- High reliability
- Vertical (inline) kinked or straight leads
- Singlelayer AC Disc capacitors
- Material categorization: For definitions of compliance please see <u>www.vishav.com/doc?99912</u>

v.vishay.com/doc?99912

- APPLICATIONS
- X1, Y1 according to IEC 60384-14.3
- Across-the-line
- Line by-pass
- Antenna coupling

DESIGN

The capacitors consist of a ceramic disc both sides of which are silver-plated. Connection leads are made of tinned copper having a diameter of 0.6 mm.

The capacitors may be supplied with vertical (inline) kinked leads having a lead spacing of 10.0 mm and 12.5 mm. Encapsulation is made of flammable resistant epoxy resin in accordance with "UL 94 V-0".

CAPACITANCE RANGE

10 pF to 4700 pF

RATED VOLTAGE UR

IEC 60384-14.3: (X1): 760 V_{AC}, 50 Hz (Y1): 500 V_{AC}, 50 Hz

TEST VOLTAGE

Component test (100 %): 4000 V_{AC}, 50 Hz, 2 s Random sampling test (destructive test): 4000 V_{AC}, 50 Hz, 60 s Voltage proof of coating (destructive test): 4000 V_{AC}, 50 Hz, 60 s

INSULATION RESISTANCE

10 000 $M\Omega$ minimum

TOLERANCE OF CAPACITANCE

± 20 % (code M); ± 10 % (code K)

DISSIPATION FACTOR

2.5 % maximum

1 For technical questions, contact: <u>cdc@vishay.com</u>


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT



'ISHAY www.vishay.com

Vishay BCcomponents

DIMENSIONS



		BODY	BODY	LEAD	CLEAR	TEXT CODE		
С (pF)	TOL. (%)	TEMP. COEFFICIENT	DIAMETER D _{MAX.}	THICKNESS SPACING T _{MAX.} F		^{rH} DIGIT: AMMO; 3 = BULK ⁽¹⁾		
			(mm)	(mm)	(mm)	RoHS COMPLIANT	RoHS AND HALOGEN-FREE	
10						VY1100K31U2JQ6*V0	VY1100K31U2JG6*V0	
15		U2J (N750)				VY1150K31U2JQ6*V0	VY1150K31U2JG6*V0	
22						VY1220K31U2JQ6*V0	VY1220K31U2JG6*V0	
33						VY1330K31Y5SQ6*V0	VY1330K31Y5SG6*V0	
47	. 10					VY1470K31Y5SQ6*V0	VY1470K31Y5SG6*V0	
68	± 10					VY1680K31Y5SQ6*V0	VY1680K31Y5SG6*V0	
100		Y5S (2C3)	8.0			VY1101K31Y5SQ6*V0	VY1101K31Y5SG6*V0	
150						VY1151K31Y5SQ6*V0	VY1151K31Y5SG6*V0	
220				5.0		VY1221K31Y5SQ6*V0	VY1221K31Y5SG6*V0	
330				5.0	10.0	VY1331K31Y5SQ6*V0	VY1331K31Y5SG6*V0	
470						VY1471M31Y5UQ6*V0	VY1471M31Y5UG6*V0	
680						VY1681M31Y5UQ6*V0	VY1681M31Y5UG6*V0	
1000			9.0			VY1102M35Y5UQ6*V0	VY1102M35Y5UG6*V0	
1500			10.5			VY1152M41Y5UQ6*V0	VY1152M41Y5UG6*V0	
2200	± 20	Y5U (2E3)	12.0	†		VY1222M47Y5UQ6*V0	VY1222M47Y5UG6*V0	
3300			15.0			VY1332M59Y5UQ6*V0	VY1332M59Y5UG6*V0	
3900			15.5			VY1392M61Y5UQ6*V0	VY1392M61Y5UG6*V0	
4700			16.0			VY1472M63Y5UQ6*V0	VY1472M63Y5UG6*V0	
10						VY1100K31U2JQ6*VX	VY1100K31U2JG6*VX	
15		U2J (N750)				VY1150K31U2JQ6*VX	VY1150K31U2JG6*VX	
22						VY1220K31U2JQ6*VX	VY1220K31U2JG6*VX	
33					VY1330K31Y5SQ6*VX	VY1330K31Y5SG6*VX		
47	. 10					VY1470K31Y5SQ6*VX	VY1470K31Y5SG6*VX	
68	± 10	± 10	8.0			VY1680K31Y5SQ6*VX	VY1680K31Y5SG6*VX	
100		Y5S (2C3)	8.0			VY1101K31Y5SQ6*VX	VY1101K31Y5SG6*VX	
150				5.0	12.5	VY1151K31Y5SQ6*VX	VY1151K31Y5SG6*VX	
220			5			VY1221K31Y5SQ6*VX	VY1221K31Y5SG6*VX	
330				5.0		VY1331K31Y5SQ6*VX	VY1331K31Y5SG6*VX	
470	0				VY1471M31Y5UQ6*VX	VY1471M31Y5UG6*VX		
680					VY1681M31Y5UQ6*VX	VY1681M31Y5UG6*VX		
1000			9.0 10.5 12.0	í	l t	VY1102M35Y5UQ6*VX	VY1102M35Y5UG6*VX	
1500					VY1152M41Y5UQ6*VX	VY1152M41Y5UG6*VX		
2200	± 20	Y5U (2E3)		12.0	†	-		VY1222M47Y5UQ6*VX
3300	1		15.0	ţ		VY1332M59Y5UQ6*VX	VY1332M59Y5UG6*VX	
3900	1		15.5	╡	l F	VY1392M61Y5UQ6*VX	VY1392M61Y5UG6*VX	
4700	1		16.0	t		VY1472M63Y5UQ6*VX	VY1472M63Y5UG6*VX	

Notes

Straight leads are available on request
Coating extension DR valid for straight leads only
On request available: ± 10 % tolerance
(1) 15th digit of the clear text code number to be completed with the packaging code

Revision: 18-Oct-13

Document Number: 28537

For technical questions, contact: cdc@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




PACKAGING


PACKAGING					
CAPACITANCE		BODY DIAMETER	P/	ACKAGING QUANTITI	ES
VALUE	SIZE CODE	D _{MAX.} (mm)	BULK	REEL	АММО
10 pF to 2200 pF	31 to 47	12.0	1000	500	750
3300 pF to 4700 pF	51 to 63	16.0	500	500	750

Note

• The capacitors are supplied in bulk packaging (cardboard boxes), in tape on reel in ammopack

STRAIGHT LEADS





Lead spacing 10.0 mm and 12.5 mm, sprocket hole pitch 25.04 mm for lead spacing



www.vishay.com

Vishay BCcomponents

DIMENSIONS OF TAPE				
SYMBOL	PARAMETER	DIMENSIONS (mm)		
		FIG. 2		
D ⁽¹⁾	Body diameter	16.0 max.		
d	Lead diameter	0.6 ± 0.05		
Р	Pitch of component	25.4 ± 1		
P ₀ ⁽²⁾	Pitch of sprocket hole	12.7 ± 0.3		
P ₁ ⁽³⁾	Distance, hole center to lead	7.7 or 6.4 ± 1.0		
P ₂ ⁽³⁾	Distance, hole to center of component	12.7 ± 1.5		
F	Lead spacing	10.0 or 12.5 + 0.6/- 0.4		
Δh	Average deviation across tape	± 1.0 max.		
ΔΡ	Average deviation in direction of reeling	± 1.0 max.		
W	Carrier tape width	18.0 + 1/- 0.5		
W ₀	Hold-down tape width	5.0 min.		
W ₁	Position of sprocket hole	9.0 + 0.75/- 0.5		
W ₂	Distance of hold-down tape	3.0 max.		
H ₁	Maximum component height	40.0		
H ₀	Height to seating plane (for kinked leads)	16.0 ± 0.5		
H ₀	Height to seating plane (for straight leads)	20.0 ± 0.5		
L	Length of cut leads	11.0 max.		
I	Length of lead protrusion	1.0 max.		
D ₀	Diameter of sprocket hole	4.0 ± 0.2		
t	Total tape thickness	0.9 max.		


Notes

⁽¹⁾ See Ordering Information table


⁽²⁾ Cumulative pitch error: ± 1 mm/20 pitches

⁽³⁾ Obliquity maximum 3°

REEL AND TAPE DATA in millimeters



Reel with capacitors on tape



Ammopack with capacitors on tape

Revision: 18-Oct-13

4 For technical questions, contact: <u>cdc@vishay.com</u> Document Number: 28537

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


VY1 Series

www.vishay.com

SHAY

Vishay BCcomponents

APPROVALS				
IEC 60384-14.3 - Safety tests This approval together with CB test certificate s	ubstitutes all national approval	s.		
CB Certificate				\frown
Y1-capacitor: CB test certificate:	US-19600-UL	10 pF to 4.7 nF	500 V _{AC}	/Ih \
X1-capacitor: CB test certificate:	US-19600-UL	10 pF to 4.7 nF	760 V _{AC}	
VDE				^
Y1-capacitor: VDE marks approval:	40012673	10 pF to 4.7 nF	500 V _{AC}	
X1-capacitor: VDE marks approval:	40012673	10 pF to 4.7 nF	760 V _{AC}	$\zeta \square E $
DIN EN 60384-14 VDE 0565-1-1:2006-04 - Safe	ety tests			
Underwriters Laboratories Inc./Canadian Sta	Indards Association			
Y1-capacitor: CSA test certificate:	E183844	10 pF to 4.7 nF	500 V _{AC}	e e e
X1-capacitor: CSA test certificate:	E183844	10 pF to 4.7 nF	760 V _{AC}	
UL 60384-14, CSA E60384-1:03, CSA E60384-	14:09			
Fixed capacitors for electromagnetic interference	e suppression and connection	to the supply mains.		
CQC				\frown
Y1-capacitor: CQC test certificate:	C0042538	10 pF to 4.7 nF	500 V _{AC}	$(\cap \cap)$
X1-capacitor: CQC test certificate:	C0042538	10 pF to 4.7 nF	760 V _{AC}	



PERFORMANCE				
TEST	TEST CONDITION	TEST LIMITS		
Visual and mechanical inspection	Optical inspection, dimensions measured with caliper	No visible damage, marking legible		
Capacitance (C)	25 °C \pm 3 °C , relative humidity (RH) \leq 75 %,	Capacitance within specified tolerance		
Dissipation factor (DF)	1.0 V_{RMS} \pm 0.2 V_{RMS} at 1 kHz for Y5U and Y5S, and 1 MHz for U2J	DF \leq 0.3 % for U2J and DF \leq 2.5 % for Y5S and Y5U		
Insulation resistance (IR)	Measured within 60 s \pm 5 s after charging at 500 V_{DC}	10 000 MΩ min.		
Dielectric strength	4000 V_{AC} at 50 Hz/60 Hz for 1 min, 50 mA max.	No failure		
Temperature characteristic	RH \leq 75 %, 1.0 V_{RMS} \pm 0.2 V_{RMS} at 1 kHz for Y5U and Y5S, and 1 MHz for U2J	U2J: -750 ppm ± 120 ppm Y5S: ± 22 % Y5U: +22 %/-56 %		
Impulse voltage	3 pulses of 8 kV	No failure		

5 For technical questions, contact: <u>cdc@vishay.com</u>

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




Г

Vishay BCcomponents

PERFORM	PERFORMANCE				
TEST	TEST CONDITION	TEST LIMITS			
Life test	1000 h at 125 °C \pm 2 °C, 850 V _{AC} /50 Hz; once every hour 1000 V _{AC} for 0.1 s	External appearance: No visible damage $\Delta C \le \pm 15 \%$ DF $\le 0.5 \%$ for U2J and $\le 5 \%$ for Y5S and Y5U IR $\ge 3000 \ M\Omega$ Dielectric strength: No failure			
Humidity test	500 h at 500 V _{AC} , 50 Hz and 500 h unloaded 40 °C, RH = 90 % to 95%	External appearance: No visible damage $\Delta C \le \pm 10$ % for U2J and $\le \pm 15$ % for Y5S and Y5U DF ≤ 0.5 % for U2J and ≤ 5 % for Y5S and Y5U IR ≥ 3000 M Ω Dielectric strength: No failure			
Robustness of termination	Pull test: 0.5 kg tensile weight in radial direction for $10 \text{ s} \pm 1 \text{ s}$ Bending strength: Capacitor body rotated by 90° in both directions	No damage to capacitor body and lead wire			
Soldering effect	Immersion of lead wires into 260 °C \pm 5 °C solder for 10 s \pm 2 s; min. distance from body: 1.5 mm Hand soldering at 400 °C \pm 10 °C for 3 s to 4 s; min. distance from body: 1.5 mm	External appearance: No visible damage $\Delta C \le \pm 5$ % for U2J and $\le \pm 10$ % for Y5S and Y5U Dielectric strength: No failure			
Vibration test	Resin (adhesive) Solder the capacitor onto test jig (glass epoxy body) and use resin (adhesive) to stick the body to the test jig. The capacitor must be soldered firmly to the supporting lead wire. Vibration change from 10 Hz to 2000 Hz and back to 10 Hz; Total amplitude: 1.5 mm; Acceleration: 100 m/s2; Sweep rate: 1 oct/min, each axis 2 h (6 h in total)	External appearance: No visible damage Capacitance within specified tolerance DF \leq 0.3 % for U2J and \leq 2.5 % for Y5S and Y5U IR \geq 10 000 G Ω			

LEAKAGE CURRENT VS. VOLTAGE (Typical)




Revision: 18-Oct-13

6


Document Number: 28537

For technical questions, contact: cdc@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



IMPEDANCE VS. FREQUENCY (Typical)

www.vishay.com



Note

ISHA

 The capacitors meet the essential requirements of "EIA 198". Unless stated otherwise all electrical values apply at an ambient temperature of 25 °C ± 3 °C, at normal atmospheric conditions.

RELATED DOCUMENTS			
General Information	www.vishay.com/doc?28536		
CB Test Certificate	www.vishay.com/doc?22249		
VDE Marks Approval	www.vishay.com/doc?22251		
UL Test Certificate	www.vishay.com/doc?22250		
CQC Test Certificate	www.vishay.com/doc?22248		



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.