

BRIDGET-W-UNI

~60° wide beam

TECHNICAL SPECIFICATIONS:

Dimensions 22.6 mm Height 12.8 mm

Fastening glue Colour metal

Box size 480 x 280 x 300 mm

Box weight 3.4 kg

Quantity in Box 1680 pcs


ROHS compliant yes 1




MATERIAL SPECIFICATIONS:

ComponentTypeMaterialColourCoatingBRIDGET-W-UNIReflectorPCmetallacquer






PHOTOMETRIC DATA (MEASURED):



PHOTOMETRIC DATA (MEASURED):



PHOTOMETRIC DATA (MEASURED):


SHARP

LED Mini Zenigata (GW5BM)

FWHM 62.0°
Efficiency 87 %
Peak intensity 1.000 cd/lm

LEDs/each optic 1 Light colour White Required components:






TRIDONIC

LED SLE G5 LES11

FWHM 62.0° Efficiency 84 % Peak intensity 0.890 cd/lm

LEDs/each optic 1
Light colour White
Required components:






TRIDONIC

LED SLE G5 LES6

FWHM 50.0° Efficiency 88 % Peak intensity 1.200 cd/lm

LEDs/each optic 1
Light colour White
Required components:







PHOTOMETRIC DATA (SIMULATED):

bridgelux.


 LED
 V6 HD

 FWHM
 60.0°

 Efficiency
 91 %

 Peak intensity
 1.046 cd/lm


LEDs/each optic 1 Light colour White Required components:



OSRAM Opto Semiconductors

LED Soleriq S9
FWHM 61.0°
Efficiency 89 %
Peak intensity 0.970 cd/lm

LEDs/each optic 1 Light colour White Required components:





GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy