

## **General Description**

The WSD25280DN56G is the highest performance trench N-Ch MOSFET with extreme high celldensity ,which provide excellent RDSON and gate charge for most of the synchronous buck converter applications .

The WSD25280DN56G meet the RoHS and Green Product requirement , 100% EAS guaranteed with full function reliability approved.

#### **Features**

- Advanced high cell density Trench technology
- Super Low Gate Charge
- Excellent CdV/dt effect decline
- 100% EAS Guaranteed
- Green Device Available


## **Product Summery**

BVDSS	RDSON	ID
25V	$0.7 m\Omega$	280A

## **Applications**

- High Frequency Point-of-Load Synchronous Buck Converter
- Networking DC-DC Power System
- Power Tool Application

## **DFN5X6-8 Pin Configuration**



# **Absolute Maximum Ratings**

Symbol	Parameter	Rating	Units	
$V_{DS}$	Drain-Source Voltage	25	V	
$V_{GS}$	Gate-Source Voltage	±20	V	
I <sub>D</sub> @T <sub>C</sub> =25℃	Continuous Drain Current (Silicon Limited) 1,7	280	Α	
I <sub>D</sub> @T <sub>C</sub> =70℃	Continuous Drain Current(Silicon Limited) 1,7	190	Α	
I <sub>DM</sub>	Pulsed Drain Current <sup>2</sup>	600	А	
EAS	Single Pulse Avalanche Energy <sup>3</sup>	1200	mJ	
I <sub>AS</sub>	Avalanche Current	100	Α	
P <sub>D</sub> @T <sub>C</sub> =25°C	Total Power Dissipation <sup>4</sup>	83	W	
T <sub>STG</sub>	Storage Temperature Range	-55 to 150	$^{\circ}$	
TJ	Operating Junction Temperature Range	-55 to 150	$^{\circ}$	

#### **Thermal Data**

Symbol	Parameter	Тур.	Max.	Unit
$R_{ heta JA}$	Thermal Resistance Junction-Ambient <sup>1</sup>		23	°C/W
$R_{ heta JC}$	Thermal Resistance Junction-Case <sup>1</sup>		1.5	°C/W



**N-Ch MOSFET** 

# Electrical Characteristics (T<sub>J</sub>=25 °C, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	$V_{GS}$ =0V , $I_D$ =250uA	25			V
$\triangle BV_{DSS}/\triangle T_{J}$	BV <sub>DSS</sub> Temperature Coefficient	Reference to 25℃, I <sub>D</sub> =1mA		0.022		V/°C
R <sub>DS(ON)</sub>	Static Drain-Source On-Resistance <sup>2</sup>	V <sub>GS</sub> =10V , I <sub>D</sub> =20A		0.7	0.9	mΩ
		V <sub>GS</sub> =4.5V , I <sub>D</sub> =20A		1.4	1.9	
$V_{GS(th)}$	Gate Threshold Voltage	\/\/  250u/\	1.0		2.5	V
$\triangle V_{GS(th)}$	V <sub>GS(th)</sub> Temperature Coefficient	$V_{GS}=V_{DS}$ , $I_D=250uA$		-6.1		mV/℃
I <sub>DSS</sub>	Drain-Source Leakage Current	$V_{DS}$ =20V , $V_{GS}$ =0V , $T_J$ =25 $^{\circ}$ C			1	uA
DSS		$V_{DS}$ =20V , $V_{GS}$ =0V , $T_J$ =55 $^{\circ}$ C			5	uA
I <sub>GSS</sub>	Gate-Source Leakage Current	$V_{GS}=\pm20V$ , $V_{DS}$ = $0V$			±100	nA
gfs	Forward Transconductance	V <sub>DS</sub> =5V , I <sub>D</sub> =10A		40		S
$R_g$	Gate Resistance	V <sub>DS</sub> =0V , V <sub>GS</sub> =0V , f=1MHz		3.8	1.5	Ω
$Q_g$	Total Gate Charge (4.5V)	V <sub>DS</sub> =15V , V <sub>GS</sub> =4.5V , I <sub>D</sub> =20A		72		
$Q_{gs}$	Gate-Source Charge			18		nC
$Q_{gd}$	Gate-Drain Charge			24		
$T_{d(on)}$	Turn-On Delay Time			33		
T <sub>r</sub>	Rise Time	V <sub>DD</sub> =15V , V <sub>GEN</sub> =10V ,		55		ns
T <sub>d(off)</sub>	Turn-Off Delay Time	$R_G=1\Omega$ , $I_D=10A$		62		
T <sub>f</sub>	Fall Time			22		
Ciss	Input Capacitance	V <sub>DS</sub> =15V , V <sub>GS</sub> =0V , f=1MHz		7752		
C <sub>oss</sub>	Output Capacitance			1120		pF
C <sub>rss</sub>	Reverse Transfer Capacitance			650		

## **Diode Characteristics**


Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
Is	Continuous Source Current <sup>1,6</sup>	$V_G$ = $V_D$ = $0V$ , Force Current			69	Α
I <sub>SM</sub>	Pulsed Source Current <sup>2,6</sup>				180	Α
$V_{SD}$	Diode Forward Voltage <sup>2</sup>				1.2	V

### Note:


- 1.The data tested by surface mounted on a 1 inch<sup>2</sup> FR-4 board with 2OZ copper,t<10sec.
- 2.The data tested by pulsed , pulse width  $\,\leq\,300\text{us}$  , duty cycle  $\,\leq\,2\%$
- 3.The EAS data shows Max. rating . The test condition is  $V_{DD}$ =25V, $V_{GS}$ =10V,L=0.1mH, $I_{AS}$ =30A
- 5.The Min. value is 100% EAS tested guarantee.
- 6. The data is theoretically the same as  $I_D$  and  $I_{DM}$ , in real applications, should be limited by total power dissipation.
- 7.Package limitation current is 100A.




# **Typical Characteristics**




#### **Output Characteristics**




On-Resistance vs. Drain Current






Transfer Characteristics




Capacitance




On-Resistance vs. Junction Temperature


**N-Ch MOSFET** 




Source-Drain Diode Forward Voltage




Threshold Voltage



On-Resistance vs. Gate-to-Source Voltage




Single Pulse Power, Junction-to-Ambient




Safe Operating Area, Junction-to-Ambient





Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case



### **Attention**

- 1, Any and all Winsok power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your Winsok power representative nearest you before using any Winsok power products described or contained herein in such applications.
- 2, Winsok power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all Winsok power products described or contained herein.
- 3, Specifications of any and all Winsok power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- 4, Winsok power Semiconductor CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- 5,In the event that any or all Winsok power products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- 6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of Winsok power Semiconductor CO., LTD.
- 7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Winsok power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- 8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the Winsok power product that you Intend to use.
- 9, this catalog provides information as of Sep.2014. Specifications and information herein are subject to change without notice.