

DCF897NT-XJ

18V XR Brushless High Torque 3/4" Impact Wrench - Bare Unit

The solution for industrial high torque applications delivering 950 Nm of max torque and 1625 Nm of max break away torque now available with a 3/4" anvil.

Selling Propositions

- Powerful fan cooled motor delivers up to 680Nm of torque for heavy duty reactionless drilling and fastening applications
- Latest generation 18V BRUSHLESS XR Li-Ion High Torque Wrench
- 3 Speed and torque settings gives you the control to best suit your application, 0-400/1,200/1,900 RPM
- 7/16" "drop-in" hex bit holder is easy to use one handed and suited for a range of drilling & screwdriving accessories
- Bright white LED with delay feature for improved visibility and flashlight functionality
- Up to 1625Nm of "breakaway" torque ensures removal of the tightest bolts
- Comfortable rubber XR grip and switch for greater application comfort and maximum control

Standard Equipment

Warranty specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Max Torque	950.0 Nm
No Load Speed	0-400/0-1200/0-1900
Impacts per Minute	2400 ipm
No. of Modes	3.0
Anvil Size and Type	3/4" Hog Ring
Weight	2.6 kg
Hand/Arm Vibration - Impact	13.0 m/s ²
Uncertainty K 1 (Vibration)	5.9 m/s ²
Sound Pressure	101.0 dB(A)
Sound Pressure Uncertainty	3.0 dB(A)
Sound Power	112.0 dB(A)
Sound Power Uncertainty	3.0 dB(A)