


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
A		REVISED PER ECO-19-006961	09MAY2019	AP AC



NOTES:

- 1. 100% ELECTRICAL TEST FOR CONTINUITY, OPENS AND SHORTS.
- 2. THE MATED BUS-BAR SHOULD HAVE SURFACE ROUGHNESS Ra 1.6um MAX. SHOULD HAVE PLATING 3um MIN. SILVER IN CONTACT AREA, AND 1.27um MIN. Ni OVERALL.
- 3. SILVER PLATING CONTACT MAY DISCOLOR IN AIR, BUT NO PERFORMANCE ISSUE
- 4. LOW HALOGEN REQUEST: Br<900ppm, Cl<900ppm, Br+Cl<1500ppm PER HOMOGENEOUS MATERIAL
- 5. LABEL CONTENT AS SHOWN

XXXXXX-X	TE P/N
MADE IN CHINA	
TE YYWW	YY: YEAR;WW: WEEK

- 6. WIRE ALLOWABLE CURRENT: 75A FOR 6AWG
- 7. OPERATING TEMPERATURE: -20C~80C
- 8. FLAMMABILITY: CONNECTOR MEET UL 94V-0, WIRE MEET VW-1
- 9. THE CABLE ASSEMBLY SHOULD BE UL AND RoHS2(2011/65/EU) COMPLIANT.
- 10. M3 NUT WITHSTAND 44N min. PUSH OUT FORCE IN HOUSING.

WIRING CHART		
FROM	TO	WIRE
J1-P1	J3	BLACK
J1-P2	J2	RED

2337275-2	100±10	NA
2337275-1	250±10	NA
TE P/N	L	CUSTOMER P/N,REV.





QTY	PC	DESCRIPTION	ITEM
1	PC	RA CCJ CONNECTOR TE 2326688-1	8
1	PC	LABEL	7
2	PC	M3 NUT	6
AR	MR	HEAT SHRINK TUBE, BLACK	5
AR	MR	UL WIRE 6AWG RED	4
AR	MR	UL WIRE 6AWG BLACK	3
AR	MR	HEAT SHRINK TUBE, BLACK	2
2	PC	R-TERMINAL 6AWG M8	1
-1	U/M		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	24MAY2018	ADAM CHEN	
DIMENSIONS: mm		CHK	-	-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	24MAY2018	DAVID ZHANG	
0 PLC ± -		PRODUCT SPEC	108-152035	NAME	
1 PLC ± -		APPLICATION SPEC	114-152042	Cable AssY, RA CCJ TO R TERMINAL	
2 PLC ± 0.25		WEIGHT	0	SIZE	A2
3 PLC ± -		CUSTOMER DRAWING		CAGE CODE	00779
4 PLC ± -		FINISH	-	DRAWING NO	C=2337275
ANGLES ± -				RESTRICTED TO	-
SCALE		N.T.S	SHEET	1 of 2	REV
SCALE		N.T.S	SHEET	1 of 2	REV

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE CONNECTIVITY ENVIRONMENTAL STANDARD TEC-138-702

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



RA CCJ CONNECTOR PROFILE FOR REFERENCE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ADAM CHEN 24MAY2018	TE Connectivity		
DIMENSIONS: mm		CHK - APVD DAVID ZHANG 24MAY2018			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-152035	RESTRICTED TO -		
0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC 114-152042	SIZE A2	CAGE CODE 00779	DRAWING NO. C=2337275
MATERIAL -		FINISH -	WEIGHT 0	SCALE N.T.S.	SHEET 2 OF 2
CUSTOMER DRAWING			REV A		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2337275-1](#)