

D-SUB contact insert - CUC-DSI-C1STZ-S/DSL5B9 HD - 1418731

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

D-SUB contact insert, Number of positions: 15, Material: Steel, Connection method: Solder pins



Why buy this product

- Various connection methods for every application
- Standard-compliant pin connector pattern

Key Commercial Data

Packing unit	10 STK
GTIN	
GTIN	4055626149691

Technical data

Mechanical characteristics

Standards/specifications	DIN 41652
Number of positions	15
Number of slots	1
Connection profile	D-SUB 9
Insertion/withdrawal cycles	50
Connection method	Solder pins
Type of contact	punched contacts
Mounting type	4-40 UNC thread
Type	09

Ambient conditions

Ambient temperature (operation)	-55 °C ... 105 °C
---------------------------------	-------------------

Material data

Flammability rating according to UL 94	V0
--	----

D-SUB contact insert - CUC-DSI-C1STZ-S/DSL5B9 HD - 1418731

Technical data

Material data

Housing material	Steel
Housing surface material	tin-plated
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0
Contact material	Copper alloy
Contact surface material	Sn/Au

Electrical characteristics

Number of positions	15
Rated current	3 A
Degree of pollution	2

Standards and Regulations


Standards/regulations	DIN 41652
Flammability rating according to UL 94	V0

Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Schematic diagram



Dimensional drawing



D-SUB contact insert

Phoenix Contact 2017 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>